

MEGAPRO Screwdrivers



MEGAPRO Screwdrivers		
Part Number	Description	Price
211R2C36RD	211 Ratcheting Bit Driver	\$34.00
151NAS	151 NAS Bit Driver	\$22.00
151ELEC	151 Electronics Bit Driver	\$30.00
151HX	151 Hex Bit Driver	~~\$25.00~~
151AUTO	151 Automotive Bit Driver	\$25.00
151SL44	151SL44 Locking Bit Driver	\$27.00
6EXT-SL6	6" Extension	\$12.00
251PRECISION	251 Precision Bit Driver	\$30.00

MEGAPRO Screwdrivers

151NAS Screwdriver \$22.00

Custom loaded multi-bit screwdriver with 7 double-ended **S2 steel hex bits** commonly used for everyday tasks. Made in the USA.



Double-Ended Bits	
Tool	Description
	Dbl-End Square 0-3
	Dbl-End Square 1-2
	Dbl-End Phillips 0-3
	Dbl-End Phillips 1-2
	Dbl-End Flat 4-6
	Dbl-End Torx (Star)
	Dbl-End Torx (Star)

Features

- The double-ended bit load includes Phillips 0, 1, 2, 3; Square 0, 1, 2, 3; Flat 4, 6; Torx 10, 15, 20, 25
- Industrial grade S2 steel bits perfect for any job
- Shaft serves as a 1/4" Hex Nut Driver
- Retractable cartridge for easy bit access
- Palm-Saver Technology improves comfort in use
- The EZ Guide collar helps maintain full contact between the bit and the screw for easier screw driving
- The Shaft is made of 12T14 alloy steel
- The handle is made from engineered (Ultra-strong) Triax 1120 resin, an ABS-Nylon alloy
- Lifetime warranty*
- Weight: 0.5 lb.
- Dimensions: 8.74 x 1.4 x 1.4 in.

* Warranty refers to manufacturer's defects and do not cover normal wear and tear, product abuse, or product modification.

Bit Handle Storage



151ELEC Screwdriver \$30.00

Custom loaded multi-bit screwdriver with 7 double-ended **S2 steel bits** commonly used in the electronic industry. Made in the USA.



Double-Ended Bits	
Tool	Description
	Dbl-End Flat 4-6
	Dbl-End Phillips 0-3
	Dbl-End Phillips 1-2
	Dbl-End Square 1-2
	Dbl-End Spanner 6-8
	Dbl-End Spanner 10-12
	Dbl-End Torx (Star) 10-15

Features

- The double-ended bit load contains, Phillips 0, 1, 2, 3; Flat (slotted) 4, 6; Square (Robertson) 1, 2; Torx pin (Star pin) 10, 15; Spanner 6, 8, 10, 12.
- Industrial grade S2 steel bits perfect for any job.
- Shaft serves as a 1/4" Hex Nut Driver.
- Retractable cartridge for easy bit access.
- Palm-Saver Technology improves comfort in use.
- The EZ Guide collar helps maintain full contact between the bit and the screw for easier screw driving.
- The Shaft is made of 12T14 alloy steel.
- The handle is made from engineered (Ultra-strong) Triax 1120 resin, an ABS-Nylon alloy.
- Lifetime warranty*
- Weight: 0.5 lb.
- Dimensions: 8.74 x 1.4 x 1.4 in.

* Warranty refers to manufacturer's defects and do not cover normal wear and tear, product abuse, or product modification.

Bit Handle Storage



MEGAPRO Screwdrivers

151HX Screwdriver \$25.00

Custom loaded multi-bit screwdriver with 7 double-ended **S2 steel hex bits** commonly used to assemble and repair furniture. Made in the USA.

151HX



Double-Ended Bits	
Tool	Description
	Dbl-End Hex 3/32-7/64
	Dbl-End Hex 1/8-9/64
	Dbl-End Hex 5/32-3/16
	Dbl-End Hex 7/32-1/4
	Dbl-End Hex 2.00-3.00
	Dbl-End Hex 4.00-5.00
	Dbl-End Hex 5.50-6.00

Features

- The double-ended bit load includes 7 double-ended ball bearing bits: Hex (Allen) 2, 3, 4, 5, 5.5, 6, 3/33, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4.
- Industrial grade S2 steel bits perfect for any job.
- Shaft serves as a 1/4" Hex Nut Driver.
- Retractable cartridge for easy bit access.
- Palm-Saver Technology improves comfort in use.
- The EZ Guide collar helps maintain full contact between the bit and the screw for easier screw driving.
- The Shaft is 12T14 alloy steel.
- The handle is made from engineered (Ultra-strong) Triax 1120 resin, an ABS-Nylon alloy.
- Lifetime warranty*
- Weight: 0.5 lb.
- Dimensions: 8.74 x 1.4 x 1.4 in.

* Warranty refers to manufacturer's defects and do not cover normal wear and tear, product abuse, or product modification.

Bit Handle Storage



151AUTO Specifications \$25.00

Custom loaded multi-bit screwdriver with 6 double-ended bits and a 1/4" socket adapter commonly used in the automotive industry. Made in the USA.

151AUTO



Double-Ended Bits	
Tool	Description
	Dbl-End Phillips 1-2
	Dbl-End Torx (Star) 9-40
	Dbl-End Torx (Star) 10-15
	Dbl-End Torx (Star) 20-25
	Dbl-End Torx (Star) 27-30
	Flat 5.5 x Valve Stem Bit
	1/4" Socket Adaptor

Features

- The bit load includes Phillips 1, 2; Torx (Star) 9, 10, 15, 20, 25, 27, 30, 40; Flat 5.5; Valve Stem; 1/4" Socket adapter; and 1/4" Hex Nut Driver shaft.
- Industrial grade S2 steel bits.
- Shaft serves as a 1/4" Hex Nut Driver.
- Retractable cartridge for easy bit access.
- Palm-Saver Technology improves comfort in use.
- The EZ Guide collar helps maintain full contact between the bit and the screw for easier screw driving.
- The Shaft is made of 12T14 alloy steel.
- The handle is made from engineered (Ultra-strong) Triax 1120 resin, an ABS-Nylon alloy.
- Lifetime warranty*.
- Weight: 0.5 lb.
- Dimensions: 8.74 x 1.4 x 1.4 in.

* Warranty refers to manufacturer's defects and do not cover normal wear and tear, product abuse, or product modification.

Bit Handle Storage



MEGAPRO Screwdrivers

151SL44 Specifications \$27.00

Multi-bit Screwdriver with patented locking mechanism that holds your bit tight. Loaded with the most widely used bits. Made in the USA.



151SL44

Double-Ended Bits	
Tool	Description
	Shaftlok Dbl-End Square 0-3
	Shaftlok Dbl-End Square 1-2
	Shaftlok Dbl-End Phillips 0-3
	Shaftlok Dbl-End Phillips 1-2
	Shaftlok Dbl-End Flat 4-6
	Shaftlok Dbl-End Torx (Star)
	Shaftlok Dbl-End Torx (Star)

Features

- The double-ended bit load includes Flat 4, 6; Phillips 0, 1, 2, 3; Square 0, 1, 2, 3; Torx 10, 15, 20, 25.
- Industrial grade S2 steel bits perfect for any job.
- Shaft serves as a 1/4" Hex Nut Driver.
- The ShaftLOK™ bit locking mechanism eliminates the hassle of bits falling out of the shaft when getting partially "stuck" in the fastener as the screwdriver is pulled away.
- The ShaftLOK™ has a 6" extension add-on using the same locking technique for a much longer reach.
- Retractable cartridge for easy bit access.
- Palm-Saver Technology improves comfort in use.
- The EZ Guide collar helps maintain full contact between the bit and the screw for easier screw driving.
- The Shaft is made of 12T14 alloy steel; specially modified S2 Steel.
- The handle is made from engineered (Ultra-strong) Triax 1120 resin, an ABS-Nylon alloy.
- Lifetime warranty.*
- Weight: 0.5 lb.
- Dimensions: 8.74 x 1.4 x 1.4 in.

* Warranty refers to manufacturer's defects and do not cover normal wear and tear, product abuse, or product modification.

Bits Handle Storage



6EXT-SL6 Specifications \$12.00

A slim profile 6" extension that locks into the ShaftLOK™ 15-in-1 Multi-Bit Screwdriver. Made with one solid steel piece with .375" (9.6mm) clearance. The Megapro ShaftLOK™ extensions can also be used in power drills and multiple extensions can be locked together for extra long reach.



Features

- Black Steel Oxide.
- Patented Locking Mechanism.
- Weight: 0.20 lb.
- Dimensions: 6 x 0.375 x 0.375 in.
- Made in USA.

MEGAPRO Screwdrivers

251PRECISION Specification

24 laser engraved Precision bit tips all in one comfortable driver. Patented Retractable Bit Cartridge and Palm-saver Cap™. Rubberized handle for comfortable use. Made in Taiwan.

251PRECISION



Double-Ended Bits		
Tool		Description
		Dbl-End Hex 1.5-2.0
		Dbl-End Hex 2.5-3.0
		Dbl-End Pentalobe 2 - 5
		Dbl-End Phillips 1-000
		Dbl-End Phillips 2-00
		Dbl-End Flat 1.5-2.0
		Dbl-End Flat 2.5-3.0
		Spanner 2.6 - Triangle 2.3
		Dbl-End Torx (Star) 3 - Torx (Star) Pin 6
		Dbl-End Torx (Star) 4 - Torx (Star) Pin 8
		Dbl-End Torx 10 - Phillips 0
		Dbl-End Torx (Star) Pin 10-15

Features

- The bit assortment includes: Hex 1.5, 2.0, 2.5, 3.0; Pentalobe 2, 5; Phillips 1, 000, 2, 00, 0; Slot 1.5, 2.0, 2.5, 3.0; Spanner 2.6; Tri-Angle 2.3; Torx 3, 4, 5; Torx tamperproof 6, 8, 10, 15.
- Industrial grade S2 steel bits.
- Retractable cartridge for easy bit access.
- Palm-Saver Technology improves comfort in use.
- Rubber grips on the collar provide even further control and comfort, maximizing speed and efficiency.
- 3-year warranty*
- Weight: 0.15 lb.
- Dimensions: 6.27 x 1.08 x 1.08 in.

* Warranty refers to manufacturer's defects and do not cover normal wear and tear, product abuse, or product modification.

Bit Handle Storage



211R2C36RD Specifications \$34.00

Ratcheting multi-bit screwdriver loaded with 12 commonly used double-ended bits. Patented zinc alloy solid-core mechanism that delivers more control and torque. Made in the USA.

211R2C36RD



Double-Ended Bits	
Tool	Description
	Dbl-End Square 1-2
	Dbl-End Phillips 0-3
	Dbl-End Phillips 1-2
	Dbl-End Flat 4-6
	Dbl-End Torx (Star) 10-15
	Dbl-End Torx (Star) 20-25

Features

- The double-ended bit load includes Philips 0, 1, 2, 3; Square (Robertson) 1, 2; Flat (Slot) 4, 6; Star (Torx) 10, 15, 20, 25.
- Industrial grade S2 steel bits perfect for any job.
- Shaft serves as a 1/4" Hex Nut Driver.
- Chamfered solid shaft for long life and durability.
- The 28-tooth ratchet with a patented zinc alloy solid-core mechanism gives you greater control and delivers more than 225 in/lbs of torque.
- Cushion grip, tapered designed handle provides extra comfort.
- Retractable cartridge for easy bit access.
- Palm-Saver Technology improves comfort in use.
- The handle is made from engineered (Ultra-strong) Triax 1120 resin, an ABS-Nylon alloy.
- Lifetime warranty*
- Weight: 0.66 lb.
- Dimensions: 9.84 x 1.97 x 1.97 in.

* Warranty refers to manufacturer's defects and do not cover normal wear and tear, product abuse, or product modification.

Bit Handle Storage

