

**BRYANT®**

Quick Selection Guide

# Manual Motor Controllers / Disconnects

**TECH·SPEC®****30002D****40003D****4002****60002D****30102D,  
30103D****30322D,  
30323D****30302D,  
30303D****60302D,  
60303D****664X33D****664X63D**

## Toggle Switch AC Motor Controllers / Disconnects


| Part Number   | Description                                                 | Amperage | Phase | Poles | Wired         | Price    |
|---------------|-------------------------------------------------------------|----------|-------|-------|---------------|----------|
| <b>30002D</b> | Switch only, 30A, 2-pole, 15 HP @ 600 VAC - Standard Toggle | 30       | 1     | 2     | Back and Side | \$40.50  |
| <b>30003D</b> | Switch only, 30A, 3-pole, 20 HP @ 600 VAC - Standard Toggle | 30       | 3     | 3     | Back and Side | \$85.00  |
| <b>4002*</b>  | Switch only, 40A, 2-pole, 5 HP @ 600 VAC - Standard Toggle  | 40       | 1     | 2     | Side          | \$41.50  |
| <b>40002D</b> | Switch only, 40A, 2-pole, 15 HP @ 600 VAC - Standard Toggle | 40       | 1     | 2     | Side          | \$71.00  |
| <b>40003D</b> | Switch only, 40A, 3-pole, 20 HP @ 600 VAC - Standard Toggle | 40       | 3     | 3     | Side          | \$115.00 |
| <b>60002D</b> | Switch only, 60A, 2-pole, 20 HP @ 600 VAC - Standard Toggle | 60       | 1     | 2     | Back          | \$124.00 |
| <b>60003D</b> | Switch only, 60A, 3-pole, 30 HP @ 600 VAC - Standard Toggle | 60       | 3     | 3     | Back          | \$152.00 |

\*Motor controller only ("Not suitable as disconnect")

## Toggle Switch AC Motor Controller Accessories

| Part Number    | Description                                                      | Price   |
|----------------|------------------------------------------------------------------|---------|
| <b>30003FG</b> | Finger guards; red; for use with 30A and 40A Switches (Set of 2) | \$11.00 |
| <b>30100</b>   | NEMA 1 enclosure without switch, use with 30002D and 30003D      | \$25.50 |

**Example  
Back and Side  
Wired**



## Enclosed Toggle Switch AC Motor Controllers / Disconnects

| Part Number    | Description                     | Included Switch          | Amperage | Phase | Poles | Enclosure                | Price    |
|----------------|---------------------------------|--------------------------|----------|-------|-------|--------------------------|----------|
| <b>30102D</b>  | Enclosed, 30A, 2-pole, NEMA 1   | 30002D Standard Toggle   | 30       | 1     | 2     | NEMA 1Metal              | \$52.00  |
| <b>30103D</b>  | Enclosed, 30A, 3-pole, NEMA 1   | 30003D Standard Toggle   | 30       | 3     | 3     |                          | \$114.00 |
| <b>30302D</b>  | Enclosed, 30A, 2-pole, Aluminum | 30002D Standard Toggle   | 30       | 1     | 2     | NEMA 3RMetal             | \$78.00  |
| <b>30303D</b>  | Enclosed, 30A, 3-pole, Aluminum | 30003D Standard Toggle   | 30       | 3     | 3     |                          | \$139.00 |
| <b>30322D*</b> | Enclosed, 30A, 2-pole, Plastic  | 30002DS Short Toggle     | 30       | 1     | 2     | NEMA 3R<br>Thermoplastic | \$90.00  |
| <b>30323D*</b> | Enclosed, 30A, 3-pole, Plastic  | 30003DS Short Toggle     | 30       | 3     | 3     |                          | \$96.00  |
| <b>60302D*</b> | Enclosed, 60A, 2-pole, Aluminum | 60002FWD Standard Toggle | 60       | 1     | 2     | NEMA 3R Metal            | \$181.00 |
| <b>60303D*</b> | Enclosed, 60A, 3-pole, Aluminum | 60003FWD Standard Toggle | 60       | 3     | 3     |                          | \$211.00 |

\*Switch is not available as a separate item

## NEMA 4X Enclosed Rotary Switch AC Motor Controllers / Disconnects

| Part Number     | Description                    | Included Switch | Amperage | Phase | Poles | Enclosure                | Price    |
|-----------------|--------------------------------|-----------------|----------|-------|-------|--------------------------|----------|
| <b>664X33D*</b> | Enclosed, 30A, 3-pole, NEMA 4X | 66033D Rotary   | 30       | 3     | 3     | NEMA 4X<br>Thermoplastic | \$189.00 |
| <b>664X63D*</b> | Enclosed, 60A, 3-pole, NEMA 4X | 66033D Rotary   | 60       | 3     | 3     |                          | \$237.00 |

\*Switch is not available as a separate item

## NEMA 4X Enclosed Rotary Switch AC Motor Controller Accessories

| Part Number    | Description                                                                                                                             | Price   |
|----------------|-----------------------------------------------------------------------------------------------------------------------------------------|---------|
| <b>30003FG</b> | Finger Guards; red; for use with 30A and 40A Switches (Set of 2)                                                                        | \$11.00 |
| <b>660AC*</b>  | SPDT Auxiliary contact NO / NC; includes one contact for use with push-on terminals; use with 664X33D and 664X63D                       | \$27.00 |
| <b>6610MK</b>  | Rotary handle replacement kit, use with 664X33D and 664X63D. (Nema 1 rating) Must use gasket replacement kit 664XWP for NEMA 4X rating. | \$22.00 |
| <b>664XWP</b>  | NEMA 4X enclosure gasket replacement kit; includes 4 seals, neoprene bushing and 3 o-rings; use with 664X33D and 664X63D                | \$14.00 |
| <b>664XFT</b>  | NEMA 4X enclosure mounting feet                                                                                                         | \$13.00 |
| <b>6603N</b>   | NEMA 4X enclosure neutral buss connector                                                                                                | \$63.00 |

\*660AC Terminal is a quick connect terminal #250