




| Toggle Switch AC Motor Controllers / Disconnects | | | | | | |
|--|---|----------|-------|-------|---------------|----------|
| Part Number | Description | Amperage | Phase | Poles | Wired | Price |
| 30002D | Switch only, 30A, 2-pole, 15 HP @ 600 VAC - Standard Toggle | 30 | 1 | 2 | Back and Side | \$40.50 |
| 30003D | Switch only, 30A, 3-pole, 20 HP @ 600 VAC - Standard Toggle | 30 | 3 | 3 | Back and Side | \$85.00 |
| 4002* | Switch only, 40A, 2-pole, 5 HP @ 600 VAC - Standard Toggle | 40 | 1 | 2 | Side | \$41.50 |
| 40002D | Switch only, 40A, 2-pole, 15 HP @ 600 VAC - Standard Toggle | 40 | 1 | 2 | Side | \$71.00 |
| 40003D | Switch only, 40A, 3-pole, 20 HP @ 600 VAC - Standard Toggle | 40 | 3 | 3 | Side | \$115.00 |
| 60002D | Switch only, 60A, 2-pole, 20 HP @ 600 VAC - Standard Toggle | 60 | 1 | 2 | Back | \$124.00 |
| 60003D | Switch only, 60A, 3-pole, 30 HP @ 600 VAC - Standard Toggle | 60 | 3 | 3 | Back | \$152.00 |

*Motor controller only ("Not suitable as disconnect")

| Toggle Switch AC Motor Controller Accessories | | |
|---|--|---------|
| Part Number | Description | Price |
| 30003FG | Finger guards; red; for use with 30A and 40A Switches (Set of 2) | \$11.00 |
| 30100 | NEMA 1 enclosure without switch, use with 30002D and 30003D | \$25.50 |



**Example
Back and Side
Wired**



| Enclosed Toggle Switch AC Motor Controllers / Disconnects | | | | | | | |
|---|---------------------------------|--------------------------|----------|-------|-------|-----------------------|----------|
| Part Number | Description | Included Switch | Amperage | Phase | Poles | Enclosure | Price |
| 30102D | Enclosed, 30A, 2-pole, NEMA 1 | 30002D Standard Toggle | 30 | 1 | 2 | NEMA 1Metal | \$52.00 |
| 30103D | Enclosed, 30A, 3-pole, NEMA 1 | 30003D Standard Toggle | 30 | 3 | 3 | | \$114.00 |
| 30302D | Enclosed, 30A, 2-pole, Aluminum | 30002D Standard Toggle | 30 | 1 | 2 | NEMA 3RMetal | \$78.00 |
| 30303D | Enclosed, 30A, 3-pole, Aluminum | 30003D Standard Toggle | 30 | 3 | 3 | | \$139.00 |
| 30322D* | Enclosed, 30A, 2-pole, Plastic | 30002DS Short Toggle | 30 | 1 | 2 | NEMA 3R Thermoplastic | \$90.00 |
| 30323D* | Enclosed, 30A, 3-pole, Plastic | 30003DS Short Toggle | 30 | 3 | 3 | | \$96.00 |
| 60302D* | Enclosed, 60A, 2-pole, Aluminum | 60002FWD Standard Toggle | 60 | 1 | 2 | NEMA 3R Metal | \$181.00 |
| 60303D* | Enclosed, 60A, 3-pole, Aluminum | 60003FWD Standard Toggle | 60 | 3 | 3 | | \$211.00 |

*Switch is not available as a separate item

| NEMA 4X Enclosed Rotary Switch AC Motor Controllers / Disconnects | | | | | | | |
|---|--------------------------------|-----------------|----------|-------|-------|-----------------------|----------|
| Part Number | Description | Included Switch | Amperage | Phase | Poles | Enclosure | Price |
| 664X33D* | Enclosed, 30A, 3-pole, NEMA 4X | 66033D Rotary | 30 | 3 | 3 | NEMA 4X Thermoplastic | \$189.00 |
| 664X63D* | Enclosed, 60A, 3-pole, NEMA 4X | 66033D Rotary | 60 | 3 | 3 | | \$237.00 |

*Switch is not available as a separate item



| NEMA 4X Enclosed Rotary Switch AC Motor Controller Accessories | | |
|--|---|---------|
| Part Number | Description | Price |
| 30003FG | Finger Guards; red; for use with 30A and 40A Switches (Set of 2) | \$11.00 |
| 660AC* | SPDT Auxiliary contact NO / NC; includes one contact for use with push-on terminals; use with 664X33D and 664X63D | \$27.00 |
| 6610MK | Rotary handle replacement kit, use with 664X33D and 664X63D. (Nema 1 rating) Must use gasket replacement kit 664XWP for NEMA 4X rating. | \$22.00 |
| 664XWP | NEMA 4X enclosure gasket replacement kit; includes 4 seals, neoprene bushing and 3 o-rings; use with 664X33D and 664X63D | \$14.00 |
| 664XFT | NEMA 4X enclosure mounting feet | \$13.00 |
| 6603N | NEMA 4X enclosure neutral buss connector | \$63.00 |

*660AC Terminal is a quick connect terminal #250