


# WA-F1/F2 Panels for Single-Door Freestanding Enclosures



## Description

- Panels for single-door single-access and single-door dual-access, freestanding NEMA 12, and freestanding NEMA 4 enclosures
- Can be positioned anywhere along horizontal depth-wise mounting channels
- Half-height panels can be located in the upper or lower portion of the enclosure
- Mounting hardware is furnished with each panel
- Painted steel subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- May be used in two-door enclosures along with other freestanding accessories

| <i>Painted Steel</i>    | <i>Price</i> | <i>Galvanized</i>        | <i>Price</i> | <i>Steel Gauge</i> | <i>Panel Size HxW</i>      | <i>Subpanel Type</i> |
|-------------------------|--------------|--------------------------|--------------|--------------------|----------------------------|----------------------|
| <b><u>WA60P24F1</u></b> | \$359.00     | —                        | —            | 12                 | 48.00 x 20.00 [1219 x 508] | Full                 |
| <b><u>WA60P24F2</u></b> | \$259.00     | —                        | —            | 10                 | 24.88 x 20.00 [632 x 508]  | Half                 |
| <b><u>WA60P36F1</u></b> | \$463.00     | <b><u>WA60P36F1G</u></b> | \$463.00     | 12                 | 48.00 x 32.00 [1219 x 813] | Full                 |
| <b><u>WA60P36F2</u></b> | \$292.00     | <b><u>WA60P36F2G</u></b> | \$292.00     | 12                 | 24.88 x 32.00 [632 x 813]  | Half                 |
| <b><u>WA72P24F1</u></b> | \$402.00     | <b><u>WA72P24F1G</u></b> | \$402.00     | 12                 | 60.00 x 20.00 [1524 x 508] | Full                 |
| <b><u>WA72P30F1</u></b> | \$468.00     | <b><u>WA72P30F1G</u></b> | \$506.00     | 12                 | 60.00 x 26.00 [1524 x 660] | Full                 |
| <b><u>WA72P36F1</u></b> | \$533.00     | <b><u>WA72P36F1G</u></b> | \$533.00     | 12                 | 60.00 x 32.00 [1524 x 813] | Full                 |
| <b><u>WA90P24F1</u></b> | \$468.00     | <b><u>WA90P24F1G</u></b> | \$468.00     | 12                 | 78.00 x 20.00 [1981 x 508] | Full                 |
| <b><u>WA90P36F1</u></b> | \$637.00     | <b><u>WA90P36F1G</u></b> | \$637.00     | 12                 | 78.00 x 32.00 [1981 x 813] | Full                 |


Notes: Dimensions in inches [millimeters].

Letters in table correspond to letters on dimensional drawing.


If used in a two-door enclosure, a center panel support must be ordered.

Suffix F1= full panel, F2 = half panel

## Dimensions



# WA-SMP Series Side-Mount Panels for Freestanding Enclosures



## Description

- Panels for freestanding NEMA 4 and freestanding NEMA 12 enclosures
- Panels are fabricated from 12-gauge steel
- They provide extra mounting space on the sides of the enclosure
- Mounting hardware is furnished with each panel
- Painted steel subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- Panels attach securely to mounting channels

| Painted Steel    | Price    | Panel Size AxB             |
|------------------|----------|----------------------------|
| <b>WA72SMP14</b> | \$248.00 | 60.00 x 14.00 [1524 x 356] |
| <b>WA72SMP20</b> | \$303.00 | 60.00 x 20.00 [1524 x 508] |

Note: Dimensions in inches [millimeters].

## Dimensions

