


# WA-F1/F2 Panels for Single-Door Freestanding Enclosures



## Description

- Panels for single-door single-access and single-door dual-access, freestanding NEMA 12, and freestanding NEMA 4 enclosures
- Can be positioned anywhere along horizontal depth-wise mounting channels
- Half-height panels can be located in the upper or lower portion of the enclosure
- Mounting hardware is furnished with each panel
- Painted steel subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- May be used in two-door enclosures along with other freestanding accessories

Painted Steel	Price	Galvanized	Price	Steel Gauge	Panel Size HxW	Subpanel Type
<a href="#"><u>WA60P24F1</u></a>	\$342.00	—	—	12	48.00 x 20.00 [1219 x 508]	Full
<a href="#"><u>WA60P24F2</u></a>	\$246.00	—	—	10	24.88 x 20.00 [632 x 508]	Half
<a href="#"><u>WA60P36F1</u></a>	\$441.00	<a href="#"><u>WA60P36F1G</u></a>	\$441.00	12	48.00 x 32.00 [1219 x 813]	Full
<a href="#"><u>WA60P36F2</u></a>	\$278.00	<a href="#"><u>WA60P36F2G</u></a>	\$278.00	12	24.88 x 32.00 [632 x 813]	Half
<a href="#"><u>WA72P24F1</u></a>	\$383.00	<a href="#"><u>WA72P24F1G</u></a>	\$383.00	12	60.00 x 20.00 [1524 x 508]	Full
<a href="#"><u>WA72P30F1</u></a>	\$445.00	<a href="#"><u>WA72P30F1G</u></a>	\$482.00	12	60.00 x 26.00 [1524 x 660]	Full
<a href="#"><u>WA72P36F1</u></a>	\$507.00	<a href="#"><u>WA72P36F1G</u></a>	\$507.00	12	60.00 x 32.00 [1524 x 813]	Full
<a href="#"><u>WA90P24F1</u></a>	\$445.00	<a href="#"><u>WA90P24F1G</u></a>	\$445.00	12	78.00 x 20.00 [1981 x 508]	Full
<a href="#"><u>WA90P36F1</u></a>	\$607.00	<a href="#"><u>WA90P36F1G</u></a>	\$607.00	12	78.00 x 32.00 [1981 x 813]	Full


Notes: Dimensions in inches [millimeters].

Letters in table correspond to letters on dimensional drawing.


If used in a two-door enclosure, a center panel support must be ordered.

Suffix F1= full panel, F2 = half panel

## Dimensions



# WA-SMP Series Side-Mount Panels for Freestanding Enclosures



## Description

- Panels for freestanding NEMA 4 and freestanding NEMA 12 enclosures
- Panels are fabricated from 12-gauge steel
- They provide extra mounting space on the sides of the enclosure
- Mounting hardware is furnished with each panel
- Painted steel subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- Panels attach securely to mounting channels

Painted Steel	Price	Panel Size AxB
<b>WA72SMP14</b>	\$236.00	60.00 x 14.00 [1524 x 356]
<b>WA72SMP20</b>	\$288.00	60.00 x 20.00 [1524 x 508]

Note: Dimensions in inches [millimeters].

## Dimensions

