



# Bayonet Mounting Adapter for Temperature Sensors

| Bayonet Mounting Adapter for Temperature Sensors |                                                                                                        |                       |             |        |         |
|--------------------------------------------------|--------------------------------------------------------------------------------------------------------|-----------------------|-------------|--------|---------|
| Part Number                                      | Description                                                                                            | Material              | Pcs/<br>Pkg | Wt(lb) | Price   |
| <a href="#"><u>BA-078</u></a>                    | Bayonet adapter, 7/8 inch long, 7/16 inch outside diameter, 9/32 inch inside diameter, 1/8 inch MNPT   | Stainless Steel (304) | 1           | 0.5    | \$1.75  |
| <a href="#"><u>BA-100</u></a>                    | Bayonet adapter, 1 inch long, 7/16 inch outside diameter, 9/32 inch inside diameter, 1/8 inch MNPT     |                       | 1           | 0.5    | \$1.75  |
| <a href="#"><u>BA-114</u></a>                    | Bayonet adapter, 1-1/4 inch long, 7/16 inch outside diameter, 9/32 inch inside diameter, 1/8 inch MNPT |                       | 1           | 0.5    | \$2.25  |
| <a href="#"><u>BA-112</u></a>                    | Bayonet adapter, 1-1/2 inch long, 7/16 inch outside diameter, 9/32 inch inside diameter, 1/8 inch MNPT |                       | 1           | 0.5    | \$2.25  |
| <a href="#"><u>BA-200</u></a>                    | Bayonet adapter, 2 inch long, 7/16 inch outside diameter, 9/32 inch inside diameter, 1/8 inch MNPT     |                       | 1           | 0.5    | \$2.50  |
| <a href="#"><u>BA-212</u></a>                    | Bayonet adapter, 2-1/2 inch long, 7/16 inch outside diameter, 9/32 inch inside diameter, 1/8 inch MNPT |                       | 1           | 0.5    | \$2.75  |
| <a href="#"><u>BA-300</u></a>                    | Bayonet adapter, 3 inch long, 7/16 inch outside diameter, 9/32 inch inside diameter, 1/8 inch MNPT     |                       | 1           | 0.5    | \$3.00  |
| <a href="#"><u>BA-312</u></a>                    | Bayonet adapter, 3-1/2 inch long, 7/16 inch outside diameter, 9/32 inch inside diameter, 1/8 inch MNPT |                       | 1           | 0.5    | \$3.50  |
| <a href="#"><u>CF18-BC</u></a>                   | Adjustable bayonet compression fitting, for 1/8" diameter probe sheath sensors                         | Brass                 | 1           | 0.1    | \$10.50 |
| <a href="#"><u>BB125N-50N</u></a>                | Reducing bushing, 1/2 MNPT x 1/8 FNPT, hex head                                                        |                       | 1           | 0.1    | \$6.00  |

[BA-078](#)[BA-100](#)[BA-114](#)[BA-112](#)[BA-200](#)[BA-212](#)[BA-300](#)[BA-312](#)[CF18-BC](#)[BB125N-50N](#)

*Note: Check the chemical compatibility of the sensor's wetted parts with the medium to be measured.*