



OKK Series Enclosure Kit – NEMA 12 Freestanding Single-Door with Window



Description

Each OKK Series enclosure kit contains all the components required to assemble one complete enclosure.

Kits do not include a plinth.

Material

- 2.0 mm carbon steel
- 4.0 mm acrylic window

Finish

- RAL 7035 light gray
- Textured powder coat finish

Listings

- Fully-assembled OKK Series enclosures are rated as follows:
 - UL 508a Type 12 [UL File E503249]
 - CSA Type 12 [CSA File 115232]
- Complies with the following:
 - NEMA Type 12
 - IEC EN60529 IP55



Create your own configuration using the link button or QR code below:

Configuration Tool



View assembly guide with the link button or QR code below:

Assembly Guide



OKK Series Enclosure Kit – NEMA12 Freestanding Single-Door with Window

Kit Number	Price	Assembled Size HxWxD	Kit Includes	Drawing Link
QTA-E180804CSWF	\$1,156.00	1800 x 800 x 400 [70.87 x 31.50 x 15.75]	(1) MTK180-4, (1) OKKTB8040, (1) PNA188, (1) DTE188, (1) RPE188 and (1) DLK184	PDF
QTA-E180806CSWF	\$1,227.00	1800 x 800 x 600 [70.87 x 31.50 x 23.62]	(1) MTK180-4, (1) OKKTB8060, (1) PNA188, (1) DTE188, (1) RPE188 and (1) DLK186	PDF
QTA-E180808CSWF	\$1,367.00	1800 x 800 x 800 [70.87 x 31.50 x 31.50]	(1) MTK180-4, (1) OKKTB8080, (1) PNA188, (1) DTE188, (1) RPE188 and (1) DLK188	PDF
QTA-E181004CSWF	\$1,284.00	1800 x 1000 x 400 [70.87 x 39.37 x 15.75]	(1) MTK180-4, (1) OKKTB1040, (1) PNA18A, (1) DTE18A, (1) RPE18A and (1) DLK184	PDF
QTA-E181006CSWF	\$1,364.00	1800 x 1000 x 600 [70.87 x 39.37 x 23.62]	(1) MTK180-4, (1) OKKTB1060, (1) PNA18A, (1) DTE18A, (1) RPE18A and (1) DLK186	PDF
QTA-E181008CSWF	\$1,518.00	1800 x 1000 x 800 [70.87 x 39.37 x 31.50]	(1) MTK180-4, (1) OKKTB1080, (1) PNA18A, (1) DTE18A, (1) RPE18A and (1) DLK188	PDF
QTA-E200804CSWF	\$1,315.00	2000 x 800 x 400 [78.74 x 31.50 x 15.75]	(1) MTK200-4, (1) OKKTB8040, (1) PNA208, (1) DTE208, (1) RPE208 and (1) DLK204	PDF
QTA-E200806CSWF	\$1,390.00	2000 x 800 x 600 [78.74 x 31.50 x 23.62]	(1) MTK200-4, (1) OKKTB8060, (1) PNA208, (1) DTE208, (1) RPE208 and (1) DLK206	PDF
QTA-E200808CSWF	\$1,530.00	2000 x 800 x 800 [78.74 x 31.50 x 31.50]	(1) MTK200-4, (1) OKKTB8080, (1) PNA208, (1) DTE208, (1) RPE208 and (1) DLK208	PDF
QTA-E201004CSWF	\$1,450.00	2000 x 1000 x 400 [78.74 x 39.37 x 15.75]	(1) MTK200-4, (1) OKKTB1040, (1) PNA20A, (1) DTE20A, (1) RPE20A and (1) DLK204	PDF
QTA-E201006CSWF	\$1,534.00	2000 x 1000 x 600 [78.74 x 39.37 x 23.62]	(1) MTK200-4, (1) OKKTB1060, (1) PNA20A, (1) DTE20A, (1) RPE20A and (1) DLK206	PDF
QTA-E201008CSWF	\$1,688.00	2000 x 1000 x 800 [78.74 x 39.37 x 31.50]	(1) MTK200-4, (1) OKKTB1080, (1) PNA20A, (1) DTE20A, (1) RPE20A and (1) DLK208	PDF

Note: Dimensions in millimeters [inches].