

# Enclosure Accessories

## Hole Seals



Your Enclosure Source®



Extra pushbutton holes can be sealed against dust, dirt, oil, and water with a SCE hole seal. Seals will cover most pushbutton hole sizes. Hole seals come with oil-resistant gasket, #10-32 x 3/8" stud, zinc plated wing nut, and plated steel back plate. Available in stainless steel or powder coated finish.

- Made of heavy gauge steel with ANSI 61 gray powder coat
- Stainless plate is made of Type 304 stainless with #4 brushed finish
- NEMA Type 3R, 4, 4X & 12
- UL Recognized Type 3R, 4, 4X & 12 [File # E69392]
- IEC 60529
- IP 56

SCE-LLB5

### Hole Seals

Part Number	Price	Material/Finish	Qty	Hole Size
<a href="#">SCE-ASPBG-RAL7035</a>	\$4.75	Steel - RAL 7035 Gray	1	22mm pushbutton
<a href="#">SCE-ASPB-RAL7035</a>	\$6.75	Steel - RAL 7035 Gray	1	30mm pushbutton
<a href="#">SCE-ASPBG-09</a>	\$4.75	Steel - ANSI 61 Gray	1	22mm pushbutton
<a href="#">SCE-ASPB-09</a>	\$6.75	Steel - ANSI 61 Gray	1	30mm pushbutton
<a href="#">SCE-ASPBG-05</a>	\$4.75	Steel - SCE-05 White	1	22mm pushbutton
<a href="#">SCE-ASPB-05</a>	\$6.75	Steel - SCE-05 White	1	30mm pushbutton
<a href="#">SCE-ASPBG-SS</a>	\$23.50	Stainless Steel	1	22mm pushbutton
<a href="#">SCE-ASPB-SS</a>	\$25.50	Stainless Steel	1	30mm pushbutton
<a href="#">SCE-ASPBG-09-25</a>	\$108.00	Steel - ANSI 61 Gray	25	22mm pushbutton
<a href="#">SCE-ASPB-09-25</a>	\$152.00	Steel - ANSI 61 Gray	25	30mm pushbutton

Note: Dimensions in inches [millimeters].



Designed to seal 2 inch square opening against dust, dirt, oil, and water. Hole seals are made of corrosion and UV resistant Polycarbonate material, supplied with adhesive gasket backing for quick, simple installation.

- UL Recognized 3, 3R, 4, 4X & 12
- IP56

### Square Hole Seal

Part Number	Price	Description	Drawing Link
<a href="#">SCE-HS2S</a>	\$7.50	61 gray, oil-resistant adhesive gasket, 2in square cutout.	PDF

Note: Dimensions in inches [millimeters].