

Hand Taps

Fractional and Metric Thread Hand Taps

High-speed steel fractional and metric size hand taps.



231100

High-Speed Steel Fractional Size Hand Taps

Coarse Thread	Part #	Pcs/Pkg	Price	Thread Size	Overall Length (in.)	Use With	Fine Thread	Part #	Pcs/Pkg	Price	Thread Size	Overall Length (in.)	Use With
	246080UNC3	1	\$10.50	8-32 UNC	1.77	2149029		246100UNF2	1	\$10.50	10-32 UNF	1.77	2149021
	246100UNC3	1	\$10.50	10-24 UNC	1.97	2149025							
	246014UNC3	1	\$6.25	1/4-20 UNC	1.97	2149007							
	246516UNC3	1	\$6.25	5/16-18 UNC	2.20	214900F							

High-Speed Steel Metric Hand Taps


Coarse Thread	Part #	Pcs/Pkg	Price	Thread Size	Overall Length (mm)	Use With	Fine Thread	Part #	Pcs/Pkg	Price	Thread Size	Overall Length (mm)	Use With
	231030	1	\$4.25	M3x0.5	40.0	214025 , 215025		235041-2	1	\$8.50	M4x0.5	45.0	214035 , 215035
	231040	1	\$4.25	M4x0.7	45.0	214033 , 215033		235050-2	1	\$9.00	M5x0.5	50.0	214045 , 215045
	231050	1	\$4.25	M5x0.8	50.0	214042 , 215042		235081-2	1	\$11.00	M8x1	56.0	214070 , 215070
	231060	1	\$4.50	M6x1	50.0	214050 , 215050		235122-2	1	\$12.00	M12x1	70.0	214110 , 215110
	231080	1	\$5.00	M8x1.25	56.0	214068 , 215068		235181-2	1	\$23.50	M18x1	80.0	17.0 mm
	231100	1	\$7.00	M10x1.5	70.0	214085 , 215085		235301-2	1	\$48.50	M30x1.5	90.0	28.5 mm
	231120	1	\$8.50	M12x1.75	75.0	214102 , 215102							

NPT Thread Hand Taps

High-speed steel National Pipe Taper hand taps.

High-Speed Steel NPT Hand Taps

Part #	Pcs/Pkg	Price	Thread Size	Overall Length (in.)	Use With
231116NPT	1	\$16.00	1/16-27 NPT	2.56	214813 , 250813T , 215813
231018NPT	1	\$14.50	1/8-27 NPT	2.56	214900R
231014NPT	1	\$15.50	1/4-18 NPT	2.76	214825 , 250825T , 215825
231038NPT	1	\$22.00	3/8-18 NPT	2.95	37/64"
231012NPT	1	\$27.00	1/2-14 NPT	3.15	23/32"




231038NPT

Conduit Thread Hand Taps

High-speed steel DIN 40430 conduit thread hand taps.

High-Speed Steel Conduit Thread Hand Taps

Part #	Pcs/Pkg	Price	Thread Size	Overall Length (mm)	Use With
264009	1	\$21.50	PG-9	70.0	14.0 mm
264011	1	\$29.50	PG-11	80.0	17.25 mm
264016	1	\$42.00	PG-16	80.0	21.25 mm
264021	1	\$63.00	PG-21	90.0	26.75 mm
264029	1	\$97.00	PG-29	100.0	35.5 mm



264029

RUKO Hand Taps

