

Enclosure Accessories

Mounting Feet



Multi-Door Mounting Feet

Part Number	Price	Material	Qty
<u>SCE-HDWMK</u>	\$104.00	carbon steel	4
<u>SCE-HDWMKSS</u>	\$136.00	stainless steel	4

Designed for use on SCE Multi-Door Wall-Mount enclosures.

- Four mounting feet per kit
- Made of heavy gauge stainless steel with a black textured finish
- Hardware included to fasten mounting kit to the enclosure




NEMA 3R Mounting Feet

Part Number	Price	Qty
<u>SCE-N3RMFK4</u>	\$34.50	4

Designed for use on large wall-mount NEMA 3R enclosures.

- Made of heavy gauge carbon steel and powder coated ANSI 61 gray
- Hardware included to fasten mounting feet to the enclosure



Enviroline Mounting Feet

Part Number	Price	Material	Qty
<u>SCE-ELMFK4</u>	\$23.50	Chemical and Corrosion resistant Polyamide	4
<u>SCE-ELMFK6</u>	\$31.50		6
<u>SCE-ELMFK4-25</u>	\$457.00		100
<u>SCE-ELMFK4SS6-OS</u>	\$71.00	stainless steel	4

- Made for use with all SCE Enviroline® Series enclosures and two-door wall-mount enclosures.
- For use in type 3, 3R, 4, 4X and 12 enclosures



Designed to attach to the bottom of the enclosure in the existing threaded holes. Allows for adjustments for uneven floors. Pads are zinc plated with a plastic base. Mounting hardware is included.



Enviroline Junction Mounting Feet

Part Number	Price	Material	Qty
<u>SCE-ELJMFK</u>	\$31.00	Chemical and Corrosion resistant Polyamide	4
<u>SCE-ELJMFKSS-OS</u>	\$65.00	stainless steel	4

Made for use with all SCE Enviroline® Series junction enclosures.

- Stainless steel fasteners
- Hardware included to fasten mounting feet to the enclosure



Workstation Leveling Pads

Part Number	Price	Thread Size	Height	Qty	Drawing Link
<u>SCE-LPD2</u>	\$49.50	3/8-16	2 [51]	4	<u>PDF</u>

Note: Dimensions in inches [millimeters].

Enclosure Accessories

Mounting Feet



SCE-XMAIMF24

Designed for use with freestanding type enclosures when the enclosure must be secured to a concrete floor or base.

- Two angle iron-mounting feet per kit.
- Made of heavy gauge carbon steel powder coated ANSI 61 gray
- Mounting hardware included to fasten feet to the enclosure
- UL Recognized sealing washer maintains environmental rating of the enclosure

Freestanding Enclosure Mounting Feet

Part Number	Price	For Enclosure Depth	Drawing Link
SCE-XMAIMF16	\$47.00	16in	PDF
SCE-XMAIMF18	\$51.00	18in	PDF
SCE-XMAIMF20	\$57.00	20in	PDF
SCE-XMAIMF24	\$68.00	24in	PDF

Enclosure Accessories

Mounting Flanges



- Made of heavy gauge carbon steel, powder coated ANSI 61 gray
- Vented 3R mounting flanges are white powder coat
- Two mounting flanges per kit
- Fastening hardware is included to attach flanges to the enclosure
- UL Recognized sealing washer maintains environmental rating of the enclosure to attach flanges to the enclosure



SCE-NMST10

NEMA 1 Enclosure Mounting Flanges


Part Number	Price	Enclosure Width	Drawing Link
SCE-NMST6	\$21.00	6 in	PDF
SCE-NMST8	\$22.50	8 in	PDF
SCE-NMST10	\$24.00	10 in	PDF
SCE-NMST12	\$25.50	12 in	PDF
SCE-NMST16	\$28.50	16 in	PDF
SCE-NMST20	\$31.00	20 in	PDF
SCE-NMST24	\$34.00	24 in	PDF



SCE-MST4

NEMA 3R Enclosure Mounting Flanges

Part Number	Price	Enclosure Width	Drawing Link
SCE-MST4	\$22.50	4 in	PDF
SCE-MST6	\$24.00	6 in	PDF
SCE-MST8	\$25.50	8 in	PDF
SCE-MST10	\$27.00	10 in	PDF
SCE-MST12	\$28.50	12 in	PDF
SCE-MST16	\$31.00	16 in	PDF
SCE-MST20	\$34.00	20 in	PDF
SCE-MST24	\$37.00	24 in	PDF



SCE-VRMS36

Vented Enclosure Mounting Flanges

Part Number	Price	Enclosure Width	Drawing Link
SCE-VRMS24	\$57.00	24 in	PDF
SCE-VRMS36	\$71.00	36 in	PDF

Enclosure Accessories

Enviroline Flush-Mounting Frames



Flush-mounting frames are designed for use with the Enviroline® Series wall-mount enclosures, quickly converting the wall-mount enclosure to a flush-mount enclosure. Two part numbers are required to complete the assembly: one part number for the height of the enclosure and one part number for the width of the enclosure. All kits are provided with hardware to assemble the frame to the enclosure and maintain the environmental rating of the enclosure.



SCE-ELFM12HSS



Material

- Frame is made of heavy gauge steel and finished with ANSI 61 gray powder coat
- "SS" parts are made of heavy gauge Type 316/316L stainless steel with #4 brushed finish

Enviroline Flush-Mounting Frames						
Carbon Steel	Price	316 Stainless Steel	Price	For Enclosure Height	For Enclosure Width	Drawing Link
SCE-ELFM12H	\$68.00	SCE-ELFM12HSS	\$163.00	12 [305]	—	PDF
SCE-ELFM16H	\$72.00	SCE-ELFM16HSS	\$174.00	16 [406]	—	PDF
SCE-ELFM20H	\$76.00	SCE-ELFM20HSS	\$181.00	20 [508]	—	PDF
SCE-ELFM24H	\$81.00	SCE-ELFM24HSS	\$194.00	24 [607]	—	PDF
SCE-ELFM30H	\$86.00	SCE-ELFM30HSS	\$207.00	30 [762]	—	PDF
SCE-ELFM36H	\$93.00	SCE-ELFM36HSS	\$224.00	36 [914]	—	PDF
SCE-ELFM12W	\$63.00	SCE-ELFM12WSS	\$150.00	—	12 [305]	PDF
SCE-ELFM16W	\$67.00	SCE-ELFM16WSS	\$160.00	—	16 [406]	PDF
SCE-ELFM20W	\$70.00	SCE-ELFM20WSS	\$168.00	—	20 [508]	PDF
SCE-ELFM24W	\$75.00	SCE-ELFM24WSS	\$181.00	—	24 [607]	PDF
SCE-ELFM30W	\$81.00	SCE-ELFM30WSS	\$194.00	—	30 [762]	PDF
SCE-ELFM36W	\$88.00	SCE-ELFM36WSS	\$211.00	—	36 [914]	PDF

Note: Dimensions in inches [millimeters].

Enclosure Accessories



Wall-Mount Standoffs



SCE-WMS1SS

Wall-mount standoffs are intended to provide space between a wall-mount enclosure and the wall for better wash down accessibility that is required in some applications. Provided with silicone seals to maintain seal between standoff and mounting surfaces. Maintains Type 4X rating. Four 304 stainless steel standoffs and eight silicone seals per kit.

Standoffs			
Part Number	Price	Length	Drawing Link
<u>SCE-WMS1SS</u>	\$142.00	1 [25]	<u>PDF</u>
<u>SCE-WMS2SS</u>	\$153.00	2 [51]	<u>PDF</u>
<u>SCE-WMS3SS</u>	\$174.00	3 [76]	<u>PDF</u>
<u>SCE-WMS4SS</u>	\$210.00	4 [102]	<u>PDF</u>
Note: Dimensions in inches [millimeters].			

Lifting Lugs



SCE-LLB5

Lifting lugs are designed to be mounted to the left and right side of a standard wall-mount type enclosure for easy handling of fully-wired enclosures. Mounting hardware is included. UL recognized sealing washers supplied to maintain UL ratings of Type 3R, 4, 4X and 12.

Lifting Lugs			
Part Number	Price	Material/Finish	Qty
<u>SCE-LLB5SS</u>	\$53.00	316 Stainless Steel, #4 Brush Finish	2
<u>SCE-LLB7</u>	\$40.50	Steel, White Powder Coat	2
<u>SCE-LLB5</u>	\$35.50	Steel, Zinc Plated	2
<u>SCE-LLB5-25</u>	\$680.00	Steel, Zinc Plated	25 sets of 2

Enclosure Accessories

Casters



- Swivel casters have ball bearing pivots and brakes
- Load rating 250 lbs for each caster



[SCE-CAKR](#)

Casters			
Part Number	Price	Description	Wheel Size
<u>SCE-CAKR</u>	\$145.00	Set of 4 - 2 Rigid, 2 Swivel	3in
<u>SCE-CAKS</u>	\$181.00	Set of 4 Swivel Casters	3in
<u>SCE-CAKR4</u>	\$218.00	Set of 4 - 2 Rigid, 2 Swivel	4in
<u>SCE-CAKS4</u>	\$254.00	Set of 4 Swivel Casters	4in

Enclosure Accessories

Drip Shields



Drip Shields for NEMA 4 and 12 Enclosures

<i>RAL 7035</i>	<i>Price</i>	<i>ANSI 61</i>	<i>Price</i>	<i>Fits Enclosure Width</i>
<u>SCE-DS12N4</u>	\$47.50	<u>SCE-DS12N4LG</u>	\$47.50	12 in
<u>SCE-DS16N4</u>	\$54.00	<u>SCE-DS16N4LG</u>	\$54.00	16 in
<u>SCE-DS20N4</u>	\$57.00	<u>SCE-DS20N4LG</u>	\$57.00	20 in
<u>SCE-DS24N4</u>	\$67.00	<u>SCE-DS24N4LG</u>	\$67.00	24 in
<u>SCE-DS30N4</u>	\$71.00	<u>SCE-DS30N4LG</u>	\$71.00	30 in
<u>SCE-DS36N4</u>	\$75.00	<u>SCE-DS36N4LG</u>	\$75.00	36 in
<u>SCE-DS42N4</u>	\$80.00	—	—	42 in
<u>SCE-DS48N4</u>	\$91.00	—	—	48 in
<u>SCE-DS60N4</u>	\$107.00	—	—	60 in
<u>SCE-DS72N4</u>	\$120.00	—	—	72 in

Protects door against dripping water and settling dust. Stainless steel screws and sealing washers are supplied with each kit. Made of steel and powder coated. Provided with cULus Recognized sealing washer to maintain Environmental Rating of the enclosure.

Stainless Steel Drip Shields for NEMA 4X Enclosures

<i>304 Stainless Steel</i>	<i>Price</i>	<i>316L Stainless Steel</i>	<i>Price</i>	<i>Fits Enclosure Width</i>
<u>SCE-DS12SS</u>	\$109.00	<u>SCE-DS12SS6</u>	\$131.00	12 in
<u>SCE-DS16SS</u>	\$119.00	<u>SCE-DS16SS6</u>	\$143.00	16 in
<u>SCE-DS20SS</u>	\$129.00	<u>SCE-DS20SS6</u>	\$154.00	20 in
<u>SCE-DS24SS</u>	\$139.00	<u>SCE-DS24SS6</u>	\$166.00	24 in
<u>SCE-DS30SS</u>	\$155.00	<u>SCE-DS30SS6</u>	\$186.00	30 in
<u>SCE-DS36SS</u>	\$172.00	<u>SCE-DS36SS6</u>	\$206.00	36 in
<u>SCE-DS42SS</u>	\$188.00	<u>SCE-DS42SS6</u>	\$226.00	42 in
<u>SCE-DS48SS</u>	\$211.00	<u>SCE-DS48SS6</u>	\$253.00	48 in
<u>SCE-DS60SS</u>	\$241.00	<u>SCE-DS60SS6</u>	\$289.00	60 in
<u>SCE-DS72SS</u>	\$287.00	<u>SCE-DS72SS6</u>	\$344.00	72 in

Protects door against dripping water and settling dust. Stainless steel screws and sealing washers are supplied with each kit. Made of type 304 or 316 stainless steel. Provided with cULus Recognized sealing washer to maintain Environmental Rating of the enclosure.