

NEMA 3R, 4, 4X, 12, and 13 Series Two-Door Floor-Mounted with 3-Point Hardware



Your Enclosure Source®



Applications

Designed to house electrical and electronic controls, instrumentation and components in indoor or outdoor locations. For outdoor applications a drip shield is recommended.

Construction

- 14-gauge carbon or stainless steel Type 304 and 316/316L
- Seams continuously welded and ground smooth
- Flange trough collar around all sides of door opening
- Collar studs are provided for mounting optional subpanels.
- Mounting hardware, sealing washers, and hole plugs are included.
- Stainless steel concealed hinges
- Removable and interchangeable doors
- Black zinc diecast keylocking/padlocking handles
- 3-point latching mechanism
- Black, 1/4-turn latches, as required
- Removable print pocket
- Poured-in-place oil- and water-resistant gasket
- Ground stud on door and body
- Removeable centerpost
- Heavy duty lifting eyes anchored into

reinforced top

- Body stiffeners
- 12 in. removeable floor stands
- Panel supports
- provisions for mechanical interlock

Finish

- Stainless Steel: #4 brushed finish on all exterior surfaces
- Carbon Steel: ANSI-61 gray powder coat
- Optional subpanels are powder coated white.

Listings

- NEMA Type 3R, 4, 4X (Stainless Steel Only), 12 and 13
- cULus Listed Type 3R, 4, 4X (Stainless Steel Only), and 12 [File E69392]
- IEC 60529 IP66

Shipping Schedule

Same day 1 - 15 days

Color indicates shipping lead time in business days.

NEMA 3R, 4, 12, and 13 Enviroline Series Two-Door with 3-Point Handle

Carbon Steel	Price	304 Stainless Steel	Price	316L Stainless Steel	Price	Size HxWxD	Drawing Link
SCE-60EL4812LPPL	\$2,635.00	SCE-60EL4812SSLPPL	\$5,729.00	SCE-60EL4812SS6LPPL	\$6,768.00	60.00 x 48.00 x 13.05 [1524 x 1219 x 331]	PDF
SCE-60EL4818LPPL	\$2,686.00	SCE-60EL4818SSLPPL	\$6,033.00	SCE-60EL4818SS6LPPL	\$7,135.00	60.00 x 48.00 x 19.05 [1524 x 1219 x 484]	PDF
SCE-60EL6012LPPL	\$2,888.00	SCE-60EL6012SSLPPL	\$6,403.00	SCE-60EL6012SS6LPPL	\$7,568.00	60.00 x 60.00 x 13.05 [1524 x 1524 x 331]	PDF
SCE-60EL6018LPPL	\$2,940.00	SCE-60EL6018SSLPPL	\$6,672.00	SCE-60EL6018SS6LPPL	\$7,892.00	60.00 x 60.00 x 19.05 [1524 x 1524 x 484]	PDF
SCE-72EL6012LPPL	\$3,228.00	SCE-72EL6012SSLPPL	\$7,275.00	SCE-72EL6012SS6LPPL	\$8,605.00	72.00 x 60.00 x 13.05 [1829 x 1524 x 331]	PDF
SCE-72EL6018LPPL	\$3,269.00	SCE-72EL6018SSLPPL	\$7,420.00	SCE-72EL6018SS6LPPL	\$8,777.00	72.00 x 60.00 x 19.05 [1829 x 1524 x 484]	PDF
SCE-72EL7212LPPL	\$3,618.00	SCE-72EL7212SSLPPL	\$7,910.00	SCE-72EL7212SS6LPPL	\$9,345.00	72.00 x 72.00 x 13.05 [1829 x 1829 x 331]	PDF
SCE-72EL7218LPPL	\$3,715.00	SCE-72EL7218SSLPPL	\$8,432.00	SCE-72EL7218SS6LPPL	\$9,975.00	72.00 x 72.00 x 19.05 [1829 x 1829 x 484]	PDF
SCE-72EL7224LPPL	\$4,202.00	SCE-72EL7224SSLPPL	\$8,873.00	SCE-72EL7224SS6LPPL	\$10,471.00	72.00 x 72.00 x 25.05 [1829 x 1829 x 636]	PDF

Note: Dimensions in inches [millimeters].

NEMA 3R, 4, 4X, 12, and 13 Series Two-Door Floor-Mounted with 3-Point Hardware



Your Enclosure Source®

Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

Subpanels for NEMA 3R, 4, 12, and 13 Enviroline Series Two-Door with 3-Point Handle

<i>Carbon Steel</i>	<i>304 Stainless Steel</i>	<i>316L Stainless Steel</i>	<i>Optional Subpanel</i>	<i>Price</i>
<u>SCE-60EL4812LPPL</u>	<u>SCE-60EL4812SSLPPL</u>	<u>SCE-60EL4812SS6LPPL</u>	<u>SCE-60P48</u>	\$373.00
<u>SCE-60EL4818LPPL</u>	<u>SCE-60EL4818SSLPPL</u>	<u>SCE-60EL4818SS6LPPL</u>	<u>SCE-60P48</u>	\$373.00
<u>SCE-60EL6012LPPL</u>	<u>SCE-60EL6012SSLPPL</u>	<u>SCE-60EL6012SS6LPPL</u>	<u>SCE-60P60</u>	\$460.00
<u>SCE-60EL6018LPPL</u>	<u>SCE-60EL6018SSLPPL</u>	<u>SCE-60EL6018SS6LPPL</u>	<u>SCE-60P60</u>	\$460.00
<u>SCE-72EL6012LPPL</u>	<u>SCE-72EL6012SSLPPL</u>	<u>SCE-72EL6012SS6LPPL</u>	<u>SCE-72P60</u>	\$548.00
<u>SCE-72EL6018LPPL</u>	<u>SCE-72EL6018SSLPPL</u>	<u>SCE-72EL6018SS6LPPL</u>	<u>SCE-72P60</u>	\$548.00
<u>SCE-72EL7212LPPL</u>	<u>SCE-72EL7212SSLPPL</u>	<u>SCE-72EL7212SS6LPPL</u>	<u>SCE-72P72</u>	\$654.00
<u>SCE-72EL7218LPPL</u>	<u>SCE-72EL7218SSLPPL</u>	<u>SCE-72EL7218SS6LPPL</u>	<u>SCE-72P72</u>	\$654.00
<u>SCE-72EL7224LPPL</u>	<u>SCE-72EL7224SSLPPL</u>	<u>SCE-72EL7224SS6LPPL</u>	<u>SCE-72P72</u>	\$654.00

Note: Dimensions in inches [millimeters].

NEMA 3R, 4, 4X, 12, and 13 Series Two-Door Floor-Mounted with 3-Point Hardware



Your Enclosure Source®

Dimensions

