

NEMA 4, 12, and 13 Extra-Deep Wall-Mount Pushbutton



Applications

Designed to offer protection for oil-tight pushbuttons, switches, and pilot lights from dust, water, dirt and oil.

Construction

- 16-gauge carbon steel
- Continuously-welded seams
- Captivated cover screws thread into sealed wells.
- 4-way pushbutton holes accept all brands of oil-tight pushbuttons, switches and pilot lights
- Hole diameter is 1.20in [30.5 mm] or 0.87in [22.5 mm]
- Poured-in-place oil- and water-resistant gasket
- Welded mounting provision top and bottom of back

Finish

- ANSI 61 gray or RAL 1018 yellow powder coated inside and out

Listings

- NEMA Type 4, 12 and 13
- cULus Listed Type 4 and 12 [File E69392]
- IEC 60529 IP66



Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

NEMA 4, 12, and 13 Extra-Deep Wall-Mount Pushbutton

ANSI 61 Gray			RAL 1018 Yellow		Size HxWxD	Holes	Drawing Link
22mm	30mm	Price	30mm	Price			
SCE-1PBXI	SCE-1PBX	\$73.00	SCE-1PBX-RAL1018	\$86.00	4.31 x 4.31 x 4.91 [109 x 109 x 125]	1	PDF
SCE-2PBXI	SCE-2PBX	\$84.00	SCE-2PBX-RAL1018	\$99.00	6.31 x 4.31 x 4.91 [160 x 109 x 125]	2	PDF
SCE-3PBXI	SCE-3PBX	\$95.00	SCE-3PBX-RAL1018	\$111.00	8.31 x 4.31 x 4.91 [211 x 109 x 125]	3	PDF
SCE-4PBXI	SCE-4PBX	\$105.00	SCE-4PBX-RAL1018	\$123.00	10.31 x 4.31 x 4.91 [262 x 109 x 125]	4	PDF
SCE-4SPBXI	SCE-4SPBX	\$106.00	SCE-4SPBX-RAL1018	\$119.00	7.56 x 6.56 x 4.91 [192 x 167 x 125]	4	PDF
—	—	—	SCE-5PBX-RAL1018	\$136.00	12.31 x 4.31 x 4.91 [313 x 109 x 125]	5	PDF
SCE-6PBXI	SCE-6PBX	\$123.00	SCE-6PBX-RAL1018	\$147.00	9.81 x 6.56 x 4.91 [249 x 167 x 125]	6	PDF
SCE-6PBXVLI	SCE-6PBXVL	\$123.00	—	—	15.06 x 4.31 x 4.91 [383 x 109 x 125]	6	PDF
SCE-9PBXI	SCE-9PBX	\$139.00	—	—	9.81 x 8.81 x 4.91 [249 x 224 x 125]	9	PDF
SCE-10PBXI	SCE-10PBX	\$152.00	—	—	14.31 x 6.56 x 4.91 [363 x 167 x 125]	10	PDF
SCE-12PBXI	SCE-12PBX	\$160.00	—	—	12.06 x 8.81 x 4.91 [306 x 224 x 125]	12	PDF

Note: Dimensions in inches [millimeters].

NEMA 4, 12, and 13 Extra-Deep Wall-Mount Pushbutton



Dimensions

