

Enclosure Accessories

Breather Vent



Designed for indoor or outdoor applications to handle the large negative pressure differential caused in a tightly sealed enclosure in extreme weather conditions or wash down applications that draw water into the enclosure. Adding a breather vent will equalize this pressure differential. Installed on the side of your enclosure as a breather or installed on the bottom as a drain and vent.

- Made of corrosion and UV resistant Polycarbonate material.
- cULus Recognized 1, 2, 3, 3R, 3RX, 3S, 4, 4X and 12 [File E69392]



Breather Vent			
Part Number	Price	Size (HxWxD)	Drawing Link
<u>SCE-BVK</u>	\$30.00	2.75 x 2.00 x 1.50 [70 x 51 x 38]	PDF
Note: Dimensions in inches [millimeters].			

Breather Vent Drain



This breather drain vent is designed for installation on the bottom of an enclosure as a drain and vent.

- UL Recognized Type 1,2,3,3R,3RX,3S,4,4X and 12. UL File E69392



Breather Vent Drain			
Part Number	Price	Size (HxWxD)	Drawing Link
<u>SCE-BVKD</u>	\$13.75	2.00 x 2.00 x 2.00 [51 x 51 x 51]	PDF
Note: Dimensions in inches [millimeters].			

Enclosure Accessories

Louver Vent Kits and Filters



SCE-AVK23

Designed for ventilation in enclosures where excessive heat or moisture is a problem. Kits may be installed in the field by making a cutout of the proper size. Louver vents are made of heavy gauge steel and powder coated ANSI 61 gray. "SS" parts are made of Type 304 stainless steel with #4 brushed finish.

Louver Vent Kit							
Carbon Steel	Price	304 Stainless Steel	Price	Size (HxW)	Cutout Size (HxW)	Drawing Link	Optional Filter Assembly
SCE-AVK23	\$24.00	SCE-AVK23SS	\$52.00	3.25 x 3.25 [83 x 83]	2.00 x 1.75 [51 x 44]	PDF	—
SCE-AVK33	\$25.00	SCE-AVK33SS	\$55.00	3.88 x 4.50 [99 x 114]	2.62 x 3.00 [67 x 76]	PDF	SCE-FLT33
SCE-AVK34	\$26.50	SCE-AVK34SS	\$58.00	4.50 x 5.50 [114 x 140]	3.25 x 4.00 [83 x 102]	PDF	SCE-FLT34
SCE-AVK43	\$27.50	SCE-AVK43SS	\$60.00	4.75 x 4.50 [121 x 114]	3.50 x 3.00 [89 x 76]	PDF	SCE-FLT43
SCE-AVK44	\$29.00	SCE-AVK44SS	\$63.00	5.63 x 5.50 [143 x 140]	4.38 x 4.00 [111 x 102]	PDF	SCE-FLT44
SCE-AVK64	\$31.50	SCE-AVK64SS	\$69.00	5.63 x 7.50 [143 x 191]	4.38 x 6.00 [111 x 152]	PDF	SCE-FLT64
SCE-AVK66	\$32.50	SCE-AVK66SS	\$70.00	5.91 x 9.50 [150 x 241]	4.56 x 8.00 [116 x 203]	PDF	SCE-FLT66
SCE-AVK84	\$34.00	SCE-AVK84SS	\$72.00	7.88 x 7.50 [200 x 191]	6.62 x 6.00 [168 x 152]	PDF	SCE-FLT84
SCE-AVK86	\$38.00	SCE-AVK86SS	\$74.00	8.18 x 9.50 [208 x 241]	6.94 x 8.00 [176 x 203]	PDF	SCE-FLT86
SCE-AVK88	\$42.50	SCE-AVK88SS	\$83.00	10.56 x 9.50 [268 x 241]	9.31 x 8.00 [236 x 203]	PDF	SCE-FLT88
SCE-AVK812	\$50.00	SCE-AVK812SS	\$110.00	15.31 x 9.50 [389 x 241]	14.06 x 8.00 [357 x 203]	PDF	SCE-FLT812

Note: Dimensions in inches [millimeters].

Designed for use with louver kit. Consists of aluminum filter brackets with mounting holes to align with louver mounting holes and a washable aluminum air filter to provide good air filtration.



SCE-FLT33

Filter Assembly				
Part Number	Price	Height	Width	Drawing Link
SCE-FLT33	\$32.50	3.22 [82]	3.25 [83]	PDF
SCE-FLT34	\$32.50	4.09 [104]	3.25 [83]	PDF
SCE-FLT43	\$32.50	3.84 [98]	4.25 [108]	PDF
SCE-FLT44	\$32.50	4.97 [126]	4.25 [108]	PDF
SCE-FLT64	\$36.00	4.45 [113]	6.25 [159]	PDF
SCE-FLT66	\$36.00	6.72 [171]	6.25 [159]	PDF
SCE-FLT84	\$39.50	4.64 [118]	8.25 [210]	PDF
SCE-FLT86	\$39.50	7.02 [178]	8.25 [210]	PDF
SCE-FLT88	\$39.50	9.39 [239]	8.25 [210]	PDF
SCE-FLT812	\$43.00	14.14 [359]	8.25 [210]	PDF

Note: Dimensions in inches [millimeters].