

Enclosure Subpanels

Galvanized Steel



Your Enclosure Source®

Subpanels are constructed from galvanized or galvanized steel for direct bonding of electrical components. Size determines steel thickness.

- Flat Subpanels are 0.075in. Galvanized
- Bent Subpanels are 0.125in. Galvanized



Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

Galvanized Subpanels

Part Number	Price	Size HxW	Fits Enclosure Size HxW	Finish	Drawing Link
SCE-6P4GALV	\$4.00	5.00 x 3.00 [127 x 76]	6 x 4 [152 x 102]		PDF
SCE-6P6GALV	\$4.75	5.00 x 5.00 [127 x 127]	6 x 6 [152 x 152]		PDF
SCE-8P6GALV	\$5.50	7.00 x 5.00 [178 x 127]	8 x 6 [203 x 152]		PDF
SCE-8P8GALV	\$6.50	7.00 x 7.00 [178 x 178]	8 x 8 [203 x 203]		PDF
SCE-10P8GALV	\$7.50	9.00 x 7.00 [229 x 178]	10 x 8 [254 x 203]		PDF
SCE-10P10GALV	\$9.00	9.00 x 9.00 [229 x 229]	10 x 10 [254 x 254]		PDF
SCE-12P6GALV	\$7.25	11.00 x 5.00 [279 x 127]	12 x 6 [305 x 152]		PDF
SCE-12P10GALV	\$10.25	11.00 x 9.00 [279 x 229]	12 x 10 [305 x 254]		PDF
SCE-12DLP12GALV	\$19.00	9.00 x 9.00 [229 x 229]	12 x 12 [305 x 305]		PDF
SCE-12P12GALV	\$12.00	11.00 x 11.00 [279 x 279]	12 x 12 [305 x 305]		PDF
SCE-12P24GALV	\$38.50	9.00 x 21.00 [229 x 533]	12 x 24 [305 x 610]		PDF
SCE-14P8GALV	\$9.75	13.00 x 7.00 [330 x 178]	14 x 8 [356 x 203]		PDF
SCE-14P12GALV	\$13.50	13.00 x 11.00 [330 x 279]	14 x 12 [356 x 305]		PDF
SCE-16P10GALV	\$13.25	15.00 x 9.00 [381 x 229]	16 x 10 [406 x 254]		PDF
SCE-16P12GALV	\$20.50	13.00 x 9.00 [330 x 229]	16 x 12 [406 x 305]		PDF
SCE-16DLP14GALV	\$24.50	13.00 x 11.00 [330 x 279]	16 x 14 [406 x 356]		PDF

Note: Dimensions in inches [millimeters].

Table continued on next page

Enclosure Subpanels

Galvanized Steel



Shipping Schedule	
Same day	1 - 15 days
Color indicates shipping lead time in business days.	

Table continued from previous page.

Galvanized Subpanels					
Part Number	Price	Size HxW	Fits Enclosure Size HxW	Finish	Drawing Link
SCE-16P14GALV	\$26.50	15.00 x 13.00 [381 x 330]	16 x 14 [406 x 356]		PDF
SCE-16P16GALV	\$34.00	13.00 x 13.00 [330 x 330]	16 x 16 [406 x 406]		PDF
SCE-20P12GALV	\$32.00	17.00 x 9.00 [432 x 229]	20 x 12 [508 x 305]		PDF
SCE-20P16GALV	\$42.00	17.00 x 13.00 [432 x 330]	20 x 16 [508 x 406]		PDF
SCE-20P16JGALV	\$40.50	19.00 x 15.00 [483 x 381]	20 x 16 [508 x 406]		PDF
SCE-20P20GALV	\$49.00	17.00 x 17.00 [432 x 432]	20 x 20 [508 x 508]		PDF
SCE-24P16GALV	\$45.50	21.00 x 13.00 [533 x 330]	24 x 16 [610 x 406]		PDF
SCE-24P20GALV	\$66.00	21.00 x 17.00 [533 x 432]	24 x 20 [610 x 508]		PDF
SCE-24P24GALV	\$78.00	21.00 x 21.00 [533 x 533]	24 x 24 [610 x 610]		PDF
SCE-30P16GALV	\$66.00	27.00 x 13.00 [686 x 330]	30 x 16 [762 x 406]		PDF
SCE-30P20GALV	\$81.00	27.00 x 17.00 [686 x 432]	30 x 20 [762 x 508]		PDF
SCE-30P24GALV	\$92.00	27.00 x 21.00 [686 x 533]	30 x 24 [762 x 610]		PDF
SCE-30P30GALV	\$122.00	27.00 x 27.00 [686 x 686]	30 x 30 [762 x 762]		PDF
SCE-36P16GALV	\$78.00	33.00 x 13.00 [838 x 330]	36 x 16 [914 x 406]		PDF
SCE-36P24GALV	\$111.00	33.00 x 21.00 [838 x 533]	36 x 24 [914 x 610]		PDF
SCE-36P30GALV	\$155.00	33.00 x 27.00 [838 x 686]	36 x 30 [914 x 762]		PDF
SCE-36P36GALV	\$182.00	33.00 x 33.00 [838 x 838]	36 x 36 [914 x 914]		PDF
SCE-40P24GALV	\$131.00	37.00 x 21.00 [940 x 533]	40 x 24 [1016 x 610]		PDF
SCE-42P24GALV	\$139.00	39.00 x 21.00 [991 x 533]	42 x 24 [1067 x 610]		PDF
SCE-42P30GALV	\$178.00	39.00 x 27.00 [991 x 686]	42 x 30 [1067 x 762]		PDF
SCE-42P36GALV	\$218.00	39.00 x 33.00 [991 x 838]	42 x 36 [1067 x 914]		PDF
SCE-42P42GALV	\$251.00	39.00 x 39.00 [991 x 991]	42 x 42 [1067 x 1067]		PDF
SCE-48P24GALV	\$151.00	45.00 x 21.00 [1143 x 533]	48 x 24 [1219 x 610]		PDF
SCE-48P30GALV	\$197.00	45.00 x 27.00 [1143 x 686]	48 x 30 [1219 x 762]		PDF
SCE-48P36GALV	\$247.00	45.00 x 33.00 [1143 x 838]	48 x 36 [1219 x 914]		PDF
SCE-48P42GALV	\$283.00	45.00 x 39.00 [1143 x 991]	48 x 42 [1219 x 1067]		PDF
SCE-48P48GALV	\$340.00	44.00 x 44.00 [1118 x 1118]	48 x 48 [1219 x 1219]		PDF
SCE-60BFP42GALV	\$368.00	56.00 x 38.00 [1422 x 965]	60 x 42 [1524 x 1067]		PDF
SCE-60P24GALV	\$197.00	57.00 x 21.00 [1448 x 533]	60 x 24 [1524 x 610]		PDF
SCE-60P30GALV	\$255.00	57.00 x 27.00 [1448 x 686]	60 x 30 [1524 x 762]		PDF
SCE-60P36GALV	\$303.00	57.00 x 33.00 [1448 x 838]	60 x 36 [1524 x 914]		PDF
SCE-60P48GALV	\$428.00	56.00 x 44.00 [1422 x 1118]	60 x 48 [1524 x 1219]		PDF
SCE-60P60GALV	\$529.00	56.00 x 56.00 [1422 x 1422]	60 x 60 [1524 x 1524]		PDF
SCE-64P25GALV	\$255.00	60.00 x 21.75 [1524 x 552]	64 x 25 [1626 x 635]		PDF
SCE-64P31GALV	\$267.00	60.00 x 27.75 [1524 x 705]	64 x 31 [1626 x 787]		PDF
SCE-64P37GALV	\$291.00	60.00 x 33.75 [1524 x 857]	64 x 37 [1626 x 940]		PDF
SCE-64P52GALV	\$534.00	60.00 x 48.00 [1524 x 1219]	64 x 52 [1626 x 1321]		PDF
SCE-64P64GALV	\$628.00	60.00 x 60.00 [1524 x 1524]	64 x 64 [1626 x 1626]		PDF

Note: Dimensions in inches [millimeters].

Table continued on next page

Enclosure Subpanels

Galvanized Steel (cont.)



Your Enclosure Source®

Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

Table continued from previous page.

Galvanized Subpanels					
Part Number	Price	Size HxW	Fits Enclosure Size HxW	Finish	Drawing Link
SCE-64P76GALV	\$738.00	60.00 x 72.00 [1524 x 1829]	64 x 76 [1626 x 1930]		PDF
SCE-72P30GALV	\$335.00	69.00 x 27.00 [1753 x 686]	72 x 30 [1829 x 762]		PDF
SCE-72P36GALV	\$360.00	69.00 x 33.00 [1753 x 838]	72 x 36 [1829 x 914]		PDF
SCE-72P60GALV	\$631.00	68.00 x 56.00 [1727 x 1422]	72 x 60 [1829 x 1524]		PDF
SCE-72P72GALV	\$817.00	68.00 x 68.00 [1727 x 1727]	72 x 72 [1829 x 1829]		PDF
SCE-76P37GALV	\$400.00	72.00 x 33.75 [1829 x 857]	76 x 37 [1930 x 940]		PDF
SCE-76P76GALV	\$865.00	72.00 x 72.00 [1829 x 1829]	76 x 76 [1930 x 1930]		PDF
SCE-82P37GALV	\$445.00	78.00 x 33.75 [1981 x 857]	82 x 37 [2083 x 940]		PDF
SCE-82P76GALV	\$870.00	78.00 x 72.00 [1981 x 1829]	82 x 76 [2083 x 1930]		PDF

Note: Dimensions in inches [millimeters].