

Enclosure Subpanels

Perforated



Perforated Subpanels have 1/8in mounting holes with 1/4in staggered patterns for the installation of lightweight control components with #8 self-tapping screws. For use in small and medium size Type 1 enclosures. Perforated subpanels are powder coated white.



Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

Perforated Subpanels

Part Number	Price	Size HxW	Fits Enclosure(s)	Drawing Link
SCE-6N6MPP	\$11.00	4.00 x 4.00 [102 x 102]	SCE-6N604LP	PDF
SCE-8N6MPP	\$13.25	6.00 x 4.00 [152 x 102]	SCE-8N604LP	PDF
SCE-8N8MPP	\$14.75	6.00 x 6.00 [152 x 152]	SCE-8N804LP and SCE-8N806LP	PDF
SCE-10N8MPP	\$17.50	8.00 x 6.00 [203 x 152]	SCE-10N804LP and SCE-10N806LP	PDF
SCE-10N10MPP	\$20.50	8.00 x 8.00 [203 x 203]	SCE-10N1004LP and SCE-10N1006LP	PDF
SCE-12N10MPP	\$23.00	10.00 x 8.00 [254 x 203]	SCE-12N1004LP and SCE-12N1006LP	PDF
SCE-12N12MPP	\$24.00	10.00 x 10.00 [254 x 254]	SCE-12N1204LP, 12N1206LP and SCE-12N1208LP	PDF
SCE-14N12MPP	\$26.00	12.00 x 10.00 [305 x 254]	SCE-14N1204LP, 14N1206LP and SCE-14N1208LP	PDF
SCE-16N12MPP	\$29.00	14.00 x 10.00 [356 x 254]	SCE-16N1206LP and SCE-16N1208LP	PDF
SCE-16N16MPP	\$34.00	14.00 x 14.00 [356 x 356]	SCE-16N1606LP and SCE-16N1608LP	PDF
SCE-20N16MPP	\$40.00	18.00 x 14.00 [457 x 356]	SCE-16N2006LP, 20N1606LP and SCE-20N1608LP	PDF
SCE-20N20MPP	\$46.00	18.00 x 18.00 [457 x 457]	SCE-20N2006LP, 20N2008LP and SCE-20N2010LP	PDF
SCE-24N16MPP	\$46.00	22.00 x 14.00 [559 x 356]	SCE-24N1606LP	PDF
SCE-24N20MPP	\$55.00	22.00 x 18.00 [559 x 457]	SCE-24N2006LP, 24N2008LP and SCE-24N2010LP	PDF
SCE-24N24MPP	\$81.00	22.00 x 22.00 [559 x 559]	SCE-24N2406LP, 24N2408LP and SCE-24N2412LP	PDF
SCE-30N24MPP	\$103.00	28.00 x 22.00 [711 x 559]	SCE-30N2406LP, 30N2408LP and SCE-30N2412LP	PDF
SCE-30N30MPP	\$129.00	28.00 x 28.00 [711 x 711]	SCE-30N3008LP	PDF
SCE-36N24MPP	\$129.00	34.00 x 22.00 [864 x 559]	SCE-36N2406LP, 36N2408LP and SCE-36N2412LP	PDF
SCE-36N30MPP	\$152.00	34.00 x 28.00 [864 x 711]	SCE-36N3006LP, 36N3008LP and SCE-36N3012LP	PDF

Note: Dimensions in inches [millimeters].