

NEMA 3R, 4, 12, and 13 Screw Cover Wall-Mount



Your Enclosure Source®



Applications

Designed for use as electrical junction boxes, terminal wiring boxes, instrument housings, and electrical control enclosures. Provides protection from dust, dirt, oil and water.

Construction

- 16-gauge carbon steel
- Seams continuously welded and ground smooth— no holes or knockouts
- Captivated cover screws thread into sealed wells.
- Poured-in-place oil- and water-resistant gasket
- Standoffs are provided for mounting optional subpanels.

Finish

- ANSI 61 gray powder coated inside and out
- Optional subpanels are powder coated white.

Listings

- NEMA Type 3R, 4, 12, and 13
- cULus Listed Type 3R, 4 and 12 [File E69392]
- IEC 60529 IP66



Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

NEMA 3R, 4, 12, and 13 Screw Cover Wall-Mount

Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
SCE-404SC	\$48.50	4.44 x 4.31 x 3.15 [113 x 109 x 80]	PDF	—	—
SCE-4044SC	\$48.50	4.44 x 4.31 x 4.15 [113 x 109 x 105]	PDF	—	—
SCE-604SC	\$55.00	6.44 x 4.31 x 3.15 [164 x 109 x 80]	PDF	SCE-6P4	\$4.25
SCE-6044SC	\$61.00	6.44 x 4.31 x 4.15 [164 x 109 x 105]	PDF	SCE-6P4	\$4.25
SCE-606SC	\$65.00	6.44 x 6.31 x 4.15 [164 x 160 x 105]	PDF	SCE-6P6	\$5.00
SCE-806SC	\$68.00	8.44 x 6.31 x 3.65 [214 x 160 x 93]	PDF	SCE-8P6	\$5.75
SCE-8066SC	\$77.00	8.44 x 6.31 x 6.15 [214 x 160 x 156]	PDF	SCE-8P6	\$5.75
SCE-808SC	\$77.00	8.44 x 8.31 x 4.15 [214 x 211 x 105]	PDF	SCE-8P8	\$6.75
SCE-1008SC	\$84.00	10.44 x 8.31 x 4.15 [265 x 211 x 105]	PDF	SCE-10P8	\$8.00
SCE-10086SC	\$95.00	10.44 x 8.31 x 6.15 [265 x 211 x 156]	PDF	SCE-10P8	\$8.00
SCE-1010SC	\$94.00	10.44 x 10.31 x 4.15 [265 x 262 x 105]	PDF	SCE-10P10	\$9.25
SCE-10106SC	\$105.00	10.44 x 10.31 x 6.15 [265 x 262 x 156]	PDF	SCE-10P10	\$9.25
SCE-1210SC	\$106.00	12.44 x 10.31 x 5.15 [316 x 262 x 131]	PDF	SCE-12P10	\$10.75
SCE-1212SC	\$124.00	12.44 x 12.31 x 6.15 [316 x 313 x 156]	PDF	SCE-12P12	\$12.50
SCE-121010SC	\$161.00	12.44 x 10.31 x 10.15 [316 x 262 x 258]	PDF	SCE-12P10	\$10.75
SCE-1412SC	\$136.00	14.44 x 12.31 x 6.15 [367 x 313 x 156]	PDF	SCE-14P12	\$14.00
SCE-1614SC	\$158.00	16.44 x 14.31 x 6.15 [418 x 363 x 156]	PDF	SCE-16P14	\$27.50

Note: Dimensions in inches [millimeters].

NEMA 3R, 4, 12, and 13 Screw Cover Wall-Mount



Dimensions

