



Vacuum Suction Cups with Fittings - Elastodur



Part No. [10.01.01.13244](#)
Model No. [SPF-30-ED-65-G1/8-AG](#)



Part No. [10.01.06.03489](#)
Model No. [SPB1-10-ED-65-M5-AG](#)



Part No. [10.01.06.03457](#)
Model No. [SPB2-30-ED-65-G1/8-AG](#)

Schmalz Elastodur suction cups are a durable choice for most cardboard and rigid packaging vacuum applications. AutomationDirect.com's offering includes flat and bellows cups with G-thread (BSPP) fittings. Sizes range from 10 to 60mm diameter. Replacement cups are available for all sizes.

Features:

- Elastodur cup material with aluminum fitting
- Flat, single bellows and double bellows styles
- Sizes 10mm to 60mm diameter
- Fitting sizes M5 to G 1/4

Vacuum Suction Cups with Fittings - Elastodur										
Part No.	Schmalz Model No.	Price	Style	Fold(s)	Size	Fitting Connection	Drawing Link	Manufacturer Specs		
10.01.01.13240	SPF-20-ED-65-G1/8-AG	\$12.50	Flat	-	20mm	G1/8 male BSPP	PDF	PDF		
10.01.01.13244	SPF-30-ED-65-G1/8-AG	\$14.00			30mm		PDF	PDF		
10.01.01.13246	SPF-40-ED-65-G1/4-AG	\$20.00			40mm	G1/4 male BSPP	PDF	PDF		
10.01.01.13248	SPF-50-ED-65-G1/4-AG	\$22.00			50mm		PDF	PDF		
10.01.06.03489	SPB1-10-ED-65-M5-AG	\$13.00	Bellows	1	10mm	M5 male	PDF	PDF		
10.01.06.03492	SPB1-20-ED-65-G1/8-AG	\$14.50			20mm	G1/8 male BSPP	PDF	PDF		
10.01.06.03496	SPB1-30-ED-65-G1/8-AG	\$17.50			30mm		PDF	PDF		
10.01.06.03498	SPB1-40-ED-65-G1/4-AG	\$23.00			40mm	PDF	PDF			
10.01.06.03500	SPB1-50-ED-65-G1/4-AG	\$26.00			50mm	G1/4 male BSPP	PDF	PDF		
10.01.06.03502	SPB1-60-ED-65-G1/4-AG	\$28.00			60mm		PDF	PDF		
10.01.06.03453	SPB2-20-ED-65-G1/8-AG	\$18.00			2		20mm	G1/8 male BSPP	PDF	PDF
10.01.06.03457	SPB2-30-ED-65-G1/8-AG	\$21.50					30mm		PDF	PDF
10.01.06.03459	SPB2-40-ED-65-G1/4-AG	\$27.50					40mm	G1/4 male BSPP	PDF	PDF
10.01.06.03461	SPB2-50-ED-65-G1/4-AG	\$33.00					50mm		PDF	PDF



Part No. [10.01.01.12370](#)
Model No. [SPF-20-ED-65-SC040](#)



Part No. [10.01.06.02782](#)
Model No. [SPB1-10-ED-65-SC030](#)



Part No. [10.01.06.03409](#)
Model No. [SPB2-20-ED-65-SC040](#)

Replacement Vacuum Suction Cups - Elastodur								
Part No.	Schmalz Model No.	Price	Style	Fold(s)	Size	Manufacturer Specs		
10.01.01.12370	SPF-20-ED-65-SC040	\$7.75	Flat	-	20mm	PDF		
10.01.01.12372	SPF-30-ED-65-SC040	\$9.25			30mm	PDF		
10.01.01.12373	SPF-40-ED-65-SC040	\$12.50			40mm	PDF		
10.01.01.12374	SPF-50-ED-65-SC040	\$14.50			50mm	PDF		
10.01.06.02782	SPB1-10-ED-65-SC030	\$7.75	Bellows	1	10mm	PDF		
10.01.06.02452	SPB1-20-ED-65-SC040	\$9.25			20mm	PDF		
10.01.06.02454	SPB1-30-ED-65-SC040	\$12.00			30mm	PDF		
10.01.06.02455	SPB1-40-ED-65-SC050	\$14.50			40mm	PDF		
10.01.06.02456	SPB1-50-ED-65-SC050	\$18.00			50mm	PDF		
10.01.06.02457	SPB1-60-ED-65-SC050	\$20.00			60mm	PDF		
10.01.06.03409	SPB2-20-ED-65-SC040	\$13.00			2		20mm	PDF
10.01.06.03411	SPB2-30-ED-65-SC040	\$17.00					30mm	PDF
10.01.06.03412	SPB2-40-ED-65-SC050	\$20.50					40mm	PDF
10.01.06.03413	SPB2-50-ED-65-SC050	\$25.50					50mm	PDF

For additional details see manufacturer's technical specifications, manuals and inserts (where applicable).