



Vacuum Suction Cups with Fittings - Nitrile Rubber

Schmalz nitrile suction cups are an excellent choice for many general purpose vacuum applications. AutomationDirect.com's offering includes bellows cups with G-thread (BSPP) fittings. Sizes range from 14 to 78mm. Replacement cups are available for all sizes.

Features:

- Durable nitrile cup material for a large range of uses
- Single bellows style for uneven surfaces
- Sizes 14 to 78mm diameter
- Fitting sizes G1/8 to G1/4



Part No. [10.01.06.00390](#)
Model No. FSGA-20-NBR-55-G1/8-AG



Part No. [10.01.06.00083](#)
Model No. FSGA-53-NBR-55-G1/4-AG

Vacuum Suction Cups with Fittings - Nitrile Rubber

Part No.	Schmalz Model No.	Price	Style	Fold(s)	Size	Fitting Connection	Drawing Link	Manufacturer Specs
10.01.06.00381	FSGA-14-NBR-55-G1/8-AG	\$9.00	Bellows	1	14mm	G1/8 male BSPP	PDF	PDF
10.01.06.00390	FSGA-20-NBR-55-G1/8-AG	\$10.50			20mm		PDF	PDF
10.01.06.00081	FSGA-33-NBR-55-G1/4-AG	\$14.00			33mm	G1/4 male BSPP	PDF	PDF
10.01.06.00082	FSGA-43-NBR-55-G1/4-AG	\$16.50			43mm		PDF	PDF
10.01.06.00083	FSGA-53-NBR-55-G1/4-AG	\$18.50			53mm		PDF	PDF
10.01.06.00685	FSGA 63 NBR-55 G1/4-AG	\$23.50			63mm		PDF	PDF
10.01.06.00084	FSGA-78-NBR-55-G1/4-AG	\$28.00			78mm		PDF	PDF



Part No. [10.01.06.00130](#)
Model No. FGA-33-NBR-55-N018



Part No. [10.01.06.00133](#)
Model No. FGA-78-NBR-55-N019

Replacement Vacuum Suction Cups - Nitrile Rubber

Part No.	Schmalz Model No.	Price	Style	Fold(s)	Size	Manufacturer Specs
10.01.06.00370	FGA-14-NBR-55-N016	\$5.75	Bellows	1	14mm	PDF
10.01.06.00373	FGA-20-NBR-55-N016	\$7.25			20mm	PDF
10.01.06.00130	FGA-33-NBR-55-N018	\$7.50			33mm	PDF
10.01.06.00131	FGA-43-NBR-55-N018	\$10.50			43mm	PDF
10.01.06.00132	FGA-53-NBR-55-N018	\$13.00			53mm	PDF
10.01.06.00688	FGA-63-NBR-55-N018	\$17.50			63mm	PDF
10.01.06.00133	FGA-78-NBR-55-N019	\$22.50			78mm	PDF

For additional details see manufacturer's technical specifications, manuals and inserts (where applicable).