

Enclosure Subpanels

Stainless Steel

Designed to mount in the back of an enclosure.



Your Enclosure Source®



Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

Stainless Steel Subpanels

Part Number	Price	Size HxW	Fits Enclosure(s)	Drawing Link
304 Stainless Steel				
SCE-16P16SS	\$95.00	13.00 x 13.00 [330 x 330]	SCE-16EL16xxxx	PDF
SCE-20P16SS	\$105.00	17.00 x 13.00 [432 x 330]	SCE-16EL20xxxx, SCE-20EL16xxxx, SCE-16H20xxxx and SCE-20H16xxxx	PDF
SCE-20P20SS	\$123.00	17.00 x 17.00 [432 x 432]	SCE-20EL20xxxx, SCE-20XEL21xxxx, SCE-20SA22xxxx and SCE-20H20xxxx	PDF
SCE-24P16SS	\$114.00	21.00 x 13.00 [533 x 330]	SCE-24EL16xxxx and SCE-24H16xLP	PDF
SCE-24P20SS	\$154.00	21.00 x 17.00 [533 x 432]	SCE-20EL24xxxx, SCE-24EL20xxxx, SCE-24XEL21xxxx, SCE-24SA22xxxx, SCE-20H24xxxx and SCE-24H20xxxx	PDF
SCE-24P24SS	\$185.00	21.00 x 21.00 [533 x 533]	SCE-24EL24xxxx, SCE-24XEL25xxxx, SCE-24SA26xxxx, SCE-29VR24xx, SCE-24R24xxxx and SCE-24H24xxxx	PDF
SCE-30P24SS	\$220.00	27.00 x 21.00 [686 x 533]	SCE-402516Sxxxx, SCE-24EL30xxxx, SCE-30EL24xxxx, SCE-30XEL25xxxx, SCE-30SA26xxxx, SCE-35VR2412, SCE-30R24xxxx, SCE-24H30xxxx and SCE-30H24xxxx	PDF
SCE-30P30SS	\$290.00	27.00 x 27.00 [686 x 686]	SCE-30EL30xxxx and SCE-30H30xxxx	PDF
SCE-36P16SS	\$185.00	33.00 x 13.00 [838 x 330]	SCE-36H1606LP	PDF
SCE-36P24SS	\$264.00	33.00 x 21.00 [838 x 533]	SCE-36EL24xxxx, SCE-36XEL25xxxx, SCE-36SA26xxxx, SCE-41VR2412, SCE-36R24xLP and SCE-36H24xxxx	PDF
SCE-36P30SS	\$351.00	33.00 x 27.00 [838 x 686]	SCE-403716xxxx, SCE-30EL36xxxx, SCE-36EL30xxxx, SCE-36XEL31xxxx, SCE-36SA32xxLPPL, SCE-36R30xxLP, SCE-30H36xxxx and SCE-36H30xxxx	PDF
SCE-36P36SS	\$413.00	33.00 x 33.00 [838 x 838]	SCE-463719xxxx, SCE-36EL36xxxx and SCE-36H36xxxx	PDF
SCE-42P30SS	\$404.00	39.00 x 27.00 [991 x 686]	SCE-42EL30xxxx, SCE-30EL4210xxWFLP, SCE-42XEL31xxxx, SCE-42SA32xxLPPL, SCE-42R30xxLP and SCE-42H30xxxx	PDF
SCE-42P36SS	\$474.00	39.00 x 33.00 [991 x 838]	SCE-42EL36xxxx, SCE-36EL4216xxWFLP, SCE-42XEL37xxxx, SCE-42SA38xxLPPL, and SCE-42H36xxxx	PDF
SCE-48P24SS	\$343.00	45.00 x 21.00 [1143 x 533]	SCE-48EL24xxxx, SCE-2448xxWFLP, SCE-24EL4810xxWFLP, SCE-48SA2610LPPL and SCE-48H2408LP	PDF
SCE-48P36SS	\$536.00	45.00 x 33.00 [1143 x 838]	SCE-464919xxxx, SCE-48EL36xxxx, SCE-36EL48xxxx, SCE-3648xxWFLP, SCE-48XEL37xxxx, SCE-48SA38xxLPPL, SCE-53VR36xx, SCE-53XVR37xx and SCE-48H36xxxx	PDF
SCE-60P30SS	\$554.00	57.00 x 27.00 [1448 x 686]	SCE-30EL6010xxWFLP and SCE-3060xxWFLP	PDF
SCE-60P36SS	\$659.00	57.00 x 33.00 [1448 x 838]	SCE-60EL36xxxx, SCE-36EL60xxxx, SCE-3660xxWFLP, SCE-60XEL37xxxx, SCE-60SA38xxLPPL, SCE-65VR36xx, SCE-65XVR37xx and SCE-60H36xxxx	PDF
316/316L Stainless Steel				
SCE-6P4SS	\$10.50	5.00 x 3.00 [127 x 76]	SCE-604ELJxx, SCE-604xCHNFxx, SCE-604xSC and SCE-7KJxxSSST	PDF
SCE-6P6SS	\$12.50	5.00 x 5.00 [127 x 127]	SCE-606ELJxx, SCE-606CHNFxx, SCE-606SC and SCE-4SPBAx	PDF
SCE-8P6SS	\$14.50	7.00 x 5.00 [178 x 127]	SCE-6PBAX, SCE-806xELJxx, SCE-806xCHNFxx, SCE-806xSC and SCE-9KxxSSST	PDF
SCE-10P8SS	\$19.75	9.00 x 7.00 [229 x 178]	SCE-6PBHx, SCE-1008xELJxx, SCE-1008xCHNFxx, SCE-1008xSC, SCE-11KJxxSSST and SCE-12PBAX	PDF
SCE-10P10SS	\$23.50	9.00 x 9.00 [229 x 229]	SCE-10106ELJxx, SCE-10106CHNF, SCE-1010xSC, SCE-9PBHxx and SCE-16PBAX	PDF
SCE-12P10SS	\$27.00	11.00 x 9.00 [279 x 229]	SCE-1210xELJxx, SCE-1210xCHNF, SCE-1210xSC, SCE-12PBHx and SCE-13KJxxSSST	PDF
SCE-12P12SS	\$31.50	11.00 x 11.00 [279 x 279]	SCE-1212ELJxx, SCE-1212CHNF, SCE-1212SC and SCE-16PBHxx	PDF
SCE-16P12SS	\$51.00	13.00 x 9.00 [330 x 229]	SCE-16EL120xxxx, SCE-16H12xxxxLP and SCE-16R120xLP	PDF
SCE-14P12SS	\$35.00	13.00 x 11.00 [330 x 279]	SCE-1412xELJxx, SCE-1412xCHNF, SCE-1412SC and SCE-15KJxxSSST	PDF
SCE-16P14SS	\$69.00	15.00 x 13.00 [381 x 330]	SCE-1614xELJxx, SCE-1614xxCHNFxx, SCE-1614SC and SCE-16C16ELJxx	PDF

Note: Dimensions in inches [millimeters].