

# Subpanels for N Series Fiberglass Enclosures



## Carbon steel subpanels

- Material: Carbon steel
- Finish: White polyester powder

Subpanel Part Number	Price	Subpanel Size HxWxD	Enclosure Nominal Size HxW	Drawing Link
<a href="#">BP2016CS</a>	\$84.00	17.00 x 13.00 [432 x 330]	20 x 16 [508 x 406]	<a href="#">PDF</a>
<a href="#">BP2420CS</a>	\$164.00	21.00 x 17.00 [533 x 432]	24 x 20 [610 x 508]	<a href="#">PDF</a>
<a href="#">BP2424CS</a>	\$277.00	21.00 x 21.00 [533 x 533]	24 x 24 [610 x 610]	<a href="#">PDF</a>
<a href="#">BP3024CS</a>	\$258.00	27.00 x 21.00 [686 x 533]	30 x 24 [762 x 610]	<a href="#">PDF</a>
<a href="#">BP3630CS</a>	\$403.00	33.00 x 27.00 [838 x 686]	36 x 30 [914 x 762]	<a href="#">PDF</a>
<a href="#">BP4836CS</a>	\$584.00	45.00 x 33.00 [1143 x 838]	48 x 36 [1219 x 914]	<a href="#">PDF</a>

**Note: Dimensions in inches [millimeters].**

## Aluminum subpanels

- Material: 3003H14 aluminum
- Finish: Mill

Subpanel Part Number	Price	Subpanel Size HxWxD	Enclosure Nominal Size HxW	Drawing Link
<a href="#">BP1610AL</a>	\$75.00	13.00 x 8.50 [330 x 216]	16 x 10 [406 x 254]	<a href="#">PDF</a>
<a href="#">BP2016AL</a>	\$84.00	17.00 x 13.00 [432 x 330]	20 x 16 [508 x 406]	<a href="#">PDF</a>
<a href="#">BP2412AL</a>	\$81.00	21.00 x 9.00 [533 x 229]	24 x 12 [610 x 305]	<a href="#">PDF</a>
<a href="#">BP2420AL</a>	\$164.00	21.00 x 17.00 [533 x 432]	24 x 20 [610 x 508]	<a href="#">PDF</a>
<a href="#">BP2424AL</a>	\$202.00	21.00 x 21.00 [533 x 533]	24 x 24 [610 x 610]	<a href="#">PDF</a>
<a href="#">BP3020AL</a>	\$210.00	27.00 x 17.00 [686 x 432]	30 x 20 [762 x 508]	<a href="#">PDF</a>
<a href="#">BP3024AL</a>	\$258.00	27.00 x 21.00 [686 x 533]	30 x 24 [762 x 610]	<a href="#">PDF</a>
<a href="#">BP3630AL</a>	\$403.00	33.00 x 27.00 [838 x 686]	36 x 30 [914 x 762]	<a href="#">PDF</a>
<a href="#">BP4836AL</a>	\$584.00	45.00 x 33.00 [1143 x 838]	48 x 36 [1219 x 914]	<a href="#">PDF</a>
<a href="#">BP6036AL</a>	\$723.00	57.00 x 33.00 [1448 x 838]	60 x 36 [1524 x 914]	<a href="#">PDF</a>

**Note: Dimensions in inches [millimeters].**