

Subpanels for Diamond Shield, J, JW, RJ, RJW, and Classic Series Fiberglass Enclosures



Carbon steel subpanels

- Material: Carbon steel
- Finish: White polyester powder finish

Part Number	Price	Subpanel Size HxW	Enclosure Nominal Size HxW
BP64CS	\$17.25	4.88 x 2.88 [124 x 73]	6 x 4 [152 x 102]
BP66CS	\$11.25	4.88 x 4.88 [124 x 124]	6 x 6 [152 x 152]
BP86CS	\$13.50	6.75 x 4.88 [171 x 124]	8 x 6 [203 x 152]
BP88CS	\$21.00	6.88 x 6.88 [175 x 175]	8 x 8 [203 x 203]
BP108CS	\$20.50	8.75 x 6.88 [222 x 175]	10 x 8 [254 x 203]
BP1210CS	\$25.00	10.88 x 8.75 [276 x 222]	12 x 10 [305 x 254]
BP1412CS	\$30.00	12.88 x 10.88 [327 x 276]	14 x 12 [356 x 305]
BP1614CS	\$39.00	14.88 x 12.88 [378 x 327]	16 x 14 [406 x 356]
BP1816CS	\$50.00	16.88 x 14.88 [429 x 378]	18 x 16 [457 x 406]
BPJ2016CS	\$64.00	18.88 x 14.88 [480 x 378]	20 x 16 [508 x 406]
BPJ2020CS	\$187.00	18.88 x 18.88 [480 x 480]	20 x 20 [508 x 508]
BPJ2420CS	\$226.00	22.88 x 18.88 [581 x 480]	24 x 20 [610 x 508]
BPJ2424CS	\$277.00	22.88 x 22.88 [581 x 581]	24 x 24 [610 x 610]

Note: Dimensions in inches [millimeters].

Fiberglass subpanels

- Material: Fiberglass reinforced polyester (FRP)
- Color: Gray

Part Number	Price	Subpanel Size HxW	Enclosure Nominal Size HxW
BP86FG	\$20.50	6.88 x 4.88 [175 x 124]	8 x 6 [203 x 152]
BP108FG	\$24.50	8.88 x 6.88 [226 x 175]	10 x 8 [254 x 203]
BP1210FG	\$31.50	10.88 x 8.88 [276 x 226]	12 x 10 [305 x 254]
BP1412FG	\$39.50	12.88 x 10.88 [327 x 276]	14 x 12 [356 x 305]
BP1614FG	\$49.00	14.88 x 12.88 [378 x 327]	16 x 14 [406 x 356]
BP1816FG	\$54.00	16.88 x 14.88 [429 x 378]	18 x 16 [457 x 406]

Note: Dimensions in inches [millimeters].

Subpanels for Diamond Shield, J, JW, RJ, RJW, and Classic Series Fiberglass Enclosures



Aluminum Subpanels

- Material: 3003H14 aluminum
- Finish: Mill



Aluminum Subpanels				
Part Number	Price	Subpanel Size HxWxD	Fits	Drawing Link
<u>BP64AL</u>	\$11.00	4.88 x 2.88 [124 x 73]	6x4 (HxW) Jx604xx J/JW series RJ604xx	<u>PDF</u>
<u>BP66AL</u>	\$11.25	4.88 x 4.88 [124 x 124]	6x6/7x7 (HxW) DSx60604xx Diamond Shield series Jx606xx J/JW series RJ606xx RJ series CL707xx F4PBW pushbutton	<u>PDF</u>
<u>BP86AL</u>	\$13.50	6.88 x 4.88 [175 x 124]	8x6/9x7 (HxW) DS80604xx Diamond Shield series Jx806xx J/JW series RJx806xx RJ/RJW series CL907xx F6PBW pushbutton	<u>PDF</u>
<u>BP88AL</u>	\$19.50	6.88 x 6.88 [175 x 175]	8x8 (HxW) DSx80804Hxx Diamond Shield series J808xx J series J808SSH Fatboy series RJ808HPL	<u>PDF</u>
<u>BP108AL</u>	\$20.50	8.88 x 6.88 [226 x 175]	10x8/11x9 (HxW) DSx100806xx Diamond Shield series Jx1008xx WH-J1008HPL J/JW/Fatboy series RJx1008xx RJ/RJW series CL1109xx F9PBW pushbutton	<u>PDF</u>
<u>BP1210AL</u>	\$25.00	10.88 x 8.88 [276 x 226]	12x10/13x11 (HxW) DSx121006xx Diamond Shield series Jx1210xx WH-J1210HPL J/JW/Fatboy series RJx1210xx RJ/RJW series CL1311xx	<u>PDF</u>
<u>BP1412AL</u>	\$30.00	12.88 x 10.88 [327 x 276]	14x12/15x13 (HxW) DSx14120xxx Diamond Shield series Jx1412xx WH-J1412HPL J/JW/Fatboy series RJx1412xx RJ/RJW series CL1513xx	<u>PDF</u>
<u>BP1614AL</u>	\$39.00	14.88 x 12.88 [378 x 327]	16x14 (HxW) DSx161408xx Diamond Shield series Jx1614xx WH-J1614HPL J/JW/Fatboy series RJx1614xx	<u>PDF</u>
<u>BP1816AL</u>	\$50.00	16.88 x 14.88 [429 x 378]	18x16 (HxW) DSx181610xx Diamond Shield series Jx1816xx WH-J1816HPL J/JW/Fatboy series RJx1816xx	<u>PDF</u>
<u>BPJ2016AL</u>	\$64.00	18.88 x 14.88 [480 x 378]	20x16 (HxW) DSx201610xx Diamond Shield series Jx2016xx WH-J2016HPL J/JW series RJx2016xx	<u>PDF</u>
<u>BPJ2020AL</u>	\$179.00	18.88 x 18.88 [480 x 480]	J2020HPL	<u>PDF</u>
<u>BPJ2420AL</u>	\$216.00	22.88 x 18.88 [581 x 480]	J2420HPL	<u>PDF</u>
<u>BPJ2424AL</u>	\$265.00	22.88 x 22.88 [581 x 581]	J2424HPL	<u>PDF</u>
<u>BPJ3024AL</u>	\$313.00	27.00 x 21.00 [686 x 533]	J2430HPL J3024HPL	<u>PDF</u>
Note: Dimensions in inches (millimeters).				