

# Subpanels for Heartland Series Enclosures

## Aluminum Subpanels

- Material: 3003-H14 aluminum
- Finish: Mill



| Aluminum Subpanels                        |         |                           |                                      |                     |
|-------------------------------------------|---------|---------------------------|--------------------------------------|---------------------|
| Part Number                               | Price   | Subpanel Size HxW         | Fits Heartland series Enclosures     | Drawing Link        |
| <a href="#">BP66A</a>                     | \$11.25 | 4.88 x 4.88 [124 x 124]   | AHx664xxx                            | <a href="#">PDF</a> |
| <a href="#">BP86A</a>                     | \$13.50 | 6.88 x 4.88 [175 x 124]   | AHx864xxx                            | <a href="#">PDF</a> |
| <a href="#">BP88A</a>                     | \$19.00 | 6.88 x 6.88 [175 x 175]   | AHx884xxx                            | <a href="#">PDF</a> |
| <a href="#">BP108A</a>                    | \$20.50 | 8.88 x 6.88 [226 x 175]   | AH1083xxx<br>AH1084xxx<br>AHx1086xxx | <a href="#">PDF</a> |
| <a href="#">BP1010A</a>                   | \$24.00 | 8.88 x 8.88 [226 x 226]   | AHxx10106xxx                         | <a href="#">PDF</a> |
| <a href="#">BP1210A</a>                   | \$25.00 | 10.88 x 8.88 [276 x 226]  | AH12104xxx<br>AHxx12106xxx           | <a href="#">PDF</a> |
| <a href="#">BP1412A</a>                   | \$30.00 | 12.88 x 10.88 [327 x 276] | AH14124xxx<br>AHxx14126xxx           | <a href="#">PDF</a> |
| <a href="#">BP1614A</a>                   | \$39.00 | 14.88 x 12.88 [378 x 327] | AH16144xxx<br>AHxx16148xxx           | <a href="#">PDF</a> |
| <a href="#">BP1816A</a>                   | \$50.50 | 16.88 x 14.88 [429 x 378] | AH18164xxx<br>AHxx181610xxx          | <a href="#">PDF</a> |
| <a href="#">BP2016A</a>                   | \$84.00 | 18.88 x 14.88 [480 x 378] | AH20164xxx<br>AHxx20168xxx           | <a href="#">PDF</a> |
| <a href="#">BP2424A</a>                   | \$92.00 | 22.88 x 22.88 [581 x 581] | AH24246xxx<br>AH242410xxx            | <a href="#">PDF</a> |
| Note: Dimensions in inches (millimeters). |         |                           |                                      |                     |



BP66A

## Aluminum Swing Panel Kits

- Material: 3003-H14 aluminum
- Finish: Mill
- Includes swing panel, (4) AHSPM brackets and mounting screws

| Aluminum Swing Panel Kits                                                                |          |                           |                                  |                     |
|------------------------------------------------------------------------------------------|----------|---------------------------|----------------------------------|---------------------|
| Part Number                                                                              | Price    | Subpanel Size HxW         | Fits Heartland series Enclosures | Drawing Link        |
| <a href="#">AH66SPK</a>                                                                  | \$52.50  | 5.63 x 5.63 [143 x 143]   | AHx664xxx                        | <a href="#">PDF</a> |
| <a href="#">AH86SPK</a>                                                                  | \$54.00  | 7.63 x 5.63 [194 x 143]   | AHx864xxx                        | <a href="#">PDF</a> |
| <a href="#">AH88SPK</a>                                                                  | Retired  | 7.63 x 7.63 [194 x 194]   | AH884xxx                         | <a href="#">PDF</a> |
| <a href="#">AH108SPK</a>                                                                 | \$59.00  | 9.63 x 7.63 [245 x 194]   | AHx1084xxx<br>AHx1086xxx         | <a href="#">PDF</a> |
| <a href="#">AH1010SPK</a>                                                                | \$85.00  | 9.63 x 9.63 [245 x 245]   | AHxx10106xxx                     | <a href="#">PDF</a> |
| <a href="#">AH1210SPK</a>                                                                | \$63.00  | 11.63 x 9.63 [295 x 245]  | AHxx12106xxx                     | <a href="#">PDF</a> |
| <a href="#">AH1412SPK</a>                                                                | \$68.00  | 13.63 x 11.63 [346 x 295] | AHxx14126xxx                     | <a href="#">PDF</a> |
| <a href="#">AH1614SPK</a>                                                                | \$73.00  | 15.63 x 13.63 [397 x 346] | AHxx16148xxx                     | <a href="#">PDF</a> |
| <a href="#">AH1816SPK</a>                                                                | \$78.00  | 17.63 x 15.63 [448 x 397] | AH18164xxx<br>AHxx181610xxx      | <a href="#">PDF</a> |
| <a href="#">AH2016SPK</a>                                                                | \$121.00 | 19.63 x 15.63 [499 x 397] | AHxx20168xxx                     | <a href="#">PDF</a> |
| <a href="#">AH2424SPK</a>                                                                | \$88.00  | 23.63 x 23.63 [600 x 600] | AHxx242410xxx                    | <a href="#">PDF</a> |
| Note: Dimensions in inches (millimeters).<br>Not compatible with Heartland SL enclosures |          |                           |                                  |                     |



AH66SPK

# Subpanels for Heartland Series Enclosures

## Aluminum Side Panels

- Material: 3003-H14 aluminum
- Finish: Mill



| Aluminum Subpanels                                                                                                      |         |                          |                                                  |                     |
|-------------------------------------------------------------------------------------------------------------------------|---------|--------------------------|--------------------------------------------------|---------------------|
| Part Number                                                                                                             | Price   | Subpanel Size HxW        | Fits Heartland series Enclosures                 | Drawing Link        |
| <a href="#">SP6</a>                                                                                                     | \$53.00 | 5.00 x 3.00 [127 x 76]   | AH664xxx<br>AHF664x                              | <a href="#">PDF</a> |
| <a href="#">SP8</a>                                                                                                     | \$54.00 | 7.00 x 3.00 [178 x 76]   | AH864xxx<br>AHF864x<br>AH884xxx<br>AHF884x       | <a href="#">PDF</a> |
| <a href="#">SP10</a>                                                                                                    | \$57.00 | 9.00 x 3.50 [229 x 89]   | AH1084xxx<br>AHF1084x<br>AH10xx6xxx<br>AHF10xx6x | <a href="#">PDF</a> |
| <a href="#">SP12</a>                                                                                                    | \$61.00 | 11.00 x 5.00 [279 x 127] | AH12106xxx<br>AHF12106x                          | <a href="#">PDF</a> |
| <a href="#">SP14</a>                                                                                                    | \$64.00 | 13.00 x 5.00 [330 x 127] | AH14126xxx<br>AHF14126x                          | <a href="#">PDF</a> |
| <a href="#">SP16</a>                                                                                                    | \$71.00 | 15.00 x 7.00 [381 x 178] | AH16148xxx<br>AHF16148x                          | <a href="#">PDF</a> |
| <a href="#">SP18</a>                                                                                                    | \$82.00 | 17.00 x 9.00 [432 x 229] | AH181610xxx<br>AHF181610x                        | <a href="#">PDF</a> |
| <a href="#">SP20</a>                                                                                                    | \$84.00 | 19.00 x 7.00 [483 x 178] | AH20168xxx<br>AHF20168x                          | <a href="#">PDF</a> |
| <a href="#">SP24</a>                                                                                                    | \$92.00 | 23.00 x 9.00 [584 x 229] | AH242410xxx                                      | <a href="#">PDF</a> |
| <b>Note: Dimensions in inches (millimeters).</b><br><b>Corrosion resistant slot nut fastening hardware kit included</b> |         |                          |                                                  |                     |

[SP8](#)

## ABS Plastic Subpanels

- Material: ABS plastic
- Finish: Mill

| ABS plastic Subpanels                            |         |                           |                                      |                     |
|--------------------------------------------------|---------|---------------------------|--------------------------------------|---------------------|
| Part Number                                      | Price   | Subpanel Size HxW         | Fits Heartland series Enclosures     | Drawing Link        |
| <a href="#">BP66ABS</a>                          | \$14.75 | 4.75 x 4.75 [121 x 121]   | AHx664xxx                            | <a href="#">PDF</a> |
| <a href="#">BP86ABS</a>                          | \$15.50 | 6.75 x 4.75 [171 x 121]   | AHx864xxx                            | <a href="#">PDF</a> |
| <a href="#">BP108ABS</a>                         | \$18.75 | 8.75 x 6.75 [222 x 171]   | AH1083xxx<br>AH1084xxx<br>AHx1086xxx | <a href="#">PDF</a> |
| <a href="#">BP1010ABS</a>                        | \$20.00 | 8.75 x 8.75 [222 x 222]   | AHxx10106xxx                         | <a href="#">PDF</a> |
| <a href="#">BP1210ABS</a>                        | \$22.00 | 10.75 x 8.75 [273 x 222]  | AH12104xxx<br>AHxx12106xxx           | <a href="#">PDF</a> |
| <a href="#">BP1412ABS</a>                        | \$25.00 | 12.75 x 10.75 [324 x 273] | AH14124xxx<br>AHxx14126xxx           | <a href="#">PDF</a> |
| <a href="#">BP1614ABS</a>                        | \$29.00 | 14.75 x 12.75 [375 x 324] | AH16144xxx<br>AHxx16148xxx           | <a href="#">PDF</a> |
| <a href="#">BP1816ABS</a>                        | \$39.00 | 16.75 x 14.75 [425 x 375] | AH18164xxx<br>AHxx181610xxx          | <a href="#">PDF</a> |
| <a href="#">BP2016ABS</a>                        | \$52.00 | 18.75 x 14.75 [476 x 375] | AH20164xxx<br>AHxx20168xxx           | <a href="#">PDF</a> |
| <a href="#">BP2424ABS</a>                        | \$62.00 | 22.75 x 22.75 [578 x 578] | AH24246xxx<br>AH242410xxx            | <a href="#">PDF</a> |
| <b>Note: Dimensions in inches (millimeters).</b> |         |                           |                                      |                     |

[BP108ABS](#)