


Wera Wrenches

Hex-Plus L-Keys Sets

Wera Hex-plus L-keys for hexagon socket screws provide more contact surface inside the screw, which prevents rounding.

L-keys can transfer high torque but do not twist to any great extent, or shear off, to minimize risk of injury. Wera's extensive experience with narrow tolerance manufacturing techniques, careful material selection, and refined hardening technologies delivers maximum safety at work.



Hex Ball-end Tip



Thermoplastic Multi-color Sleeve



Engraved Size Identification












Hex-Plus L-Key Sets						
Part Number	Number of Pieces	Part Image	Features	Material	Set Includes	Price
05022639055	9		Ball-end tip Hex-plus tip	Blacklaser Steel With Multicolor Grips	(9) multicolor hex L-keys (5/64, 3/32, 1/8, 5/32, 3/16, 7/32, 1/4, 5/16 and 3/8in), durable cloth pouch	\$46.00
05022089055	9		Ball-end tip Hex-plus tip		(9) multicolor hex L-keys (1.5, 2, 2.5, 3, 4, 5, 6, 8 and 10mm), fold-out L-key holder	\$41.00
05022210001	9		Ballpoint holding function Ball-end tip Hex-plus tip		(9) color-coded BlackLaser L-key hex keys (1.5 x 90mm, 2.0 x 101mm, 2.5 x 112mm, 3.0 x 123mm, 4.0 x 137mm, 5.0 x 154mm, 6.0 x 172mm, 8.0 x 195mm, 10.0 x 224mm), (1) wear-resistant clip	\$52.00
05022640001	9		Ball-end tip Hex-plus tip		(9) color-coded BlackLaser L-key hex keys (5/64 x 101mm, 3/32 x 112mm, 1/8 x 123mm, 5/32 x 137mm, 3/16 x 154mm, 7/32 x 172mm, 1/4 x 185mm, 5/16 x 195mm, 3/8 x 224mm), (1) wear-resistant clip	\$40.00
05022641001	9		Ball-end tip Hex-plus tip		(9) color-coded BlackLaser L-key hex keys (5/64 x 50mm, 3/32 x 56mm, 1/8 x 63mm, 5/32 x 71mm, 3/16 x 80mm, 7/32 x 90mm, 1/4 x 100mm, 5/16 x 112mm, 3/8 x 125mm), (1) wear-resistant clip	\$42.00
05133164001	9		Ball-end tip Hex-plus tip		(9) color-coded BlackLaser L-key hex keys (1.5 x 50mm, 2.0 x 56mm, 2.5 x 63mm, 3.0 x 71mm, 4.0 x 80mm, 5.0 x 90mm, 6.0 x 100mm, 8.0 x 112mm, 10.0 x 125mm), (1) wear-resistant clip	\$40.00

Note: L-keys are warranted against manufacturer defect only.



Wera Wrenches

Hex-Plus L-Key Sets - Cont'd

Part Number	Number of Pieces	Part Image	Features	Material	Set Includes	Price
<u>TW-HK-SET-MM</u>	9		Ball-end tip Hex-plus tip	Blacklaser Steel	(9) BlackLaser hex L-keys (1.5, 2, 2.5, 3, 4, 5, 6, 8 and 10mm), fold-out L-key holder	\$13.00
<u>TW-HK-SET-STD</u>	13		Ball-end tip Hex-plus tip		(13) hex L-keys (0.05, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16 and 3/8in), fold-out L-key holder	\$24.00
<u>05133180001</u>	9		Ball-end tip Hex-plus tip		(9) BlackLaser L-key hex keys (5/64 x 100mm, 3/32 x 112mm, 1/8 x 126mm, 5/32 x 140mm, 3/16 x 160mm, 7/32 x 180mm, 1/4 x 190mm, 5/16 x 200mm, 3/8 x 212mm), (1) wear-resistant clip	\$12.00
<u>05021737001</u>	9		Hex-plus tip		(9) L-key hex keys with BlackLaser material (1.5 x 45mm, 2.0 x 50mm, 2.5 x 56mm, 3.0 x 63mm, 4.0 x 70mm, 5.0 x 80mm, 6.0 x 90mm, 8.0 x 100mm, 10.0 x 112mm), (1) wear-resistant clip	\$4.00
<u>05022669001</u>	9		Ball-end tip Hex-plus tip	Stainless steel with multicolor grips	(9) color-coded stainless steel L-key hex keys (1.5 x 90mm, 2.0 x 101mm, 2.5 x 112mm, 3.0 x 123mm, 4.0 x 137mm, 5.0 x 154mm, 6.0 x 172mm, 8.0 x 195mm, 10.0 x 224mm), (1) wear-resistant clip	\$60.00
<u>05022699001</u>	9		Ballpoint holding function Ball-end tip Hex-plus tip		(9) color-coded stainless steel L-key hex keys (1.5 x 90mm, 2.0 x 101mm, 2.5 x 112mm, 3.0 x 123mm, 4.0 x 137mm, 5.0 x 154mm, 6.0 x 172mm, 8.0 x 195mm, 10.0 x 224mm), (1) wear-resistant clip	\$70.00
<u>05022860001</u>	9		Ball-end tip Hex-plus tip		(9) color-coded stainless steel L-key hex keys (5/64 x 101mm, 3/32 x 112mm, 1/8 x 123mm, 5/32 x 137mm, 3/16 x 154mm, 7/32 x 172mm, 1/4 x 185mm, 5/16 x 195mm, 3/8 x 224mm), (1) wear-resistant clip	\$60.00
<u>05073544001</u>	9		Ball-end tip Hex-plus tip	Stainless steel	(9) stainless steel L-key hex keys (1.5 x 90mm, 2.0 x 101mm, 2.5 x 112mm, 3.0 x 123mm, 4.0 x 137mm, 5.0 x 154mm, 6.0 x 172mm, 8.0 x 195mm, 10.0 x 224mm), (1) wear-resistant clip	\$46.00
<u>05073391001</u>	9		Ball-end tip Hex-plus tip	Chrome-plated steel	(9) chrome-plated L-key hex keys (1.5 x 90mm, 2.0 x 100mm, 2.5 x 112mm, 3.0 x 126mm, 4.0 x 140mm, 5.0 x 160mm, 6.0 x 180mm, 8.0 x 200mm, 10.0 x 219mm), (1) wear-resistant clip	\$18.00
<u>05133163001</u>	9		Ball-end tip Hex-plus tip		(9) chrome-plated L-key hex keys (1.5 x 50mm, 2.0 x 56mm, 2.5 x 63mm, 3.0 x 71mm, 4.0 x 80mm, 5.0 x 90mm, 6.0 x 100mm, 8.0 x 112mm, 10.0 x 125mm), (1) wear-resistant clip	\$22.00
<u>05022130001</u>	9		Ballpoint holding function Hex-plus tip		(9) chrome-plated L-key hex keys (1.5 x 90mm, 2.0 x 100mm, 2.5 x 112mm, 3.0 x 126mm, 4.0 x 140mm, 5.0 x 160mm, 6.0 x 180mm, 8.0 x 200mm, 10.0 x 219mm), (1) wear-resistant clip	\$36.00

Note: L-keys are warranted against manufacturer defect only.

Wera Wrenches

Torx L-Key Sets

Wera Torx L-keys for Torx socket screws provide more contact surface inside the screw, which prevents rounding.

L-keys can transfer high torque but do not twist to any great extent, or shear off, to minimize risk of injury. Wera's extensive experience with narrow tolerance manufacturing techniques, careful material selection, and refined hardening technologies delivers maximum safety at work.



Torx Ball-end Tip



Thermoplastic Multi-color Sleeve



Engraved Size Identification



Torx L-Key Sets						
Part Number	Number of Pieces	Part Image	Features	Material	Set Includes	Price
05073599001	9		Demagnetizer Ball-end tip	Blacklaser Steel With Multicolor Grips	(9) color-coded BlackLaser L-key hex keys, short end tamperproof torx, long end ball-end torx (T9 x 79mm, T8 x 76mm, T10 x 85mm, T15 x 90mm, T20 x 96mm, T25 x 104mm, T30 x 122mm, T40 x 132mm, T27 x 112mm), (1) wear-resistant clip	\$46.00
05024179001	9		Ballpoint holding function Ball-end tip Hex-plus tip		(9) color-coded BlackLaser L-key hex keys (T8 x 76mm, T9 x 79mm, T10 x 85mm, T15 x 90mm, T20 x 96mm, T25 x 104mm, T27 x 112mm, T30 x 122mm, T40 x 132mm), (1) wear-resistant clip	\$46.00
05024480001	9		Ball-end tip		(9) color-coded BlackLaser L-key hex keys (T8 x 90mm, T9 x 101mm, T10 x 112mm, T15 x 123mm, T20 x 137mm, T25 x 154mm, T27 x 172mm, T30 x 195mm, T40 x 224mm)	\$54.00
05024460001	9		Ball-end tip	Blacklaser Steel	(9) BlackLaser L-key hex keys (T8 x 90mm, T9 x 101mm, T10 x 112mm, T15 x 123mm, T20 x 137mm, T25 x 154mm, T27 x 172mm, T30 x 195mm, T40 x 224mm), (1) wear-resistant clip	\$48.00
05073598001	9		Ball-end tip		(9) BlackLaser L-key hex keys (T9 x 79mm, T10 x 85mm, T8 x 76mm, T15 x 90mm, T20 x 96mm, T25 x 104mm, T27 x 112mm, T30 x 122mm, T40 x 132mm), (1) wear-resistant clip	\$30.00
05022689001	9		Holding function	Stainless steel	(9) color-coded stainless steel L-key torx keys (T8 x 90mm, T9 x 101mm, T10 x 112mm, T15 x 123mm, T20 x 137mm, T25 x 154mm, T27 x 172mm, T30 x 195mm, T40 x 224mm), (1) 2-component plastic clip	\$68.00

Note: L-keys are warranted against manufacturer defect only.