

Enclosure Accessories – Hole Seals and Plugs



Hole Seals for Metal Enclosures

Designed to seal extra pushbutton holes, conduit openings, and knockout openings in metal enclosures from dirt, dust, oil and water. Conduit hole sizes are nominal trade sizes, not actual hole sizes. (Example: 1 in [25 mm] conduit actual diameter = 1.315in [33.4mm].)



<i>Steel Hole Seals with ANSI 61 Gray Polyester Powder</i>	<i>Price</i>	<i>Stainless Steel Hole Seals with Grained Finish</i>	<i>Price</i>	<i>Description</i>	<i>Hole Diameter</i>	<i>Wt.[lb]</i>
<u>WAS050</u>	\$7.50	<u>WAS050SS</u>	\$16.25	Wiegmann conduit hole seal, 0.5in [13mm], quick wing nut, oil-resistant gasket	0.87 [22]	0.1
<u>WAS075</u>	\$9.50	<u>WAS075SS</u>	\$22.50	Wiegmann conduit hole seal, 0.75in [19 mm], quick wing nut, oil-resistant gasket	1.14 [29]	
<u>WAS100</u>	\$13.00	<u>WAS100SS</u>	\$30.00	Wiegmann conduit hole seal, 1.00in [25mm], quick wing nut, oil-resistant gasket	1.38 [35]	
<u>WAS125</u>	\$15.50	<u>WAS125SS</u>	\$32.00	Wiegmann conduit hole seal, 1.25in [31.8mm], quick wing nut, oil-resistant gasket	1.61 [41]	0.2
<u>WAS150</u>	\$17.75	<u>WAS150SS</u>	\$36.00	Wiegmann conduit hole seal, 1.5in [38mm], quick wing nut, oil-resistant gasket	2.00 [51]	
<u>WAS200</u>	\$19.75	<u>WAS200SS</u>	\$43.50	Wiegmann conduit hole seal, 2.00in [51mm], quick wing nut, oil-resistant gasket	2.52 [64]	0.3
<u>WAS250</u>	\$23.00	—	—	Wiegmann conduit hole seal, 2.50in [64mm], quick wing nut, oil-resistant gasket	3.00 [76]	0.4
<u>WAS300</u>	\$30.50	—	—	Wiegmann conduit hole seal, 3.00in [76mm], quick wing nut, oil-resistant gasket	3.62 [92]	
<u>WAS350</u>	\$43.00	—	—	Wiegmann conduit hole seal, 3.50in [89mm], quick wing nut, oil-resistant gasket	4.13 [105]	
<u>WAS400</u>	\$55.00	—	—	Wiegmann conduit hole seal, 4.00in [102mm], quick wing nut, oil-resistant gasket	4.64 [118]	0.6
<u>WASPB</u>	\$10.00	<u>WASPBSS</u>	\$25.00	Wiegmann hole seal, for 30mm [1.18 in] pushbutton cutout, quick wing nut, oil-resistant gasket	1.18 [30]	0.1
<u>WASPBG</u>	\$7.50	<u>WASPBGSS</u>	\$16.25	Wiegmann hole seal, for 22mm [0.87 in] pushbutton cutout, quick wing nut, oil-resistant gasket	0.87 [22]	

Note: Dimensions in inches [millimeters].