



Zyklop Metal Ratchet



Small return angle

The fine 72 tooth ratchet mechanism has a low return angle of 5°. This short stroke allows fast and precise work in small spaces.



Extremely slim Long leverage

Forged, chrome-molybdenum steel ratchet has no torque limitation and is designed to fit in tight areas.



Secure socket lock mechanism

The ball lock holds sockets and attachments securely, ensuring safe operation. To release the socket simply press the release button.

Wera Metal Ratchets and Ratchet Sets			
Part Number	Description	Pcs/ Pkg	Price
05004004055	Wera Zyklop Metal ratchet, switch lever, 1/4 inch drive, 5 degree return angle, all metal construction, secure socket lock mechanism.	1	\$46.00
05004034055	Wera Zyklop Metal ratchet, switch lever, 3/8 inch drive, 5 degree return angle, all metal construction, secure socket lock mechanism.	1	\$53.00
05004064055	Wera Zyklop Metal ratchet, switch lever, 1/2 inch drive, 5 degree return angle, all metal construction, secure socket lock mechanism.	1	\$61.00



Switch Lever

Switch lever for convenient change of direction.


Wera

Zyklop Metal Ratchet and Socket Sets



1/4 inch Drive Imperial and Metric Ratchet Sets



1/4 inch Drive Metal Ratchet Sets		
Part Number	Description	Price
05004021055	Wera socket set with Zyklop Metal switch lever ratchet, 1/4 inch drive, SAE. 28 pieces. Durable cloth pouch included. Manufacturer part number: 004021.	\$109.00
05004018055	Wera socket set with Zyklop Metal switch lever ratchet, 1/4 inch drive, metric. 28 pieces. Durable cloth pouch included. Manufacturer part number: 004018.	\$109.00

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect only.



Wera socket set with Zyklop Metal switch lever ratchet, 1/4 inch drive, SAE, 28 pieces. Includes the pieces listed in the table below.



Wera socket set with Zyklop Metal switch lever ratchet, 1/4 inch drive, metric, 28 pieces. Includes the pieces listed in the table below.

05004021055 Contents		
	1/4 Zyklop Metal ratchet	
	6-point socket, 23mm long	3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2
	Extension	1/4 x 150
	Wobble Extension	1/4 x 56
	Bit adapter	1/4 x 1/4 x 37
	Hex-Plus bit, 25mm long	3, 4, 5, 6
	Phillips bit, 25mm long	PH1, PH2, PH3
	Posidriv® bit, 25mm long	PZ1, PZ2
	Torx® bit, 25mm long	TX10, TX15, TX20, TX25, TX27, TX30

Note: Fractional dimensions are in inches.
Whole and decimal dimensions are in millimeters.

05004018055 Contents		
	1/4 Zyklop Metal ratchet	
	6-point socket, 23mm long	5, 5.5, 6, 7, 8, 10, 11, 12, 13
	Extension	1/4 x 150
	Wobble Extension	1/4 x 56
	Bit adapter	1/4 x 1/4 x 37
	Hex-Plus bit, 25mm long	3, 4, 5, 6
	Phillips bit, 25mm long	PH1, PH2, PH3
	Posidriv® bit, 25mm long	PZ1, PZ2
	Torx® bit, 25mm long	TX10, TX15, TX20, TX25, TX27, TX30

Note: Fractional dimensions are in inches.
Whole and decimal dimensions are in millimeters.


Wera

Zyklop Metal Ratchet and Socket Sets



3/8 inch Drive Imperial and Metric Ratchet Sets



3/8 inch Drive Metal Ratchet Sets		
Part Number	Description	Price
05004051055	Wera socket set with Zyklop Metal switch lever ratchet, 3/8 inch drive, SAE. 29 pieces. Durable cloth pouch included. Manufacturer part number 004051.	\$140.00
05004048055	Wera socket set with Zyklop Metal switch lever ratchet, 1/2 inch drive, metric. 28 pieces. Durable cloth pouch included. Manufacturer part number 004078.	\$140.00

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect.



Wera socket set with Zyklop Metal switch lever ratchet, 3/8 inch drive, SAE, 29 pieces. Includes the pieces listed in the table below.



Wera socket set with Zyklop Metal switch lever ratchet, 3/8 inch drive, metric, 29 pieces. Includes the pieces listed in the table below.

05004051055 Contents		
	3/8 Zyklop Metal ratchet	
	6-point socket	1/4 x 29, 5/16 x 29, 3/8 x 29, 7/16 x 29, 1/2 x 29, 9/16 x 29, 5/8 x 30, 11/16 x 30, 3/4 x 30
	Extension	3/8 x 200
	Wobble Extension	3/8 x 76
	Bit adaptor	3/8 x 1/4 x 44
	Hex-plus bit, 25mm long	5/32, 3/16, 7/32, 1/4, 5/16
	Phillips bit, 25mm long	PH1, PH2, PH3
	Posidriv® bit, 25mm long	PZ1, PZ2
	Torx® bit, 25mm long	TX 15, TX 20, TX 25, TX 27, TX 30, TX 40

Note: Fractional dimensions are in inches.
Whole and decimal dimensions are in millimeters.

05004048055 Contents		
	3/8 Zyklop Metal ratchet	
	6-point socket	8 x 29, 10 x 29, 12 x 29, 13 x 29, 15 x 29, 16 x 30, 17 x 30, 18 x 30, 19 x 30
	Extension	3/8 x 200
	Wobble Extension	3/8 x 76
	Bit adaptor	3/8 x 1/4 x 44
	Hex-Plus bit, 25mm long	3, 4, 5, 6, 8
	Phillips bit, 25mm long	PH1, PH2, PH3
	Posidriv® bit, 25mm long	PZ1, PZ2
	Torx® bit, 25mm long	TX 15, TX 20, TX 25, TX 27, TX 30, TX 40

Note: Fractional dimensions are in inches.
Whole and decimal dimensions are in millimeters.


Wera

Zyklop Metal Ratchet and Socket Sets



1/2 inch Drive Imperial and Metric Ratchet Sets



1/2 inch Drive Metal Ratchet Sets		
Part Number	Description	Price
05004081055	Wera socket set with Zyklop Metal switch lever ratchet, 1/2 inch drive, SAE. 28 pieces. Durable cloth pouch included. Manufacturer part number 004081.	\$203.00
05004078055	Wera socket set with Zyklop Metal switch lever ratchet, 1/2 inch drive, metric. 28 pieces. Durable cloth pouch included. Manufacturer part number 004078.	\$203.00

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect.



Wera socket set with Zyklop Metal switch lever ratchet, 1/2 inch drive, SAE, 28 pieces. Includes the pieces listed in the table below.



Wera socket set with Zyklop Metal switch lever ratchet, 1/2 inch drive, metric, 28 pieces. Includes the pieces listed in the table below.

05004081055 Contents		
	1/2 Zyklop Metal ratchet	
	6-point socket, 37mm long	3/8, 7/16, 1/2, 9/16, 19/32, 5/8, 11/16, 3/4, 25/32, 13/16
	Extension	1/2 x 250
	Wobble Extension	1/2 x 52
	Bit adaptor	1/2 x 5/16 x 50
	Hex-Plus bit, 30mm long	7/32, 1/4, 5/16, 3/8
	Phillips bit, 32mm long	PH2, PH3
	Torx® bit, 35mm long	TX20, TX25, TX27, TX30, TX40, TX45, TX50, TX55

Note: Fractional dimensions are in inches. Whole and decimal dimensions are in millimeters.

05004078055 Contents		
	1/2 Zyklop Metal ratchet	
	6-point socket, 37mm long	10, 11, 12, 13, 14, 15, 16, 17, 18, 19
	Extension	1/2 x 250
	Wobble Extension	1/2 x 52
	Bit adaptor	1/2 x 5/16 x 50
	Hex-Plus bit, 30mm long	5, 6, 8, 10
	Phillips bit, 32mm long	PH2, PH3
	Torx® bit, 35mm long	TX20, TX25, TX27, TX30, TX40, TX45, TX50, TX55

Note: Fractional dimensions are in inches. Whole and decimal dimensions are in millimeters.



Zyklop Speed Ratchet



Small return angle

The fine 72 tooth ratchet mechanism has a low return angle of 5°. This short stroke allows fast and precise work in small spaces.



Swivel ratchet head


The ratchet head pivots freely and locks at 0°, 15° and 90°, making it possible to work in confined spaces with ample hand clearance.



Simple direction change

Rotating the large thumbwheel quickly changes rotation from clockwise to counterclockwise from any position of the ratchet head.

Wera Speed Ratchets		
Part Number	Description	Price
<u>05003500055</u>	Wera Zyklop Speed ratchet, 1/4 inch drive, with locking swivel head and ergonomic grip handle. Manufacturer part number 003500.	\$76.00
<u>05003550055</u>	Wera Zyklop Speed ratchet, 3/8 inch drive, with locking swivel head and ergonomic grip handle. Manufacturer part number 003550.	\$85.00
<u>05003600055</u>	Wera Zyklop Speed ratchet, 1/2 inch drive, with locking swivel head and ergonomic grip handle. Manufacturer part number 003600.	\$93.00



Unbelievably fast

The gyrating mass design along with the Kraftform handle and free-turning sleeve allow for rapid rotation when used as a screwdriver.


Wera

Zyklop Speed Ratchet and Socket Sets



1/4 inch Drive Metric Ratchet Sets



Wera driver bit and socket set with Zyklop Speed ratchet, 1/4 inch drive, metric, 42 pieces. Includes the pieces listed in the table below.

05003533055 Contents		
	1/4 Zyklop Speed ratchet	
	Sliding T-handle	1/4 x 110
	6-point socket, 23mm long	4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13, 14
	Wobble extension	1/4 x 56
	Universal joint	1/4 x 35.5
	Lockable extension	1/4 x 75, 1/4 x 150
	Bit adaptor	1/4 x 37
	Slotted bit, 25mm long	0.6 x 4.5, 1.0 x 5.5, 1.2 x 8
	Hex-Plus bit, 25mm long	3, 4, 5, 6, 8
	Phillips bit, 25mm long	PH1, PH2, PH3
	Posidriv® bit, 25mm long	PZ1, PZ2, PZ3
	Torx® bit, 25mm long	TX8, TX9, TX10, TX15, TX20, TX25, TX30, TX40

Note: Fractional dimensions are in inches. Whole and decimal dimensions are in millimeters.

1/4 inch Drive Metric Ratchet Sets		
Part Number	Description	Price
05051045055	Wera driver bit and socket set with Zyklop Speed ratchet, 1/4 inch drive, metric, 26 pieces. Durable cloth pouch included. Manufacturer part number 051045.	\$126.00
Note: Screwdriver bits and bit-holders are warranted against manufacturer defect only.		



Wera driver bit and socket set with Zyklop Speed ratchet, 1/4 inch drive, metric, 26 pieces. Includes the pieces listed in the table below.

05051045055 Contents		
	1/4 Zyklop Speed ratchet	
	6-point socket	5.5, 6, 7, 8, 10, 12, 13
	Lockable extension	1/4 x 150
	Bit adaptor	1/4 x 37
	Slotted bit	1.0 x 5.5 x 50
	Hex-Plus bit, 50mm long	3, 4, 5, 6
	Phillips bit, 50mm long	PH1, PH2, PH3
	Posidriv® bit, 50mm long	PZ1, PZ2
	Torx® bit, 50mm long	TX10, TX15, TX20, TX25, TX30, TX40

Note: Fractional dimensions are in inches. Whole and decimal dimensions are in millimeters.



Zyklop Mini Ratchet

The Wera Zyklop mini bit ratchet is designed for easy, flexible fastening using 1/4" bits and sockets. Its compact design features a small 6° return angle, a thumbwheel for quick operation and a switch lever for convenient direction change. It's constructed of chrome vanadium steel with a brushed chrome-plated finish for corrosion protection.

Wera Zyklop Mini Bit Ratchet		
Part Number	Description	Price
05073230055	Wera Zyklop Mini bit ratchet, 1/4 inch drive, 6 degree return angle. Adapter for 1/4-inch sockets included. Manufacturer part number 073230.	\$36.00



Thumbwheel



Switch Lever



Small return angle





Wera Zyklop Mini Bit Ratchet Sets



Zyklop Mini Bit Ratchet Sets		
Part Number	Description	Price
05073220055	Wera Tool-Check driver bit and socket set with Zyklop Mini bit ratchet, 1/4 inch drive, metric. 38 pieces. Plastic case included. Manufacturer part number 073220.	\$102.00
TW-DB-SET-28R	Wera Bit-Check driver bit set with Zyklop Mini bit ratchet, 1/4 inch drive, SAE. 31 pieces. Plastic case included. Manufacturer part number 346293.	\$77.00

Note: Screwdriver bits are warranted against manufacturer defect.



05073220055



TW-DB-SET-28R

Wera Tool-Check driver bit and socket set with Zyklop Mini bit ratchet, 1/4 inch drive, SAE, 38 pieces. Includes the pieces listed in the table below.

Wera Bit-Check driver bit set with Zyklop Mini bit ratchet, 1/4 inch drive, SAE, 31 pieces. Includes the pieces listed in the table below.

05073220055 Contents		
	Zyklop Mini bit ratchet	
	Rapidaptor bit holder	1/4 x 50
	1/4 socket adaptor	1/4 x 25
	Slotted	1.0 x 5.5 x 25
	Hex-Plus bit, 25mm long	3, 4, 5, 6, 8
	Phillips bit, 25mm long	(2) PH1, (3) PH2, PH3
	Torx® bit, 25mm long	TX10, TX15, TX20, TX25, TX30, TX40
	Tamper-proof Torx® bit, 25mm long	TX10, TX15, TX20, TX25, TX30
	Posidriv® bit, 25mm long	PZ1, (3) PZ2, PZ3
	6-point socket	5.5, 6.0, 7.0, 8.0 10.0, 12.0, 13.0

TW-DB-SET-28R Contents		
	Zyklop Mini bit ratchet	
	1/4 Rapidaptor bit holder	1/4 x 50
	1/4 socket adaptor	1/4 x 25
	Phillips bit, 25mm long	(2) PH1, (3) PH2, PH3
	Torx® bit, 25mm long	TX10, TX15, TX20, TX25, TX30, TX40
	Tamper-proof Torx® bit, 25mm long	TX10, TX15, TX20, TX25, TX30
	Slotted bit	1.0 x 5.5 x 25
	Hex-Plus bit, 25mm long	3/32, 1/8, 5/32, 3/16, 1/4
	Square bit, 25mm long	#1, (3) #2, #3

Note: Fractional dimensions are in inches. Whole and decimal dimensions are in millimeters.