


**Wera**

# Zyklop Metal Ratchet and Socket Sets



## 1/4 inch Drive Imperial and Metric Ratchet Sets



| 1/4 inch Drive Metal Ratchet Sets |                                                                                                                                                            |          |
|-----------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------|----------|
| Part Number                       | Description                                                                                                                                                | Price    |
| <b>05004021055</b>                | Wera socket set with Zyklop Metal switch lever ratchet, 1/4 inch drive, SAE. 28 pieces. Durable cloth pouch included. Manufacturer part number: 004021.    | \$109.00 |
| <b>05004018055</b>                | Wera socket set with Zyklop Metal switch lever ratchet, 1/4 inch drive, metric. 28 pieces. Durable cloth pouch included. Manufacturer part number: 004018. | \$109.00 |

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect only.



Wera socket set with Zyklop Metal switch lever ratchet, 1/4 inch drive, SAE, 28 pieces. Includes the pieces listed in the table below.



Wera socket set with Zyklop Metal switch lever ratchet, 1/4 inch drive, metric, 28 pieces. Includes the pieces listed in the table below.

| 05004021055 Contents |                           |                                                    |
|----------------------|---------------------------|----------------------------------------------------|
|                      | 1/4 Zyklop Metal ratchet  |                                                    |
|                      | 6-point socket, 23mm long | 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2 |
|                      | Extension                 | 1/4 x 150                                          |
|                      | Wobble Extension          | 1/4 x 56                                           |
|                      | Bit adapter               | 1/4 x 1/4 x 37                                     |
|                      | Hex-Plus bit, 25mm long   | 3, 4, 5, 6                                         |
|                      | Phillips bit, 25mm long   | PH1, PH2, PH3                                      |
|                      | Posidriv® bit, 25mm long  | PZ1, PZ2                                           |
|                      | Torx® bit, 25mm long      | TX10, TX15, TX20, TX25, TX27, TX30                 |

Note: Fractional dimensions are in inches.  
Whole and decimal dimensions are in millimeters.

| 05004018055 Contents |                           |                                    |
|----------------------|---------------------------|------------------------------------|
|                      | 1/4 Zyklop Metal ratchet  |                                    |
|                      | 6-point socket, 23mm long | 5, 5.5, 6, 7, 8, 10, 11, 12, 13    |
|                      | Extension                 | 1/4 x 150                          |
|                      | Wobble Extension          | 1/4 x 56                           |
|                      | Bit adapter               | 1/4 x 1/4 x 37                     |
|                      | Hex-Plus bit, 25mm long   | 3, 4, 5, 6                         |
|                      | Phillips bit, 25mm long   | PH1, PH2, PH3                      |
|                      | Posidriv® bit, 25mm long  | PZ1, PZ2                           |
|                      | Torx® bit, 25mm long      | TX10, TX15, TX20, TX25, TX27, TX30 |

Note: Fractional dimensions are in inches.  
Whole and decimal dimensions are in millimeters.


**Wera**

# Zyklop Metal Ratchet and Socket Sets



## 3/8 inch Drive Imperial and Metric Ratchet Sets



| 3/8 inch Drive Metal Ratchet Sets |                                                                                                                                                           |          |
|-----------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------|----------|
| Part Number                       | Description                                                                                                                                               | Price    |
| <b>05004051055</b>                | Wera socket set with Zyklop Metal switch lever ratchet, 3/8 inch drive, SAE. 29 pieces. Durable cloth pouch included. Manufacturer part number 004051.    | \$140.00 |
| <b>05004048055</b>                | Wera socket set with Zyklop Metal switch lever ratchet, 1/2 inch drive, metric. 28 pieces. Durable cloth pouch included. Manufacturer part number 004078. | \$140.00 |

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect.



Wera socket set with Zyklop Metal switch lever ratchet, 3/8 inch drive, SAE, 29 pieces. Includes the pieces listed in the table below.



Wera socket set with Zyklop Metal switch lever ratchet, 3/8 inch drive, metric, 29 pieces. Includes the pieces listed in the table below.

| 05004051055 Contents |                          |                                                                                               |
|----------------------|--------------------------|-----------------------------------------------------------------------------------------------|
|                      | 3/8 Zyklop Metal ratchet |                                                                                               |
|                      | 6-point socket           | 1/4 x 29, 5/16 x 29, 3/8 x 29, 7/16 x 29, 1/2 x 29, 9/16 x 29, 5/8 x 30, 11/16 x 30, 3/4 x 30 |
|                      | Extension                | 3/8 x 200                                                                                     |
|                      | Wobble Extension         | 3/8 x 76                                                                                      |
|                      | Bit adaptor              | 3/8 x 1/4 x 44                                                                                |
|                      | Hex-plus bit, 25mm long  | 5/32, 3/16, 7/32, 1/4, 5/16                                                                   |
|                      | Phillips bit, 25mm long  | PH1, PH2, PH3                                                                                 |
|                      | Posidriv® bit, 25mm long | PZ1, PZ2                                                                                      |
|                      | Torx® bit, 25mm long     | TX 15, TX 20, TX 25, TX 27, TX 30, TX 40                                                      |

Note: Fractional dimensions are in inches.  
Whole and decimal dimensions are in millimeters.

| 05004048055 Contents |                          |                                                                                |
|----------------------|--------------------------|--------------------------------------------------------------------------------|
|                      | 3/8 Zyklop Metal ratchet |                                                                                |
|                      | 6-point socket           | 8 x 29, 10 x 29, 12 x 29, 13 x 29, 15 x 29, 16 x 30, 17 x 30, 18 x 30, 19 x 30 |
|                      | Extension                | 3/8 x 200                                                                      |
|                      | Wobble Extension         | 3/8 x 76                                                                       |
|                      | Bit adaptor              | 3/8 x 1/4 x 44                                                                 |
|                      | Hex-Plus bit, 25mm long  | 3, 4, 5, 6, 8                                                                  |
|                      | Phillips bit, 25mm long  | PH1, PH2, PH3                                                                  |
|                      | Posidriv® bit, 25mm long | PZ1, PZ2                                                                       |
|                      | Torx® bit, 25mm long     | TX 15, TX 20, TX 25, TX 27, TX 30, TX 40                                       |

Note: Fractional dimensions are in inches.  
Whole and decimal dimensions are in millimeters.


**Wera**

# Zyklop Metal Ratchet and Socket Sets



## 1/2 inch Drive Imperial and Metric Ratchet Sets



| 1/2 inch Drive Metal Ratchet Sets |                                                                                                                                                           |          |
|-----------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------|----------|
| Part Number                       | Description                                                                                                                                               | Price    |
| <b>05004081055</b>                | Wera socket set with Zyklop Metal switch lever ratchet, 1/2 inch drive, SAE. 28 pieces. Durable cloth pouch included. Manufacturer part number 004081.    | \$203.00 |
| <b>05004078055</b>                | Wera socket set with Zyklop Metal switch lever ratchet, 1/2 inch drive, metric. 28 pieces. Durable cloth pouch included. Manufacturer part number 004078. | \$203.00 |

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect.



Wera socket set with Zyklop Metal switch lever ratchet, 1/2 inch drive, SAE, 28 pieces. Includes the pieces listed in the table below.



Wera socket set with Zyklop Metal switch lever ratchet, 1/2 inch drive, metric, 28 pieces. Includes the pieces listed in the table below.

| 05004081055 Contents |                           |                                                            |
|----------------------|---------------------------|------------------------------------------------------------|
|                      | 1/2 Zyklop Metal ratchet  |                                                            |
|                      | 6-point socket, 37mm long | 3/8, 7/16, 1/2, 9/16, 19/32, 5/8, 11/16, 3/4, 25/32, 13/16 |
|                      | Extension                 | 1/2 x 250                                                  |
|                      | Wobble Extension          | 1/2 x 52                                                   |
|                      | Bit adaptor               | 1/2 x 5/16 x 50                                            |
|                      | Hex-Plus bit, 30mm long   | 7/32, 1/4, 5/16, 3/8                                       |
|                      | Phillips bit, 32mm long   | PH2, PH3                                                   |
|                      | Torx® bit, 35mm long      | TX20, TX25, TX27, TX30, TX40, TX45, TX50, TX55             |

Note: Fractional dimensions are in inches. Whole and decimal dimensions are in millimeters.

| 05004078055 Contents |                           |                                                |
|----------------------|---------------------------|------------------------------------------------|
|                      | 1/2 Zyklop Metal ratchet  |                                                |
|                      | 6-point socket, 37mm long | 10, 11, 12, 13, 14, 15, 16, 17, 18, 19         |
|                      | Extension                 | 1/2 x 250                                      |
|                      | Wobble Extension          | 1/2 x 52                                       |
|                      | Bit adaptor               | 1/2 x 5/16 x 50                                |
|                      | Hex-Plus bit, 30mm long   | 5, 6, 8, 10                                    |
|                      | Phillips bit, 32mm long   | PH2, PH3                                       |
|                      | Torx® bit, 35mm long      | TX20, TX25, TX27, TX30, TX40, TX45, TX50, TX55 |

Note: Fractional dimensions are in inches. Whole and decimal dimensions are in millimeters.


**Wera**

# Zyklop Speed Ratchet and Socket Sets



## 1/4 inch Drive Metric Ratchet Sets



| 1/4 inch Drive Metric Ratchet Sets                                                     |                                                                                                                                                             |          |
|----------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------|----------|
| Part Number                                                                            | Description                                                                                                                                                 | Price    |
| <b>05051045055</b>                                                                     | Wera driver bit and socket set with Zyklop Speed ratchet, 1/4 inch drive, metric, 26 pieces. Durable cloth pouch included. Manufacturer part number 051045. | \$126.00 |
| Note: Screwdriver bits and bit-holders are warranted against manufacturer defect only. |                                                                                                                                                             |          |



Wera driver bit and socket set with Zyklop Speed ratchet, 1/4 inch drive, metric, 26 pieces. Includes the pieces listed in the table below.

| 05051045055 Contents |                          |                                    |
|----------------------|--------------------------|------------------------------------|
|                      | 1/4 Zyklop Speed ratchet |                                    |
|                      | 6-point socket           | 5.5, 6, 7, 8, 10, 12, 13           |
|                      | Lockable extension       | 1/4 x 150                          |
|                      | Bit adaptor              | 1/4 x 37                           |
|                      | Slotted bit              | 1.0 x 5.5 x 50                     |
|                      | Hex-Plus bit, 50mm long  | 3, 4, 5, 6                         |
|                      | Phillips bit, 50mm long  | PH1, PH2, PH3                      |
|                      | Posidriv® bit, 50mm long | PZ1, PZ2                           |
|                      | Torx® bit, 50mm long     | TX10, TX15, TX20, TX25, TX30, TX40 |

Note: Fractional dimensions are in inches. Whole and decimal dimensions are in millimeters.