



# Wera Wrenches

## Hex-Plus L-Keys Sets

Wera Hex-plus L-keys for hexagon socket screws provide more contact surface inside the screw, which prevents rounding.

L-keys can transfer high torque but do not twist to any great extent, or shear off, to minimize risk of injury. Wera's extensive experience with narrow tolerance manufacturing techniques, careful material selection, and refined hardening technologies delivers maximum safety at work.



Hex Ball-end Tip



Thermoplastic Multi-color Sleeve



Engraved Size Identification

### Hex-Plus L-Key Sets

| Part Number                        | Number of Pieces | Part Image | Features                                                      | Material                                     | Set Includes                                                                                                                                                                                   | Price   |
|------------------------------------|------------------|------------|---------------------------------------------------------------|----------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------|
| <a href="#"><u>05022639055</u></a> | 9                |            | Ball-end tip<br>Hex-plus tip                                  | Blacklaser Steel<br>With Multicolor<br>Grips | (9) multicolor hex L-keys (5/64, 3/32, 1/8, 5/32, 3/16, 7/32, 1/4, 5/16 and 3/8in), durable cloth pouch                                                                                        | \$46.00 |
| <a href="#"><u>05022089055</u></a> | 9                |            | Ball-end tip<br>Hex-plus tip                                  |                                              | (9) multicolor hex L-keys (1.5, 2, 2.5, 3, 4, 5, 6, 8 and 10mm), fold-out L-key holder                                                                                                         | \$41.00 |
| <a href="#"><u>05022210001</u></a> | 9                |            | Ballpoint holding<br>function<br>Ball-end tip<br>Hex-plus tip |                                              | (9) color-coded BlackLaser L-key hex keys (1.5 x 90mm, 2.0 x 101mm, 2.5 x 112mm, 3.0 x 123mm, 4.0 x 137mm, 5.0 x 154mm, 6.0 x 172mm, 8.0 x 195mm, 10.0 x 224mm), (1) wear-resistant clip       | \$52.00 |
| <a href="#"><u>05022640001</u></a> | 9                |            | Ball-end tip<br>Hex-plus tip                                  |                                              | (9) color-coded BlackLaser L-key hex keys (5/64 x 101mm, 3/32 x 112mm, 1/8 x 123mm, 5/32 x 137mm, 3/16 x 154mm, 7/32 x 172mm, 1/4 x 185mm, 5/16 x 195mm, 3/8 x 224mm), (1) wear-resistant clip | \$40.00 |
| <a href="#"><u>05022641001</u></a> | 9                |            | Ball-end tip<br>Hex-plus tip                                  |                                              | (9) color-coded BlackLaser L-key hex keys (5/64 x 50mm, 3/32 x 56mm, 1/8 x 63mm, 5/32 x 71mm, 3/16 x 80mm, 7/32 x 90mm, 1/4 x 100mm, 5/16 x 112mm, 3/8 x 125mm), (1) wear-resistant clip       | \$42.00 |
| <a href="#"><u>05133164001</u></a> | 9                |            | Ball-end tip<br>Hex-plus tip                                  |                                              | (9) color-coded BlackLaser L-key hex keys (1.5 x 50mm, 2.0 x 56mm, 2.5 x 63mm, 3.0 x 71mm, 4.0 x 80mm, 5.0 x 90mm, 6.0 x 100mm, 8.0 x 112mm, 10.0 x 125mm), (1) wear-resistant clip            | \$40.00 |

Note: L-keys are warranted against manufacturer defect only.



# Wera Wrenches

## Hex-Plus L-Key Sets - Cont'd

| Part Number                          | Number of Pieces | Part Image | Features                                                   | Material                              | Set Includes                                                                                                                                                                                        | Price   |
|--------------------------------------|------------------|------------|------------------------------------------------------------|---------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------|
| <a href="#"><u>TW-HK-SET-MM</u></a>  | 9                |            | Ball-end tip<br>Hex-plus tip                               | Blacklaser Steel                      | (9) BlackLaser hex L-keys (1.5, 2, 2.5, 3, 4, 5, 6, 8 and 10mm), fold-out L-key holder                                                                                                              | \$13.00 |
| <a href="#"><u>TW-HK-SET-STD</u></a> | 13               |            | Ball-end tip<br>Hex-plus tip                               |                                       | (13) hex L-keys (0.05, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16 and 3/8in), fold-out L-key holder                                                                             | \$24.00 |
| <a href="#"><u>05133180001</u></a>   | 9                |            | Ball-end tip<br>Hex-plus tip                               |                                       | (9) BlackLaser L-key hex keys (5/64 x 100mm, 3/32 x 112mm, 1/8 x 126mm, 5/32 x 140mm, 3/16 x 160mm, 7/32 x 180mm, 1/4 x 190mm, 5/16 x 200mm, 3/8 x 212mm), (1) wear-resistant clip                  | \$12.00 |
| <a href="#"><u>05021737001</u></a>   | 9                |            | Hex-plus tip                                               |                                       | (9) L-key hex keys with BlackLaser material (1.5 x 45mm, 2.0 x 50mm, 2.5 x 56mm, 3.0 x 63mm, 4.0 x 70mm, 5.0 x 80mm, 6.0 x 90mm, 8.0 x 100mm, 10.0 x 112mm), (1) wear-resistant clip                | \$4.00  |
| <a href="#"><u>05022669001</u></a>   | 9                |            | Ball-end tip<br>Hex-plus tip                               | Stainless steel with multicolor grips | (9) color-coded stainless steel L-key hex keys (1.5 x 90mm, 2.0 x 101mm, 2.5 x 112mm, 3.0 x 123mm, 4.0 x 137mm, 5.0 x 154mm, 6.0 x 172mm, 8.0 x 195mm, 10.0 x 224mm), (1) wear-resistant clip       | \$60.00 |
| <a href="#"><u>05022699001</u></a>   | 9                |            | Ballpoint holding function<br>Ball-end tip<br>Hex-plus tip |                                       | (9) color-coded stainless steel L-key hex keys (1.5 x 90mm, 2.0 x 101mm, 2.5 x 112mm, 3.0 x 123mm, 4.0 x 137mm, 5.0 x 154mm, 6.0 x 172mm, 8.0 x 195mm, 10.0 x 224mm), (1) wear-resistant clip       | \$70.00 |
| <a href="#"><u>05022860001</u></a>   | 9                |            | Ball-end tip<br>Hex-plus tip                               |                                       | (9) color-coded stainless steel L-key hex keys (5/64 x 101mm, 3/32 x 112mm, 1/8 x 123mm, 5/32 x 137mm, 3/16 x 154mm, 7/32 x 172mm, 1/4 x 185mm, 5/16 x 195mm, 3/8 x 224mm), (1) wear-resistant clip | \$60.00 |
| <a href="#"><u>05073544001</u></a>   | 9                |            | Ball-end tip<br>Hex-plus tip                               | Stainless steel                       | (9) stainless steel L-key hex keys (1.5 x 90mm, 2.0 x 101mm, 2.5 x 112mm, 3.0 x 123mm, 4.0 x 137mm, 5.0 x 154mm, 6.0 x 172mm, 8.0 x 195mm, 10.0 x 224mm), (1) wear-resistant clip                   | \$46.00 |
| <a href="#"><u>05073391001</u></a>   | 9                |            | Ball-end tip<br>Hex-plus tip                               | Chrome-plated steel                   | (9) chrome-plated L-key hex keys (1.5 x 90mm, 2.0 x 100mm, 2.5 x 112mm, 3.0 x 126mm, 4.0 x 140mm, 5.0 x 160mm, 6.0 x 180mm, 8.0 x 200mm, 10.0 x 219mm), (1) wear-resistant clip                     | \$18.00 |
| <a href="#"><u>05133163001</u></a>   | 9                |            | Ball-end tip<br>Hex-plus tip                               |                                       | (9) chrome-plated L-key hex keys (1.5 x 50mm, 2.0 x 56mm, 2.5 x 63mm, 3.0 x 71mm, 4.0 x 80mm, 5.0 x 90mm, 6.0 x 100mm, 8.0 x 112mm, 10.0 x 125mm), (1) wear-resistant clip                          | \$22.00 |
| <a href="#"><u>05022130001</u></a>   | 9                |            | Ballpoint holding function<br>Hex-plus tip                 |                                       | (9) chrome-plated L-key hex keys (1.5 x 90mm, 2.0 x 100mm, 2.5 x 112mm, 3.0 x 126mm, 4.0 x 140mm, 5.0 x 160mm, 6.0 x 180mm, 8.0 x 200mm, 10.0 x 219mm), (1) wear-resistant clip                     | \$36.00 |

Note: L-keys are warranted against manufacturer defect only.



# Wera Wrenches

## Torx L-Key Sets

Wera Torx L-keys for Torx socket screws provide more contact surface inside the screw, which prevents rounding.

L-keys can transfer high torque but do not twist to any great extent, or shear off, to minimize risk of injury. Wera's extensive experience with narrow tolerance manufacturing techniques, careful material selection, and refined hardening technologies delivers maximum safety at work.



Torx Ball-end Tip



Thermoplastic Multi-color Sleeve



Engraved Size Identification

| Torx L-Key Sets                    |                  |            |                                                            |                                              |                                                                                                                                                                                                                                       |         |
|------------------------------------|------------------|------------|------------------------------------------------------------|----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------|
| Part Number                        | Number of Pieces | Part Image | Features                                                   | Material                                     | Set Includes                                                                                                                                                                                                                          | Price   |
| <a href="#"><u>05073599001</u></a> | 9                |            | Demagnetizer<br>Ball-end tip                               | Blacklaser Steel<br>With Multicolor<br>Grips | (9) color-coded BlackLaser L-key hex keys, short end tamperproof torx, long end ball-end torx (T9 x 79mm, T8 x 76mm, T10 x 85mm, T15 x 90mm, T20 x 96mm, T25 x 104mm, T30 x 122mm, T40 x 132mm, T27 x 112mm), (1) wear-resistant clip | \$46.00 |
| <a href="#"><u>05024179001</u></a> | 9                |            | Ballpoint holding function<br>Ball-end tip<br>Hex-plus tip |                                              | (9) color-coded BlackLaser L-key hex keys (T8 x 76mm, T9 x 79mm, T10 x 85mm, T15 x 90mm, T20 x 96mm, T25 x 104mm, T27 x 112mm, T30 x 122mm, T40 x 132mm), (1) wear-resistant clip                                                     | \$46.00 |
| <a href="#"><u>05024480001</u></a> | 9                |            | Ball-end tip                                               |                                              | (9) color-coded BlackLaser L-key hex keys (T8 x 90mm, T9 x 101mm, T10 x 112mm, T15 x 123mm, T20 x 137mm, T25 x 154mm, T27 x 172mm, T30 x 195mm, T40 x 224mm)                                                                          | \$54.00 |
| <a href="#"><u>05024460001</u></a> | 9                |            | Ball-end tip                                               | Blacklaser Steel                             | (9) BlackLaser L-key hex keys (T8 x 90mm, T9 x 101mm, T10 x 112mm, T15 x 123mm, T20 x 137mm, T25 x 154mm, T27 x 172mm, T30 x 195mm, T40 x 224mm), (1) wear-resistant clip                                                             | \$48.00 |
| <a href="#"><u>05073598001</u></a> | 9                |            | Ball-end tip                                               |                                              | (9) BlackLaser L-key hex keys (T9 x 79mm, T10 x 85mm, T8 x 76mm, T15 x 90mm, T20 x 96mm, T25 x 104mm, T27 x 112mm, T30 x 122mm, T40 x 132mm), (1) wear-resistant clip                                                                 | \$30.00 |
| <a href="#"><u>05022689001</u></a> | 9                |            | Holding function                                           | Stainless steel                              | (9) color-coded stainless steel L-key torx keys (T8 x 90mm, T9 x 101mm, T10 x 112mm, T15 x 123mm, T20 x 137mm, T25 x 154mm, T27 x 172mm, T30 x 195mm, T40 x 224mm), (1) 2-component plastic clip                                      | \$68.00 |

Note: L-keys are warranted against manufacturer defect only.