



Ratcheting Combination Wrenches

Joker combination ratchet wrenches revolutionize the humble wrench. The 12-point open end features a unique 6-point stop plate that enables easier turning of bolts and also provides improved grip for loosening stubborn bolts. The fine tooth ratchet mechanism is exceptional for working in tight spaces. Joker wrenches feature chrome molybdenum steel construction with a nickel-chrome coating for corrosion protection. Offered in metric and imperial sizes.



Metric Ratcheting Combination Wrenches						
Part Number	Wrench Type	Fastening Size	Jaw Thickness	Overall Length	Wrench Features	Price
<u>05073268055</u>	Combination	8mm	0.22in (5.5mm)	9.3in (235mm)	Special nut holding feature Fine tooth ratchet	\$21.00
<u>05073270055</u>		10mm		6.7in (171mm)		\$22.00
<u>05073271055</u>		11mm	0.25in (6.3mm)	6.3in (159mm)		\$23.00
<u>05073272055</u>		12mm	0.26in (6.6mm)	7.4in (188mm)		\$24.00
<u>05073273055</u>		13mm	0.28in (7.0mm)	6.5in (165mm)		\$24.00
<u>05073274055</u>		14mm	0.30in (7.7mm)	9.7in (246mm)		\$25.00
<u>05073275055</u>		15mm	0.31in (7.8mm)	8.3in (212mm)		\$27.00
<u>05073276055</u>		16mm	0.32in (8.2mm)	7.0in (177mm)		\$28.00
<u>05073277055</u>		17mm	0.33in (8.5mm)	6.5in (165mm)		\$31.00
<u>05073278055</u>		18mm	0.35in (9.0mm)	6.3in (159mm)		\$32.00
<u>05073279055</u>		19mm	0.37in (9.5mm)	7.4in (188mm)		\$35.00

Metric Ratcheting Combination Wrench Sets				
Part Number	Number of Pieces	Part Image	Set Includes	Price
<u>05073290055</u>	4		(4) ratcheting combination wrenches (10, 13, 17 and 19mm), durable cloth pouch	\$107.00
<u>05020013055</u>	11		(8) ratcheting combination wrenches (8, 10, 11, 12, 13, 14, 15, 16, 17, 18 and 19mm), durable cloth pouch	\$287.00



Imperial Ratcheting Combination Wrenches						
Part Number	Wrench Type	Fastening Size	Jaw Thickness	Overall Length	Wrench Features	Price
<u>05073280055</u>	Combination	5/16in	0.22in (5.5mm)	5.7in (144mm)	Special nut holding feature Fine tooth ratchet	\$21.00
<u>05073281055</u>		3/8in		7.9in (200mm)		\$22.00
<u>05073282055</u>		7/16in	0.25in (6.3mm)	5.7in (144mm)		\$24.00
<u>05073283055</u>		1/2in	0.28in (7.0mm)	4.7in (119mm)		\$24.00
<u>05073284055</u>		9/16in	0.30in (7.7mm)	9.3in (235mm)		\$25.00
<u>05073285055</u>		5/8in	0.32in (8.2mm)	7.0in (177mm)		\$28.00
<u>05073286055</u>		11/16in	0.35in (9.0mm)	9.7in (246mm)		\$32.00
<u>05073287055</u>		3/4in	0.37in (9.5mm)	8.3in (212mm)		\$35.00

Imperial Ratcheting Combination Wrench Sets				
Part Number	Number of Pieces	Part Image	Set Includes	Price
<u>05073295055</u>	4		(4) ratcheting combination wrenches (7/16, 1/2, 9/16 and 3/4in), durable cloth pouch	\$107.00
<u>05020012055</u>	8		(8) ratcheting combination wrenches (5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16 and 3/4in), durable cloth pouch	\$205.00