



Wera Tool Sets

Maintenance Sets

Wera maintenance sets are compact tool sets with the most important screwdriving tools for maintenance jobs both indoors as well as outdoors. The sets come in two variations, metric and imperial.

Features

- Incredibly fast 1/4 in Zyklop speed ratchet with pivoting ratchet head and 5 predefined locking positions
- Manual and power tool sockets (non-impact) with ball-stop groove and knurling at lower end for more grip
- Joker double open-end wrench with holding function, limit stop, small return angle, and extreme gripping teeth
- VDE-insulated Kraftform 817 VDE bitholding screwdriver with anti-roll protection
- VDE blades (157 mm length) with practical spinning function, anti-roll protection, and "Take-it-easy" tool finder: color-coding by profile and laser-engraved size indicator
- Set includes a robust textile box




Metric Maintenance Set						
Part Number	Number of Pieces	Part Image	Type	Size	Set Includes	Price
05135870001	35		n/a		(1) Kraftform handle for interchangeable VDE blades	\$208.00
			 Phillips	#1, #2	(12) Kraftform Kompakt VDE blades (slotted: 2.5, 3.5, 4, 5.5mm, Phillips: #1, #2, Pozidriv: #1, #2, torx: T10, T15, T20, T25)	
			 Slotted	2.5, 3.5, 4, 5.5mm		
			 Torx	T10, T15, T20, T25		
			 Pozidriv	#1, #2		
			 Slotted	2.5mm	(1) Kraftform standard 2.5mm slotted screwdriver	
			Combination wrench	10mm, 13mm	(1) Joker combination wrench (10mm/13mm)	
			Speed ratched	1/4in drive	(1) Zyklop Speed ratchet with 1/4in drive	
		  	Adapter	1/4in	(1) Zyklop 1/4in bit adapter	
					(1) 1/4in universal bit holder	
					(1) Zyklop 1/4in extension with free-turning sleeve	
			 Internal Hex	5.5mm, 6mm, 7mm, 8mm, 10mm, 11mm, 12mm, 13mm	(8) 1/4in sockets (5.5mm - 13mm)	
			 Phillips	#1, #2	(7) 1in standard bits (Phillips: #1, #2, hex: 3mm, 4mm, 5mm, 6mm, torx: T25)	
			 Hex	3mm, 4mm, 5mm, 6mm		
			 Torx	T25		
			n/a		(1) screw gripper attachment	



Wera Tool Sets



Interchangeable System



Take-it-Easy Tool Finder



Compact Maintenance



ANTI-SLIP



PRESS TO UNLOCK

KRAFTFORM
ERGONOMICS30°
SMALL
ANGLEFLEXIBLE
HEAD

Imperial Maintenance Set

Part Number	Number of Pieces	Part Image	Type	Tip Size	Set Includes	Price
05135871001	35		n/a		(1) Kraftform handle for interchangeable VDE blades	\$208.00
			 Phillips	#1, #2	(12) Kraftform Kompakt VDE blades (slotted: 2.5, 3.5, 4, 5.5mm, Phillips: #1, #2, torx: T10, T15, T20, T25, square: #1, #2)	
			 Slotted	2.5, 3.5, 4, 5.5mm		
			 Torx	T10, T15, T20, T25		
			 Square	#1, #2		
			 Slotted	2.5mm	(1) Kraftform standard 2.5mm slotted screwdriver	
			Combination wrench	1/2in	(1) 1/2in Joker combination wrench	
			Speed ratchet	1/4in	(1) Zyklop Speed ratchet with 1/4in drive	
			Adapter	1/4in	(1) Zyklop 1/4in bit adapter	
					(1) 1/4in universal bit holder	
			Extension		(1) Zyklop 1/4in extension with free-turning sleeve	
			 Internal Hex	7/32in, 1/4in, 9/32in, 5/16in, 3/8in, 7/16in, 1/2in, 9/16in	(8) 1/4in sockets (7/32 - 9/16in)	
			 Phillips	#1, #2	(7) 1in standard bits (Phillips: #1, #2, hex: 1/8in, 5/32in, 7/32in, 1/4in, torx: T25)	
			 Hex	1/8in, 5/32in, 7/32in, 1/4in		
			 Torx	T25		
			n/a		(1) screw gripper attachment	