


















# Wera Socket and Driver Bit Sets


















Tool-Check Socket and Driver Bit Sets			Bit-Check Socket and Driver Bit Sets		
<i>05073220055</i>			<i>TW-DB-SET-28R</i>		
					
Wera Tool-Check standard driver bit and socket set, Phillips, Pozidriv, slotted, Torx, tamperproof torx and hex, 38 pieces, 1in bit length, 1/4in drive, metric.			Wera Bit-Check standard driver bit set, Phillips, Torx, tamperproof torx, hex, slotted and square, 31 pieces, 1in bit length, 1/4in drive, imperial.		
<i>Type</i>			<i>Type</i>		
<i>Bit Size</i>			<i>Bit Size</i>		
Zyklop Mini bit ratchet			Zyklop Mini bit ratchet		
Rapidaptor bit holder			Rapidaptor bit holder		
Socket adaptor			Socket adaptor		
	Slotted bit 25mm long	1.0 x 5.5mm		Phillips bit, 25mm long	(2) PH1, (3) PH2, PH3
	Hex-Plus bit 25mm long	3, 4, 5, 6, 8mm		Torx bit, 25mm long	T10, T15, T20, T25, T30, T40
	Phillips bit, 25mm long	(2) P#, (3) #2, #3		Tamperproof Torx bit, 25mm long	T10, T15, T20, T25, T30
	Torx bit, 25mm long	T10, T15, T20, T25, T30, T40		Slotted bit 25mm long	1.0 x 5.5mm
	Tamperproof Torx bit, 25mm long	T10, T15, T20, T25, T30		Hex-Plus bit 25mm long	3/32, 1/8, 5/32, 3/16, 1/4in
	Pozidriv bit 25mm long	#1, (3) #2, #3		Square bit 25mm long	#1, (3) #2, #3
	6-point socket	5.5, 6.0, 7.0, 8.0 10.0, 12.0, 13.0mm			

Note: Fractional dimensions are in inches. Whole and decimal dimensions are in millimeters.  
 Note: Screwdriver bits and bit-holders are warranted against manufacturer defect only.



# Wera Socket and Driver Bit Sets



Tool-Check PLUS Socket and Driver Bit Sets			Tool-Check Socket and Driver Bit Sets		
05056490001			05056491001		
					
Wera Tool-Check PLUS standard socket and driver bit set, Phillips, slotted, Torx, tamperproof torx, internal hex, external hex and Pozidriv, 39 pieces, 1in bit length, 1/4in drive, metric.		\$108.00	Wera Tool-Check standard socket and driver bit set, Phillips, slotted, Torx, tamperproof torx, hex and square, 39 pieces, 1in bit length, 1/4in drive, imperial.		\$113.00
Type		Size	Type		Size
Bitholding screwdriver		1/4in x 78mm	Bitholding screwdriver		1/4in x 78mm
Zyklop mini bit ratchet		1/4in	Zyklop mini bit ratchet		1/4in
Rapidaptor bit holder		1/4in x 50mm	Rapidaptor bit holder		1/4in x 50mm
Socket adaptor		1/4in x 25mm	Socket adaptor		1/4in x 25mm
	Phillips bit, 25mm long	(2) #1, (3) #2, #3		Phillips bit, 25mm long	(2) #1, (3) #2, #3
	Pozidriv bit, 25mm long	#1, (3) #2, #3			
	Torx bit, 25mm long	T10, T15, T20, T25, T30, T40		Torx bit, 25mm long	T10, T15, T20, T25, T30, T40
	Tamperproof Torx bit 25mm long	T10, T15, T20, T25, T30		Tamperproof Torx bit 25mm long	T10, T15, T20, T25, T30
	Slotted bit 25mm long	1.0 x 5.5mm		Slotted bit 25mm long	1.0 x 5.5mm
	Hex-Plus bit 25mm long	3.0, 4.0, 5.0, 6.0, 8.0mm		Hex-Plus bit 25mm long	3/32, 1/8, 5/32, 3/16, 1/4in
	6-point socket	5.5, 6.0, 7.0, 8.0, 10.0, 12.0, 13.0mm		6-point socket	3/16, 1/4, 5/16, 11/32, 3/8, 7/16, 1/2in

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect only.