



Bit Drivers, Bits, & Adapters

Tools that work for you

















Impact Driver bits

Wiha driver bits are impact rated for power tools and rigorously heat-treated to produce a bit lasting 120 times the service life compared to standard bits. Wiha's specially designed torsion zone absorbs the impact energy, allowing a maximum torsion flex that is unmatched. With TerminatorBlue Impact Bits you get the tightest-fit, precision-machined driver tips from the company that sets the standard for precision. Wiha's exact-fit tips eliminate excessive bit-wobble for increased driver accuracy. The result is a highly stable engagement with the screw head and a reduction in fastener cam-out that can lead to injury or damage to finished materials.

Features

- TST™ Torsion Stabilizing Technology for maximum flex and reduced tip stress
- Computer-controlled heat treatment for 120 times service life over Wiha standard bits
- Tuned torsion zone for maximum flex and reduced tip stress
- CVM premium quality tool steel for strength and durability
- Exact fit precision machined tips for reduced cam-out
- Fit with a standard 1/4 inch hex drive
- Bit lengths available: 1-inch; 2-inch; 3.5-inch
- Impact-rated for power tool applications
- Minimum hardness tolerance of 61 RHC +/- 1






Impact Driver Bits								
Part Number	Part Image	Type	Tip Size	Bit Length	Drive Size	Description	Package Quantity	Price
WT70002		 Phillips	#2	1in		Wiha TerminatorBlue #2 Phillips impact driver bit, 1in bit length, 1/4in drive, hexagonal. Package of 2.	2	\$3.50
WT70020		 Torx	T25			Wiha TerminatorBlue T25 Torx impact driver bit, 1in bit length, 1/4in drive, hexagonal. Package of 2.		\$3.50
WT70042		 Phillips	#2			Wiha TerminatorBlue #2 Phillips impact driver bit, 1in bit length, 1/4in drive, hexagonal. Package of 20.	20	\$15.00
WT70201			#1	1/4in	Wiha TerminatorBlue #1 Phillips impact driver bit, 2in bit length, 1/4in drive, hexagonal. Package of 2.	2	\$4.00	
WT70202			#2		Wiha TerminatorBlue #2 Phillips impact driver bit, 2in bit length, 1/4in drive, hexagonal. Package of 2.		\$4.00	
WT70203		#3	Wiha TerminatorBlue #3 Phillips impact driver bit, 2in bit length, 1/4in drive, hexagonal. Package of 2.		\$4.00			
WT70220		 Torx	T25		Wiha TerminatorBlue T25 Torx impact driver bit, 2in bit length, 1/4in drive, hexagonal. Package of 2.		\$4.00	
WT70222			T30		Wiha TerminatorBlue T30 Torx impact driver bit, 2in bit length, 1/4in drive, hexagonal. Package of 2.		\$4.00	
WT70223			T40		Wiha TerminatorBlue T40 Torx impact driver bit, 2in bit length, 1/4in drive, hexagonal. Package of 2.		\$4.00	
WT70269		 Phillips	#2		3.5in		Wiha TerminatorBlue #2 Phillips impact driver bit, 2in bit length, 1/4in drive, hexagonal. Package of 5.	5
WT70302			Wiha TerminatorBlue #2 Phillips impact driver bit, 3.5in bit length, 1/4in drive, hexagonal. Package of 2.	2		\$5.00		



Bit Drivers, Bits, & Adapters

Tools that work for you

Impact Driver Bit Sets

Impact Driver Bit Sets								
Part Number	Number of Pieces	Part Image	Type	Bit Size Tip Size x Length	Bit Quantity Included	Drive Size	Set Includes	Price
<u>WT70098</u>	8		<div><div>+</div>Phillips</div> <div><div>☆</div>Torx</div> <div><div>□</div>Square</div>	<div>#1 x 1in</div> <div>#2 x 1in</div> <div>T20 x 1in</div> <div>T25 x 1in</div> <div>T30 x 1in</div> <div>#1 x 1in</div> <div>#2 x 1in</div>	1	1/4in	(2) 1in Phillips bits (#1, #2), (3) 1in torx bits (T20, T25, T30), (2) 1in square bits (#1, #2), plastic case	\$13.00
<u>WT70297</u>	40		<div><div>+</div>Phillips</div> <div><div>☆</div>Torx</div> <div><div>□</div>Square</div> <div><div>⊗</div>Nut Setter</div> <div><div>⦿</div>Bit Holder</div>	<div>#1 x 1in</div> <div>#2 x 1in</div> <div>#3 x 1in</div> <div>#1 x 2in</div> <div>#2 x 2in</div> <div>#3 x 2in</div> <div>#2 x 3.5in</div> <div>T15 x 1in</div> <div>T20 x 1in</div> <div>T25 x 1in</div> <div>T30 x 1in</div> <div>T20 x 2in</div> <div>T25 x 2in</div> <div>T30 x 2in</div> <div>T40 x 2in</div> <div>T20 x 3.5in</div> <div>T25 x 3.5in</div> <div>T30 x 3.5in</div> <div>#1 x 1in</div> <div>#2 x 1in</div> <div>#3 x 1in</div> <div>#1 x 2in</div> <div>#2 x 2in</div> <div>3/8 x 3.5in</div> <div>3/8 x 3in</div> <div>5/16 x 3in</div> <div>1/4 x 2.4in</div>	<div>5</div> <div>1</div> <div>3</div> <div>1</div> <div>2</div> <div>5</div> <div>1</div> <div>2</div> <div>1</div> <div>2</div> <div>2</div> <div>1</div> <div>2</div> <div>1</div> <div>1</div> <div>1</div> <div>1</div> <div>1</div> <div>1</div> <div>1</div> <div>1</div> <div>1</div> <div>1</div> <div>1</div> <div>1</div>		(7) 1in Phillips bits (#1, (5) #2, #3), (5) 2in Phillips bits (#1, (3) #2, #3), (1) 3.5in Phillips bit (#2), (3) 1in square bits (#1, (2) #2, #3), (2) 2in square bits (#1, #2), (1) 3.5in square bits (#3), (9) 1in Torx bits (T15, (2) T20, (5) T25, T30), (5) 2in Torx bits (T20, (2) T25, T30, T40), (3) 3.5in Torx bits (T20, T25, T30), (2) nut setters (5/16in, 3/8in), (1) bit holder (1/4in), plastic case	\$32.50
<u>WT70298</u>	7		<div><div>+</div>Phillips</div> <div><div>☆</div>Torx</div> <div><div>□</div>Square</div>	<div>#1 x 2in</div> <div>#2 x 2in</div> <div>T20 x 2in</div> <div>T25 x 2in</div> <div>T30 x 2in</div> <div>#1 x 2in</div> <div>#2 x 2in</div>	1		(2) 2in Phillips bits (#1, #2), (2) 2in square bits (#1, #2), (3) 2in torx bits (T20, T25, T30), plastic case	\$13.00



Tools that work for you

Bit Drivers, Bits, & Adapters

Impact Driver Bit Sets - cont'd

Part Number	Number of Pieces	Part Image	Type	Bit Size Tip Size x Length	Bit Quantity Included	Drive Size	Set Includes	Price
WT76889	32		⊕ Phillips	#1 x 1in	2	1/4in	(1) Mini ratchet 1/4in hex to 1/4in square adapter, (1) 1/4in drive locking magnetic bit holder, (6) Phillips bits ((2) #1, (2) #2, (2) #3), (3) square bits (#1, #2, #3), (7) torx bits (T10, T15, T20, T25, T27, T30, T40), (4) hex metric bits (3.0mm, 4.0mm, 5.0mm, 6.0mm), (7) hex imperial bits (1/8, 9/64, 5/32, 3/16, 7/32, 1/4in), (3) Pozidriv bits (#1, #2, #3), plastic case	\$33.75
				#2 x 1in				
				#3 x 1in				
			T15 x 1in					
			T20 x 1in					
			T25 x 1in					
			T27 x 1in					
			T30 x 1in					
			T40 x 1in					
			#2 x 1in					
			#3 x 1in					
			9/64 x 1in					
			5/32 x 1in					
			3/16 x 1in					
			7/32 x 1in					
			1/4 x 1in					
			3.0 mm x 1in					
			4.0 mm x 1in					
			5.0 mm x 1in					
			6.0 mm x 1in					
			#2 x 1in					
			#3 x 1in					

Driver Bit Holders

Part Number	Part Image	Overall Length	Shaft Length	Handle Type	Lock Mechanism	Description	Price
<u>WT28103</u>		2.25in (57mm)	n/a	SoftFinish cushion grip handle with bit storage	n/a	Wiha multi-bit stubby bit holder, 2.25in (57mm) overall length, 1/4in drive, magnetic bit holder locking mechanism, SoftFinish cushion grip handle with bit storage.	\$14.00
<u>WT70096</u>		2.4in (61mm)		n/a	Magnetic bit holder	Wiha TerminatorBlue quick-release driver bit adapter, 1/4in drive, 2.4in (61mm) overall length. Impact-rated for power tool applications.	\$8.00
<u>WT38800</u>		7.3in (184mm)	4.9in (125mm)	Classic grip t-handle		Wiha T-handle bit holder, 7.3in (184mm) overall length, 1/4in drive, magnetic bit holder locking mechanism, classic grip t-handle.	\$12.00
<u>WT38802</u>		7.0in (177mm)	5.9in (150mm)	SoftGrip t-handle	n/a	Wiha T-handle bit holder, 7.0in (177mm) overall length, 1/4in drive, magnetic bit holder locking mechanism, SoftGrip t-handle.	\$20.00