

A-A

**Thread Type**  
N=NPT threaded

**Material**  
1=303 (1.4305 AISI 303)  
2=304 (1.4301 AISI 304)  
3=304L (1.4307 AISI 304L)  
4=316 (1.4401 AISI 316)  
5=316L (1.4404 AISI 316L)

**Gland Sizes**  
02=NPT1/2"

**Thread length**  
(optional)  
(if not standard TL)

**Accessory Code**  
L=Locknut  
(Locknut is mandatory for NPT threads)


**Thread Type**  
N=NPT threaded

**Material**  
1=303 (1.4305 AISI 303)  
2=304 (1.4301 AISI 304)  
3=304L (1.4307 AISI 304L)  
4=316 (1.4401 AISI 316)  
5=316L (1.4404 AISI 316L)

**Gland Sizes**  
02=NPT1/2"


**Thread length**  
(optional)  
(if not standard TL)

**Accessory Code**  
L=Locknut  
(Locknut is mandatory for NPT threads)



B-B

CLAMPING RANGE= min.Ø6.0 - max.Ø12.0mm



9	1	NPSL 1/2" LOCKNUT	Stainless Steel
8	1	M25 HYGIENIC GLAND SEAL WASHER	EPDM (Food Contact Grade)
7	1	M25 HYGIENIC GLAND PISTON RING INOX	Stainless Spring Steel
6	1	NPT 1/2" HYGIENIC GLAND BODY TL11 INOX	Stainless Steel
5	1	M20 HYGIENIC GLAND PRESSURE RING INOX	Stainless Steel
4	1	M20 HYGIENIC GLAND CABLE CLAMPING RING	POM (Hostaform C13031)
3	1	M20 HYGIENIC GLAND CONICAL RING INOX	Stainless Steel
2	1	M20 HYGIENIC GLAND SEAL	EPDM (Food Contact Grade)
1	1	NPT 1/2" HYGIENIC GLAND CAP INOX	Stainless Steel
No/Nu.	Qty/Ad.	Part Name/Parça Adı	Material/Malzeme
Part List / Parça Listesi			

Drawing Number / Resim No	11274	Reference Number / Ref. No	-	Date / Tarih	22.07.2019
1st Discl.Request #/Y.Yn.Tal.No	2378	Designed by / Tasarlayan	Mustafa KOCAOĞLU	22.07.2019	
Bimed Code / Bimed Kodu	BNHG1-02-L	Approved by / Onaylayan	Nursel ORAL	22.07.2019	
NPT 1/2" HYGIENIC GLAND TL11 INOX WITH LOCKNUT				Material / Malzeme	
NPT 1/2" HİJYENİK RAKOR TL11 INOX SOMUNLU				Material / Malzeme	
bimed				Volume/Hacim	Mass / Ağırlık
				N/A	-
				Undefined Tolerances acc.to/ Belirtilmeyen Toleranslar (DIN 7168-f)	
				Nominal size ranges Anma ölçü aralıkları	Value Değer
				0.5s...s3	±0,05
				3<...s6	±0,05
				6<...s30	±0,10
				30<...s120	±0,15
				120<...s400	±0,20