




Technical drawing of a rectangular plate with the following dimensions and features:

- Overall width: A
- Overall height: B
- Inner width (excluding mounting holes): C
- Inner height (excluding mounting holes): D
- Distance from top edge to mounting hole center: E
- Distance from left edge to mounting hole center: F
- Corner radius: $R0.25$ TYP
- Mounting hole diameter: $\text{Ø}0.250$ TYP



STANDARD P/N: N/A			ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED			TOLERANCES UNLESS SPECIFIED			.003 .000 ±.003 ±0.010		
CUSTOMER DWG: N/A											
Y			 AttaBox A ROBROY ENCLOSURES™ BRAND								
			<i>Robroy Enclosures</i> 500 Maple Street Belding, Michigan 48809 Phone: 616-794-0700 Fax: 616-749-3378								
DATE			DRAWN BY			CUSTOMER			DWG		
ENG			BH			ROBROY ENCLOSURES			SP20		
-			DATE			DESCRIPTION			PART NUMBER		
-			12/30/22			SIDE PANEL KIT			SP20		
-			DO NOT SCALE								
-											
-											
-											

NOTES:

1. PANEL SHALL BE FREE FROM BURRS & SHARP EDGES
2. PANEL SHALL BE FLAT
3. MISALIGNED EDGES EXCEEDING 0.005" (STEPS) SHALL NOT BE PERMITTED
4. ALL EDGES SHALL BE SQUARE AND PARALLEL
5. PANEL SHALL HAVE CLEAR PVC FILM ON FRONT SIDE
6. PANELS SHALL BE PACKAGED IN AN ENVELOPE WITH NO METAL (CLASP)

THIS DRAWING IS THE SOLE AND EXCLUSIVE
PROPERTY OF ROBROY ENCLOSURES.
NO PART OF THIS DRAWING MAY BE
REPRODUCED, DISTRIBUTED, OR PUBLICALLY
DISPLAYED IN ANY FORM OR BY ANY MEANS
WITHOUT THE EXPRESS WRITTEN
PERMISSION OF ROBROY ENCLOSURES.
ALL RIGHTS RESERVED
UNDER THE COPYRIGHT LAWS.
COPYRIGHT © 2022 ROBROY ENCLOSURES


SPECIAL REQUIREMENTS

ASSEMBLY:

1. (1) WPSKIT TAPED TO EACH PANEL
 - (4x) RMSLOTNUT
 - (4x) RMSCT10-32X3/4RHZN
 - (4x) RMSP10-32X5-16NYLON
 - (4x) RMWA510ZN
2. PACK IN POLY MAILER
 - FOLD EXCESS MATERIAL AROUND PANEL AND TAPE TIGHT
 - PLACE 4X3 LABEL ON OUTSIDE OF TAPE MAILER

END USER NOTES:

1. SLOT-NUT KIT INSTALLATION
 - TORQUE SCREWS TO 16 IN.-LBS
2. 80 lb. RECOMMENDED PANEL LOAD LIMIT

NEMA 250: TYPE N/A IEC 60529: N/A		STANDARD P/N: N/A		ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED		TOLERANCES UNLESS SPECIFIED		XX3 ±.003		XX10 ±.010	
COLOR: N/A COLOR STANDARD: N/A		CUSTOMER DWG: N/A									
MATERIAL: ALUMINUM				<div>Robroy Enclosures 500 Maple Street Belding, Michigan 48809 Phone: 616-749-0700 Fax: 616-749-3378</div> <div>A ROBROY ENCLOSURES™ BRAND</div>							
REVISION HISTORY											
REV	DESCRIPTION	DATE	ENG	DRAWN BY	DATE	CUSTOMER			DWG		
-	-	-	-	BH	12/30/22	ROBROY ENCLOSURES			SP20		
-	-	-	-	SCALE		DESCRIPTION			PART NUMBER		
-	-	-	-	DO NOT SCALE		SIDE PANEL KIT			SP20		