




✓ BREAK SHARP CORNERS




- NOTES:**
1. PANEL SHALL BE FREE FROM BURRS & SHARP EDGES
  2. PANEL SHALL BE FLAT
  3. MISALIGNED EDGES EXCEEDING 0.005" (STEPS) SHALL NOT BE PERMITTED
  4. ALL EDGES SHALL BE SQUARE AND PARALLEL
  5. PANEL SHALL HAVE CLEAR PVC FILM ON ONE SIDE
  6. ALL "16" SIZE PANELS AND BELOW SHALL BE PACKAGED IN AN ENVELOPE WITH NO METAL (CLASP)
  7. "24" SIZE PANEL SHALL BE PACKAGED IN CARDBOARD WITH NO METAL (STAPLES)

THIS DRAWING IS THE SOLE AND EXCLUSIVE  
PROPERTY OF ROBROY ENCLOSURES.  
NO PART OF THIS DRAWING MAY BE  
REPRODUCED, DISTRIBUTED, OR PUBLICALLY  
DISPLAYED IN ANY FORM OR BY ANY MEANS  
WITHOUT THE EXPRESS WRITTEN  
PERMISSION OF ROBROY ENCLOSURES.  
ALL RIGHTS RESERVED  
UNDER THE COPYRIGHT LAWS.  
COPYRIGHT © 2022 ROBROY ENCLOSURES

**ASSEMBLY:**  
1. (1) SLOT NUT KIT (PCSNK) INCLUDED  
2. PACK IN POLY MAILER  
-FOLD EXCESS MATERIAL AROUND PANEL AND TAPE TIGHT  
-PLACE 4X3 LABEL ON OUTSIDE OF TAPED MAILER

1. SLOT-NUT KIT INSTALLATION  
- TORQUE SCREWS TO 16 IN.-LBS  
2. 150 lb. RECOMMENDED SHELF LOAD LIMIT

NEMA 250: TYPE N/A IEC 60529: N/A				STANDARD PIN: N/A		ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED		TOLERANCES UNLESS SPECIFIED		.XX ±0.03 .XXX ±0.010	
COLOR: N/A COLOR STANDARD: N/A				CUSTOMER DWG: N/A							
MATERIAL: ALUMINUM						 <b>AttaBox</b> A ROBROY ENCLOSURES™ BRAND					
REVISION HISTORY											
REV	DESCRIPTION			DATE	ENG	<b>Robroy Enclosures</b> 500 Maple Street Belding, Michigan 48809 Phone: 616-794-0700 Fax: 616-749-3378					
-	-			-	-	DRAWN BY	DATE	CUSTOMER			DWG
-	-			-	-	BH	12/30/22	ROBROY ENCLOSURES			WD1610
-	-			-	-	SCALE			PART NUMBER		
-	-			-	-	DESCRIPTION			WEIGHT DISTRIBUTION SHELF		
-	-			-	-	DO NOT SCALE			WD1610		

