


ACCESSORIES INSTALLATION MANUAL

S Series - Plastic fastening clamps





Part number	S00G2
Material	Resin
Orientation	Fixed at 0°
Packaging unit	2 units




Dimensions in mm

How to install:




SCREW OPTIONS

P Series - Metal fastening clamps





Part number	P00G1
Material	Stainless steel
Orientation	Fixed at 0° y 90°
Packaging unit	2 units



Dimensions in mm

How to install:




SCREW OPTIONS

P Series - Plastic fastening clamps





Part number	P00G2
Material	Resin
Orientation	Fixed at 0° y 90°
Packaging unit	2 units



Dimensions in mm


How to install:



P Series - Plastic rotating clamps








Part number	P00G3
Material	Resin
Orientation	Fixed at 0°, 15°, 30°, 60°, 75°, 90°
Packaging unit	2 units




Dimensions in mm


How to install:



P-Series - Magnetic fastening clamps




Part number	P00G4
Material	Resin
Orientation	Fixed at 0°
M6D16 magnet integrated in the clamp	
Packaging unit	2 units




Dimensions in mm


How to install:



P Series - Rotary fixings




Part number	P00R1
Material	Stainless steel
Fixed orientation	0° & 90°
Variable orientation	0° to 90°
Compatible with M6DI6	
Packaging unit	2 units (left + right)




Dimensions in mm


How to install:



P Series - Double Bar Rotary fixing




Part number	P00R2
Material	Stainless steel
Fixed orientation	0° & 90°
Variable orientation	0° to 90°
Packaging unit	2 units (symmetrical)



Dimensions in mm


How to install:



P Series - 60° double rotating fixings




Part number	P00R3
Material	Stainless steel
Fixed orientation	0° & 90°
Variable orientation	0° to 90°
Compatible with M6D16	
Packaging unit	1 unit



Dimensions in mm


How to install:




P Series - 90° double rotating fixings




Part number	P00R4
Material	Stainless steel
Fixed orientation	0° & 90°
Variable orientation	0° to 90°
Compatible with M6DI6	
Packaging unit	2 units (left + right)




Dimensions in mm




How to install:



F-Series - Plastic fastening clamps





Part number	F00G2
Material	Resin
Orientation	Fixed at 0°
Packaging unit	2 units




Dimensions in mm

How to install:




SCREW OPTIONS

F Series - Magnetic fixing clamps




Part number	F00G4
Material	Resin
Orientation	Fixed at 0°
Magnet M6D16 integrated in the clamp	
Packaging unit	2 units




Dimensions in mm


How to install:



F Series - Rotary fixings




Referencia	FOOR1
Material	Stainless steel
Fixed orientation	0° & 90°
Variable orientation	0° to 90°
Compatible with M6D16	
Packaging unit	2 units (left + right)



Dimensions in mm


How to install:



Magnetic support ø16 mm




Part number	M6D16
Material	Stainless steel + neodymium
Compatibilidad	P00R1, P00R2, P00R3, F00R1
Packaging unit	2 units




Dimensions in mm



How to install:



B and R Series - Lateral support




Part number	B00S1
Material	Stainless steel
Fixed orientation	0° & 90°
Packaging unit	1 unit




Dimensions in mm


How to install:



Support for Cognex 5000, 7000 Series cameras




Part number	C00C1
Material	Stainless steel
Fixed orientation	90°
Packaging unit	1 unit




Dimensions in mm

How to install:




COGNEX 7000




COGNEX 5000


Support Sensopart 1st. & Next Gen cameras




Part number	C00SI
Material	Stainless steel
Fixed orientation	90°
Variable feed rate	0 - 80 mm.
Packaging unit	1 unit



How to install:





Sensopart camera bracket for Dome




Part number	C00S2
Material	Stainless steel
Fixed orientation	90°
Variable feed rate	0 - 80 mm.
Packaging unit	1 unit

How to install:




Dimensions in mm

Universal flat camera bracket



Part number	C00FI
Material	Stainless steel
Packaging unit	1 unit



Dimensions in mm

How to install:

