

Monitor OSD and Settings



Chapter 3

In this Chapter...

On Screen Display (OSD) Controls.....3-2

On Screen Display (OSD) Controls

Use the OSD controls to make adjustments to the monitor’s settings. The OSD controls are located on the back of the monitor. They consist of five pushbuttons.



OSD Buttons		
Button	Function	Purpose
Power	Power On/Off	Press to power the monitor on/off.
		Press at least 1 second for power off.
Menu	OSD menu On/Off	Press to turn the OSD menu on/off.
	Leave OSD Submenu	Press to step out of a submenu.
Select	Step through menu	Press to step into a submenu.
	Execute Autotune (VGA only)	Press to execute autotune after clicking the "Auto" key.
+	Move up to next item	Press to move the cursor up to the next menu item.
	Increase value	Press to increase the value of an item.
-	Move down to next item	Press to move the cursor down to the next menu item.
	Decrease value	Press to decrease the value of an item.

On-Screen Display Menus Controls

OSD Menus					
Main Menu	Submenu	Input Method	Value/Range	Default Value	Notes
Picture	Backlight	Slider	0-100	100	Adjust luminance
	Brightness	Slider	0-100	50	Adjust brightness
	Contrast	Slider	0-100	50	Adjust contrast
	Sharpness	Slider	0-4	2	Adjust sharpness
Display	Auto Adjust	Text	—	—	Auto adjust VGA screen (VGA only)
	H Position	Slider	0-100	VGA adjustable	Adjust VGA screen horizontal position (VGA only)
	V Position	Slider	0-100	VGA adjustable	Adjust VGA screen vertical position (VGA only)
	Clock	Slider	0-100	VGA adjustable	Adjust VGA signal clock latency (VGA only)
	Phase	Slider	0-100	VGA adjustable	Adjust VGA signal clock phase (VGA only)
Color	Temperature	Text	9300K	6500k	Select color temperature
			6500K		
			5800K		
			User		
	Hue	Slider	0-100	50	Adjust color hue
	Saturation	Slider	0-100	50	Adjust color saturation
	Auto Color	Text	—	—	Auto adjust color parameter on VGA
Advance	Aspect Ratio	Text	Full	Full	Select the aspect ratio of the screen
			16:9		
			4:3		
			5:4		
	Over Scan	Text	On/Off	On	Turn on/off over scan on screen
Input	DDCCI	Text	On/Off	On	Turn on/off DDCCI communication function
	Auto Select	—	—	—	Auto select input source
	VGA	—	—	—	Set input source as VGA
	HDMI	—	—	—	Set input source as HDMI
Other	Reset	—	—	—	Reset OSD user setting
	Menu Time	Slider	10-60	10	Set OSD menu timeout
	OSD H Pos	Slider	0-100	50	Set OSD menu horizontal position
	OSD V POS	Slider	0-100	50	SET OSD MENU VERTICAL POSITION
	Language	Text	English	English	Set OSD language
			French		
			German		
			Italiano		
			Spanish		
			中文		
			簡中		
			日文		
	Transparency	Slider	0-7	0	Set OSD menu transparency
Information	—	Text	—	—	Display input source information