

# SAGINAW CONTROL AND ENGINEERING

## TWO-DOOR - SINGLE ACCESS ACCESSORY SELECTION GUIDE

PART NUMBER	DESCRIPTION	SIZE	SCE-604818FSD/SSFS	SCE-724818FSD/SSFS	SCE-724824FSD/SSFS	SCE-726018FSD/SSFS	SCE-726024FSD/SSFS	SCE-726036FSD/SSFS	SCE-727218FSD/SSFS	SCE-727224FSD/SSFS	SCE-904820FSD/SSFS	SCE-904824FSD/SSFS	SCE-907220FSD/SSFS	SCE-907224FSD/SSFS	SCE-907236FSD/SSFS	SCE-60EL4818FSD
SCE-60P24F1	Full Panel	48.00H x 20.00W	B	AB	AB						AB	AB				
SCE-60P36F1	Full Panel	48.00H x 32.00W							AB	AB			AB	AB	AB	
SCE-60P48F1	Full Panel	48.00H x 44.00W	•	A	A						A	A				•
SCE-72P24F1	Full Panel	60.00H x 20.00W		B	B						AB	AB				
SCE-72P30F1	Full Panel	60.00H x 26.00W				B	B	B								
SCE-72P36F1	Full Panel	60.00H x 32.00W							B	B			AB	AB	AB	
SCE-72P48F1	Full Panel	60.00H x 44.00W		•	•						A	A				
SCE-72P60F1	Full Panel	60.00H x 56.00W				•	•	•					A	A	A	
SCE-72P72F1	Full Panel	60.00H x 68.00W							•	•			A	A	A	
SCE-90P24F1	Full Panel	78.00H x 20.00W									B	B				
SCE-90P36F1	Full Panel	78.00H x 32.00W											B	B	B	
SCE-90P48F1	Full Panel	78.00H x 44.00W									•	•				
SCE-90P72F1	Full Panel	78.00H x 68.00W											•	•	•	
SCE-60P24F2	Half Panel	24.88H x 20.00W	B	AB	AB						AB	AB				•
SCE-60P36F2	Half Panel	24.88H x 32.00W							AB	AB			AB	AB	AB	
SCE-72P24F2	Half Panel	30.88H x 20.00W	AB	B	B						AB	AB				AB
SCE-72P30F2	Half Panel	30.88H x 26.00W				B	B	B								
SCE-72P36F2	Half Panel	30.88H x 32.00W							B	B			AB	AB	AB	
SCE-72P48F2	Half Panel	30.88H x 44.00W	A	•	•						A	A				A
SCE-72P60F2	Half Panel	30.88H x 56.00W				•	•	•								
SCE-72P72F2	Half Panel	30.88H x 68.00W							•	•			A	A	A	
SCE-90P24F2	Half Panel	39.88H x 20.00W	AB	AB	AB						B	B				AB
SCE-90P36F2	Half Panel	39.88H x 32.00W							AB	AB			B	B	B	
SCE-90P48F2	Half Panel	39.88H x 44.00W		A	A						•	•				
SCE-90P72F2	Half Panel	39.88H x 68.00W							A	A			•	•	•	
SCE-60SMP14	Side Panel	48.00H x 14.00W	C													C
SCE-72SMP14	Side Panel	60.00H x 14.00W		C	•	C	•	•	C	•						
SCE-72SMP20	Side Panel	60.00H x 20.00W			C		C	•		C						
SCE-90SMP14	Side Panel	78.00H x 14.00W									•	•	•	•	•	
SCE-90SMP20	Side Panel	78.00H x 20.00W										C		C	•	
SCE-90SMP30	Side Panel	78.00H x 30.00W													•	
SCE-72SP24F3	Full Swing-Out Panel	60.00H x 18.81W		B	B											
SCE-72SP30F3	Full Swing-Out Panel	60.00H x 24.81W				B	B	B								
SCE-72SP36F3	Full Swing-Out Panel	60.00H x 30.81W							B	B						
SCE-90SP36F3	Full Swing-Out Panel	78.00H x 30.81W											B	B	B	
SCE-72SP24F4	Half Swing-Out Panel	30.88H x 18.81W		B	B											
SCE-72SP30F4	Half Swing-Out Panel	30.88H x 24.81W				B	B	B								
SCE-72SP36F4	Half Swing-Out Panel	30.88H x 30.81W							B	B						
SCE-90SP36F4	Half Swing-Out Panel	39.88H x 30.81W											B	B	B	
SCE-7230SOF19	Swing-Out Rack Frame	60.50H x 27.56W				B	B	B								
SCE-7236SOF19	Swing-Out Rack Frame	60.50H x 33.56W							B	B						
SCE-9036SOF19	Swing-Out Rack Frame	78.50H x 33.56W											B	B	B	
SCE-14RMW	Removable Wire Cover	14.00D	•	•		•			•							
SCE-20RMW	Removable Wire Cover	20.00D			•	•	•		•	•	•	•	•	•	•	
SCE-60RA19TH	Type RA Rack Angle	49.00H	B	B	B						B					B
SCE-72RA19TH	Type RA Rack Angle	61.25H		B	B						B					
SCE-72RA24TH	Type RA Rack Angle	61.25H				B	B	B								
SCE-90RA19TH	Type RA Rack Angle	78.75H									B					
SCE-60RP24F5	Type RP Full Rack Angle	49.00H		B	B						B					B
SCE-72RP24F5	Type RP Full Rack Angle	61.25H	B	B	B						B					B
SCE-72RP30F5	Type RP Full Rack Angle	61.25H				B	B	B								
SCE-90RP24F5	Type RP Full Rack Angle	78.75H									B					
SCE-60RP24F6	Type RP Half Rack Angle	26.25H	B													B
SCE-72RP24F6	Type RP Half Rack Angle	31.50H	B	B	B											B
SCE-72RP30F6	Type RP Half Rack Angle	31.50H				B	B	B								
SCE-90RP24F6	Type RP Half Rack Angle	40.25H	B	B	B						B					B
SCE-60FSHDPS	Heavy Duty Panel Support	57.25H	B													B
SCE-72FSHDPS	Heavy Duty Panel Support	69.25H		B	B	B	B	B	B							
SCE-90FSHDPS	Heavy Duty Panel Support	87.25H									B	B	B	B	B	
SCE-60FSCPS	Center Panel Support	56.00H	•													•
SCE-72FSCPS	Center Panel Support	68.00H		•	•	•	•	•	•							
SCE-90FSCPS	Center Panel Support	86.00H									•	•	•	•	•	
SCE-72FSCS	Center Support	69.50H	•	•	•	•	•	•	•							
SCE-90FSCS	Center Support	87.50H									•	•	•	•	•	

A - Requires heavy duty panel supports (SCE-FSHDPS\*)  
 B - Requires center panel support (SCE-FSCPS\*)  
 C - Cannot be used when other panels are installed.

• - Installation does not require additional supports or hardware.  
 \* Blank space - Height of enclosure.