

AUTOMATIONDIRECT.com

DN-WS-PG

Pistol grip design
optimized for use
parallel to workbench



Tool-less
interchangeable
stripping cassettes

Widest stripping
capacity of any
tool of its type

Ergonomic,
strong & durable



DN-WSJ
Gray Straight Blade
Cassette.
Wire Stripping
Capacity:
PVC Insulation
34 - 8 AWG
(0.02 mm² - 10 mm²)

DN-WSMMC
Red Curved Blade
Cassette
Wire Stripping
Capacity:
PVC Insulation
10 - 5 AWG
(4 mm² - 16 mm²)

DN-WSVBC
Blue "V" Blade
Cassette
Wire Stripping
Capacity:
PVC Insulation
28 - 12 AWG
(0.1 mm² - 4 mm²)

DN-WS-PG

Self-Adjusting Stripping and Cutting Tool
(Includes DN-WSJ Straight Blade Cassette)

- **Wire Stripping Capacity:**
PVC Insulation Wire
34 - 8 AWG (0.02 mm² - 10 mm²)
- **Wire Cutting Capacity:**
Stranded Copper Wire, 8 AWG (10 mm²)
Solid Copper Wire, 16 AWG (1.5 mm²)



MADE IN SWEDEN

AUTOMATIONDIRECT.com

DN-WS-PG

Self-Adjusting Stripping and Cutting Tool














34-8 AWG
(0.02 mm²-10 mm²)




Operating instructions
Bedienungsanleitung
Mode d'emploi

Istruzioni per l'uso
Instrucciones de empleo
Gebruiksaanwijzing

Bruksanvisning
Χειρίδιος
Utilização



 CAUTION
VORSICHT
ATTENTION
ATTENZIONE
ATENCIÓN
VOORZICHTIG
OBSERVER
ΠΡΟΞΟΧΗ
CUIDADO

 Use safety Glasses to Avoid Eye Injury
Benützen Sie eine Sicherheitsbrille um Ihre Augen zu schützen
Utiliser des lunettes de sécurité pour éviter une blessure aux yeux
Usare gli occhiali di sicurezza per evitare il rischio di ferite agli occhi
Se deben usar gafas de protección para evitar lesiones de la vista
Draag ter voorkoming van oogletsel een veiligheidsbril
Αντίειδ σκόνης/λασάνων ή/και υπεριώδους ακτινοβολίας
Χρησιμοποιείτε προστατευτικά γυαλιά για να μην τραυματίσετε τα μάτια σας
Utilize óculos de proteção para evitar lesões nos olhos