

# SINGLE-DOOR - DUAL ACCESS ACCESSORY SELECTION GUIDE

| PART NUMBER   | DESCRIPTION              | SIZE            |                         |                         |                         |                         |                       |                       |                       |                       |   |
|---------------|--------------------------|-----------------|-------------------------|-------------------------|-------------------------|-------------------------|-----------------------|-----------------------|-----------------------|-----------------------|---|
|               |                          |                 | SCE-72EL2424FSDA/SSFSDA | SCE-72EL2430FSDA/SSFSDA | SCE-72EL2436FSDA/SSFSDA | SCE-72EL3024FSDA/SSFSDA | SCE-723624FSDA/SSFSDA | SCE-723636FSDA/SSFSDA | SCE-903624FSDA/SSFSDA | SCE-903636FSDA/SSFSDA |   |
| SCE-60P24F1   | Full Panel               | 48.00H x 20.00W | A                       | A                       | A                       |                         |                       |                       |                       |                       |   |
| SCE-60P36F1   | Full Panel               | 48.00H x 32.00W |                         |                         |                         |                         | A                     | A                     | A                     | A                     |   |
| SCE-72P24F1   | Full Panel               | 60.00H x 20.00W | •                       | •                       | •                       |                         |                       |                       |                       |                       |   |
| SCE-72P30F1   | Full Panel               | 60.00H x 26.00W |                         |                         |                         | •                       |                       |                       |                       |                       |   |
| SCE-72P36F1   | Full Panel               | 60.00H x 32.00W |                         |                         |                         |                         | •                     | •                     | A                     | A                     |   |
| SCE-90P36F1   | Full Panel               | 78.00H x 32.00W |                         |                         |                         |                         |                       |                       |                       | •                     | • |
| SCE-60P24F2   | Half Panel               | 24.88H x 20.00W | A                       | A                       | A                       |                         |                       |                       |                       |                       |   |
| SCE-60P36F2   | Half Panel               | 24.88H x 32.00W |                         |                         |                         |                         | A                     | A                     | A                     | A                     |   |
| SCE-72P24F2   | Half Panel               | 30.88H x 20.00W | •                       | •                       | •                       |                         |                       |                       |                       |                       |   |
| SCE-72P30F2   | Half Panel               | 30.88H x 26.00W |                         |                         |                         | •                       |                       |                       |                       |                       |   |
| SCE-72P36F2   | Half Panel               | 30.88H x 32.00W |                         |                         |                         |                         | •                     | •                     | A                     | A                     |   |
| SCE-90P24F2   | Half Panel               | 39.88H x 20.00W | A                       | A                       | A                       |                         |                       |                       |                       |                       |   |
| SCE-90P36F2   | Half Panel               | 39.88H x 32.00W |                         |                         |                         |                         | A                     | A                     | •                     | •                     |   |
| SCE-72SMP14   | Side Panel               | 60.00H x 14.00W | •                       | •                       | •                       | •                       | •                     | •                     |                       |                       |   |
| SCE-72SMP20   | Side Panel               | 60.00H x 20.00W | •                       | •                       | •                       | •                       | •                     | •                     |                       |                       |   |
| SCE-90SMP14   | Side Panel               | 78.00H x 14.00W |                         |                         |                         |                         |                       |                       |                       | •                     | • |
| SCE-90SMP20   | Side Panel               | 78.00H x 20.00W |                         |                         |                         |                         |                       |                       |                       | •                     | • |
| SCE-90SMP30   | Side Panel               | 78.00H x 30.00W |                         |                         |                         |                         |                       |                       |                       |                       | • |
| SCE-72SP24F3  | Full Swing-Out Panel     | 60.00H x 18.81W | •                       | •                       | •                       |                         |                       |                       |                       |                       |   |
| SCE-72SP30F3  | Full Swing-Out Panel     | 60.00H x 24.81W |                         |                         |                         | •                       |                       |                       |                       |                       |   |
| SCE-72SP36F3  | Full Swing-Out Panel     | 60.00H x 30.81W |                         |                         |                         |                         | •                     | •                     |                       |                       |   |
| SCE-90SP36F3  | Full Swing-Out Panel     | 78.00H x 30.81W |                         |                         |                         |                         |                       |                       |                       | •                     | • |
| SCE-72SP24F4  | Half Swing-Out Panel     | 30.88H x 18.81W | •                       | •                       | •                       |                         |                       |                       |                       |                       |   |
| SCE-72SP30F4  | Half Swing-Out Panel     | 30.88H x 24.81W |                         |                         |                         | •                       |                       |                       |                       |                       |   |
| SCE-72SP36F4  | Half Swing-Out Panel     | 30.88H x 30.81W |                         |                         |                         |                         | •                     | •                     |                       |                       |   |
| SCE-90SP36F4  | Half Swing-Out Panel     | 30.88H x 30.81W |                         |                         |                         |                         |                       |                       |                       | •                     | • |
| SCE-7230SOF19 | Swing-Out Rack Frame     | 60.50H x 27.56W |                         |                         |                         | •                       |                       |                       |                       |                       |   |
| SCE-7236SOF19 | Swing-Out Rack Frame     | 60.50H x 33.56W |                         |                         |                         |                         | •                     | •                     |                       |                       |   |
| SCE-9036SOF19 | Swing-Out Rack Frame     | 78.50H x 33.56W |                         |                         |                         |                         |                       |                       |                       | •                     | • |
| SCE-20RMW     | Removable Wire Cover     | 20.00D          | •                       |                         |                         | •                       | •                     | •                     | •                     | •                     | • |
| SCE-60RA19TH  | Type RA Rack Angle       | 49.00H          | •                       | •                       | •                       |                         |                       |                       |                       |                       |   |
| SCE-72RA19TH  | Type RA Rack Angle       | 61.25H          | •                       | •                       | •                       |                         |                       |                       |                       |                       |   |
| SCE-72RA24TH  | Type RA Rack Angle       | 61.25H          |                         |                         |                         | •                       |                       |                       |                       |                       |   |
| SCE-60RP24F5  | Type RP Full Rack Angle  | 49.00H          | •                       | •                       | •                       |                         |                       |                       |                       |                       |   |
| SCE-72RP24F5  | Type RP Full Rack Angle  | 61.25H          | •                       | •                       | •                       |                         |                       |                       |                       |                       |   |
| SCE-72RP30F5  | Type RP Full Rack Angle  | 61.25H          |                         |                         |                         | •                       |                       |                       |                       |                       |   |
| SCE-72RP24F6  | Type RP Half Rack Angle  | 31.50H          | •                       | •                       | •                       |                         |                       |                       |                       |                       |   |
| SCE-72RP30F6  | Type RP Half Rack Angle  | 31.50H          |                         |                         |                         | •                       |                       |                       |                       |                       |   |
| SCE-90RP24F6  | Type RP Half Rack Angle  | 40.25H          | •                       | •                       | •                       |                         |                       |                       |                       |                       |   |
| SCE-72FSHDPS  | Heavy Duty Panel Support | 69.25H          | •                       | •                       | •                       | •                       | •                     | •                     |                       |                       |   |
| SCE-90FSHDPS  | Heavy Duty Panel Support | 87.25H          |                         |                         |                         |                         |                       |                       |                       | •                     | • |

• - Installation does not require additional supports or hardware.  
 A - Requires heavy duty panel supports (SCE-FSHDPS\*)  
 B - Requires center panel support (SCE-FSCPS\*)  
 C - Cannot be used when other panels are installed.  
 \* Blank space - Height of enclosure.