

TWO-DOOR - DUAL ACCESS ACCESSORY SELECTION GUIDE

PART NUMBER	DESCRIPTION	SIZE	SCE-724824 FSDAD/ISSFSDAD	SCE-726024 FSDAD/ISSFSDAD	SCE-726036 FSDAD/ISSFSDAD	SCE-727224 FSDAD/ISSFSDAD	SCE-907224 FSDAD/ISSFSDAD
SCE-60P24F1	Full Panel	48.00H x 20.00W	AB				
SCE-60P36F1	Full Panel	48.00H x 32.00W				AB	AB
SCE-60P48F1	Full Panel	48.00H x 44.00W	A				
SCE-72P24F1	Full Panel	60.00H x 20.00W	B				
SCE-72P30F1	Full Panel	60.00H x 26.00W		B	B		
SCE-72P36F1	Full Panel	60.00H x 32.00W				B	AB
SCE-72P48F1	Full Panel	60.00H x 44.00W	•				
SCE-72P60F1	Full Panel	60.00H x 56.00W		•	•		
SCE-72P72F1	Full Panel	60.00H x 68.00W				•	B
SCE-90P36F1	Full Panel	78.00H x 32.00W					B
SCE-90P72F1	Full Panel	78.00H x 68.00W					•
SCE-60P24F2	Half Panel	24.88H x 20.00W	AB				
SCE-60P36F2	Half Panel	24.88H x 32.00W				AB	AB
SCE-72P24F2	Half Panel	30.88H x 20.00W	B				
SCE-72P30F2	Half Panel	30.88H x 26.00W		B	B		
SCE-72P36F2	Half Panel	30.88H x 32.00W				B	AB
SCE-72P48F2	Half Panel	30.88H x 44.00W	•				
SCE-72P60F2	Half Panel	30.88H x 56.00W		•	•		
SCE-72P72F2	Half Panel	30.88H x 68.00W				•	B
SCE-90P24F2	Half Panel	39.88H x 20.00W	AB				
SCE-90P36F2	Half Panel	39.88H x 32.00W				AB	B
SCE-90P48F2	Half Panel	39.88H x 44.00W	A				
SCE-90P72F2	Half Panel	39.88H x 68.00W				A	•
SCE-72SMP14	Side Panel	60.00H x 14.00W	•	•	•	•	
SCE-72SMP20	Side Panel	60.00H x 20.00W	•	•	•	•	
SCE-90SMP14	Side Panel	78.00H x 14.00W					•
SCE-90SMP20	Side Panel	78.00H x 20.00W					•
SCE-72SP24F3	Full Swing-Out Panel	60.00H x 18.81W	B				
SCE-72SP30F3	Full Swing-Out Panel	60.00H x 24.81W		B	B		
SCE-72SP36F3	Full Swing-Out Panel	60.00H x 30.81W				B	
SCE-90SP36F3	Full Swing-Out Panel	78.00H x 30.81W					B
SCE-72SP24F4	Half Swing-Out Panel	30.88H x 18.81W	B				
SCE-72SP30F4	Half Swing-Out Panel	30.88H x 24.81W		B	B		
SCE-72SP36F4	Half Swing-Out Panel	30.88H x 30.81W				B	
SCE-90SP36F4	Half Swing-Out Panel	39.88H x 30.81W					B
SCE-7230SOF19	Swing-Out Rack Frame	60.50H x 27.56W		B	B		
SCE-7236SOF19	Swing-Out Rack Frame	60.50H x 33.56W				B	
SCE-9036SOF19	Swing-Out Rack Frame	78.50H x 33.56W					B
SCE-20RMW	Removable Wire Cover	20.00D	•	•	•	•	•
SCE-72RA19TH	Type RA Rack Angle	61.25H	B				
SCE-72RA24TH	Type RA Rack Angle	61.25H		B	B		
SCE-72RP24F5	Type RP Full Rack Angle	61.25H	B				
SCE-72RP30F5	Type RP Full Rack Angle	61.25H		B	B		
SCE-72RP24F6	Type RP Half Rack Angle	31.50H	B				
SCE-72RP30F6	Type RP Half Rack Angle	31.50H		B	B		
SCE-90RP24F6	Type RP Half Rack Angle	40.25H	B				
SCE-72FSDPS	Heavy Duty Panel Support	69.25H	B	B	B	B	
SCE-90FSDPS	Heavy Duty Panel Support	87.25H					B
SCE-72FSCPS	Center Panel Support	68.00H	•	•	•	•	
SCE-90FSCPS	Center Panel Support	86.00H					•
SCE-72FSCS	Center Support	69.50H	•	•	•	•	
SCE-90FSCS	Center Support	87.50H					•