

PATLITE® Signal Devices

56mm Visual-Audible and Industrial Signal Beacon Accessories NE-A and NE-IL Series

| 56mm Beacon Accessories NE-A and NE-IL Series | | | | |
|---|----------|---|------------------|----------------------------|
| Part Number | Price | Description | Weight g [oz] | Drawing Link |
| <u>NE-002D</u> | \$,5,n8: | Patlite mounting bracket, wall mount, 56mm diameter, 82mm height, dark gray, polycarbonate. For use with Patlite NE-A and NE-IL series beacons. | 34 [1.19] | <u>PDF</u> |
| <u>NE-001D</u> | \$,5,nu: | Patlite tube adapter, tube mount, 56mm diameter, black, polycarbonate. For use with Patlite NE-A and NE-IL series beacons. | 31 [1.09] | <u>PDF</u> |
| <u>SZP-092D</u> | \$,5,nv: | Patlite tube adapter, tube mount, 1/2in NPT thread type, 56mm diameter, black, polycarbonate. For use with Patlite NE-A and NE-IL series beacons. | 23 [0.81] | <u>PDF</u> |
| <u>GA0000119-F1</u> | \$,5,n9: | Patlite O-ring, silicone. For use with Patlite NE-A and NE-IL series beacons. | 45.35 [1.5] | N/A |
| <u>POLE-100A21</u> | \$,5,na: | Patlite mounting pole, 22mm diameter, 100mm length, silver, aluminum. For use with Patlite NE-A and NE-IL series beacons. | 29 [1.02] | <u>PDF</u> |
| <u>POLE-300A21</u> | \$,5,nb: | Patlite mounting pole, 22mm diameter, 300mm length, silver, aluminum. For use with Patlite NE-A and NE-IL series beacons. | 86 [3.03] | <u>PDF</u> |
| <u>POLE-800A21</u> | \$,5,nc: | Patlite mounting pole, 22mm diameter, 800mm length, silver, aluminum. For use with Patlite NE-A and NE-IL series beacons. | 228 [8.04] | <u>PDF</u> |
| <u>SZ-010</u> | \$,5,nd: | Patlite mounting bracket, flange mount, 100mm diameter, 65mm height, silver, aluminum. For use with Patlite NE-A and NE-IL series beacons. | 122 [4.30] | <u>PDF</u> |
| <u>SZ-016A</u> | \$,5,n7: | Patlite mounting bracket, flange mount, 68mm diameter, 45mm height, silver, aluminum. For use with Patlite NE-A and NE-IL series beacons. | 96 [3.38] | <u>PDF</u> |



[NE-002D](#)



[NE-001D](#)



[SZP-092D](#)



[GA0000119-F1](#)



[POLE-100A21](#)



[SZ-010](#)



[SZ-016A](#)