

Bellows suction cup (round)

FGA 20 SI-55 N016

Part no...:10.01.06.00374

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > FGA 20 SI-55 N016

Bellows suction cup (round) with optimal adaptation to uneven surfaces



Size: 20

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Number of folds: 1.5

Design Data



Attribute	Value
d	4.50 mm
d2	11 mm
D1	19.90 mm
Dk	10 mm
Dmax(S)	21 mm
Ds	18.10 mm
H	15.20 mm
H2	3.80 mm
H3	8.70 mm
Z (Stroke)	5 mm

Technical Data

Attribute	Value
Number of folds	1.50
Suction force (-600mbar)	4.70 N
Size	20
Suction cup material	Silicone SI
Weight	1.50 g
Curve radius (min) (convex)	30 mm
Product family	FGA

Bellows suction cup (round)

FGA 20 SI-55 N016

Part no...:10.01.06.00374

Accessories



SA-NIP N016 G1/8-AG DN350

Part no...:10.01.06.05735

Nipple family: N 016

Thread G1: G1/8"-M

Length L1: 20 mm

Fitting length: 6 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum



SA-NIP N016 G1/8-IG DN350

Part no...:10.01.06.05731

Nipple family: N 016

Thread G1: G1/8"-F

Length L1: 18.5 mm

Fitting length: 12 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum



SA-NIP N016 M5-AG DN250

Part no...:10.01.06.00123

Nipple family: N 016

Thread G1: M5-M

Length L1: 16 mm

Fitting length: 5 mm

Nominal diameter dn: 2.5 mm

Material: Aluminum

Bellows suction cup (round)

FGA 20 SI-55 N016

Part no.:10.01.06.00374



SA-NIP N016 G1/8-AG DN310

Part no.:10.01.06.04062

Nipple family: N 016

Thread G1: G1/8"-M

Length L1: 20 mm

Fitting length: 6 mm

Nominal diameter dn: 3.1 mm

Spanner size SW2: 3 mm

Material: Aust. Stainless steel



SA-NIP N016 M5-AG DN250

Part no.:10.01.06.04365

Nipple family: N 016

Thread G1: M5-M

Length L1: 16 mm

Fitting length: 5 mm

Nominal diameter dn: 2.5 mm

Spanner size SW2: 3 mm

Material: Aust. Stainless steel



SA-NIP N016 M5-IG DN310

Part no.:10.01.06.04689

Nipple family: N 016

Thread G1: M5-F

Length L1: 16 mm

Fitting length: 10 mm

Nominal diameter dn: 3.1 mm

Spanner size SW2: 3 mm

Material: Aust. Stainless steel

Bellows suction cup (round)

FGA 20 SI-55 N016

Part no.:10.01.06.00374



SA-NIP N016 G1/8-IG DN310

Part no.:10.01.06.04690

Nipple family: N 016

Thread G1: G1/8"-F

Length L1: 18.5 mm

Fitting length: 12 mm

Nominal diameter dn: 3.1 mm

Material: Aust. Stainless steel



SPI 18 PEEK

Part no.:10.01.06.03284

Size: 18

Material: Polyetheretherketon