



DEFAULT SETTINGS

In this Appendix...

Default Settings A-2

Default Settings

Stride SE2 Series Managed Switch Default Settings		
	Configuration Parameter	Default Settings
Main Settings		
System Settings	User Name	admin
	Password	admin
	DHCP	Disabled
	IP Address	192.168.0.1
	Subnet Mask	255.255.255.0
	Gateway	192.168.0.1
	Project Name	PRJNAME
	Switch Name	Switch
	Location	Switch Location
Contact	Contact Info	
Port Settings	Port Admin	Enabled (all ports)
	Auto Speed and Duplex	Enabled (all ports)
	Flow Control	Off
	Jumbo Frame	Enabled
Redundancy Settings		
RSTP	Redundancy	RSTP enabled (all ports)
	Spanning Tree Priority	32768
	Hello Time	2
	Max Age Time	20
	Forward Delay Time	15
	Message Age Increment	Default = Increments by the greater of (Max Age Time / 16) or one
	Port Priority	128
Proprietary Redundancy Protocols	RTSP Transparent	Disabled (all ports)
	AD-Ring	No Domain ID assigned No ports assigned as AD-Ring ports
	AD-Ring+	Disabled
	AD-RP	No Domain ID assigned No ports assigned as AD-RP Ring ports

A

Stride SE2 Series Managed Switch Default Settings (cont'd)		
Configuration Parameter	Default Settings	
Traffic Filtering Settings		
Multicast Filtering	IGMP	Enabled (all ports)
	IGMP Auto Query	Enabled (all ports)
QoS	QoS	802.1P (all ports)
	Egress Type	SP (Strict Priority) (all ports)
VLAN	VLAN	All ports and switch management participate in VLAN1
	GVRP	Disabled
	MAC Aging Time	300 sec
Switch Management Settings		
	ARP Aging Time	20 min
	Port Trunk (Link Aggregation) Mode	HASH No port selected for Link Aggregation
	SSH	Disabled
	Dot1x	Disabled
	TACACS+	Disabled
	Browser Access Protocol	HTTP
	DHCP Server	Disabled
	DHCP Snooping	Disabled
Network Management Settings		
Network Monitoring	LLDP	Disabled
	Syslog	Enabled
	RunLog	Disabled
	Save in Flash	Disabled
	Send to Server	Disabled
	Remote Server IP Address	0.0.0.0
	SNMP	Disabled
	SNMP Trap	Enabled
	SNMP Trap Port ID	162
	EtherNet/IP	Disabled
	Modbus TCP	Disabled
	Link Check	No ports enabled
	RMON	None Configured
Network Time Protocol SNTP	Disabled	

Stride SE2 Series Managed Switch Default Settings (cont'd)		
	Configuration Parameter	Default Settings
Network Management Settings (continued)		
Network Security	Port Security	No ports enabled
Network Troubleshooting Settings	Port Monitor	No ports monitored
	Alarm	No alarms enabled
	Port CRC Project	No ports enabled
	Loop Detect	No ports enabled

A