




Stripping Tools


Wire and Cable Stripping Tools



JT30155 Features

- Stripping jackets of round cables and single conductor wire
- Cable Capacity 8 to 13mm (0.31 to 0.50in)
- Conductor stripping capacity:
 - 0.2, 0.3, 0.8, 1.5, 2.5 & 4.0 mm²
 - 24, 22, 18, 16, 14 & 12 AWG
- No adjustment of cutting depth necessary
- Internal blade for longitudinal cut
- Retractable trimming blade
- Special hardened and tempered steel titanium-nitride coated blade for long life

To use the tool, open the cable stripper and insert the cable. Close the cable stripper and rotate 1/4 turn to the right and 1/4 turn to the left. Bend cable slightly and pull off sheathing



Wire and Cable Stripping Tools			
Part Number	Description	Qty	Price
JT30155	JOKARI multi-purpose cutting and stripping tool, compatible with round cable and round wire, non-slip grip, slide-out blade, 0.31-0.50in cable stripping capacity, 24-12 AWG wire stripping capacity.	1	\$64h0:



Stripping Tools

Wire and Cable Stripping Tools



JT30120 Features

- Stripping of sheathing of round cable
- Capacity 8 to 13mm (0.31 to 0.50in)
- No adjustment of cutting depth necessary
- Special hardened and tempered steel titanium-nitride coated blade for long life



JT30500 Features

- Stripping jackets of Ethernet cables
- Cable Capacity 4.5 to 10mm (0.19 to 0.38in)
- No adjustment of cutting depth necessary
- Special hardened and tempered steel titanium-nitride coated blade for long life



JT30161 Features

- Stripping jackets of Ethernet cables
- Cable Capacity 4.5 to 10mm (0.19 to 0.38in)
- Conductor stripping for 0.2, 0.3, 0.8mm² / 24, 22, 18AWG
- No adjustment of cutting depth necessary
- Internal blade for longitudinal cut
- Special hardened and tempered steel titanium-nitride coated blade for long life



Wire and Cable Stripping Tools			
Part Number	Description	Qty	Price
<u>JT30161</u>	JOKARI multi-purpose cutting and stripping tool, compatible with data & communications cable and round wire, slide-out blade, 0.19-0.38in cable stripping capacity, 24-18 AWG wire stripping capacity.	1	\$64h2:
<u>JT30500</u>	JOKARI precision stripping tool, compatible with data & communications cable, 0.19-0.38in cable stripping capacity.	1	\$64h3:
<u>JT30120</u>	JOKARI precision stripping tool, compatible with round cable, 0.31-0.50in cable stripping capacity.	1	\$.64g,: