



Heat Guns

Overview

Master Heat Guns are the result of more than 60 years of leadership in building rugged, reliable heat guns.

AutomationDirect is proud to offer a robust selection of handheld electric heat guns and tools. Ranging from North America's #1 best selling heavy-duty industrial heat gun to the small but powerful pencil-style EC-MINI, we have a heat gun to meet your needs. You can find the Master brand used in some of the most demanding production environments by many of the most well-respected companies worldwide.

All Master products are made from superior quality materials and the finest craftsmanship. With over 60 years of experience, the Master name stands for uncommon expertise in heat technology and quality products.

So whether you are looking for the industry's most rugged and reliable heat tools for heavy-duty industrial use or DIY projects, Master Appliance heat guns will blow you away!



[HG-201D-00-K](#)
[HG-301D-00-K](#)
[HG-501D-00-K](#)
[VT-751D-00-K](#)



[VT-751D](#)



[HG-201D](#)
[HG-301D](#)
[HG-501D](#)



[MA10008](#)



[EC-MINI](#)

Heat Gun Overview			
Part Number	Series	Item	Price
HG-201D	D-Series Fixed-range	Heat Gun: 400 deg F, 600W	\$06b4o:
HG-201D-00-K			\$06b4s:
HG-301D		Heat Gun: 800 deg F, 1440W	\$06b4p:
HG-301D-00-K			\$06b4t:
HG-501D		Heat Gun: 1200 deg F, 1740W	\$06b4q:
HG-501D-00-K			\$06b4u:
VT-751D	D-series Varitemp	Heat Gun: 1200 deg F, 1740W	\$06b4v:
VT-751D-00-K			\$06b4x:
MA10008	Master-Mite	Heat Gun: 650 deg F, 475W	\$06b4z:
EC-MINI	EC-Mini	Heat Gun: 650 deg F, 350W	\$06b4f:



Heat Guns

Fixed-Range Heat Guns

The D-series Master Heat Guns are Heavy-duty industrial-quality heat guns. A universal motor, die-cast aluminum housing, reinforced mica-insulated ceramic heating element, and externally replaceable carbon brushes make a rugged, reliable source of flame-less heat whether you're working with freezer coils, plastic laminates, circuit boards, PVC, fiberglass, or heat-shrinkable materials. This heat gun was designed to be versatile for use in hundreds of applications: bending plastics, curing adhesives, drying parts, heating parts, shrink-tubing and packaging, stripping paint, and much, much more.

Features

- Upgraded long-life universal motor delivers industry-leading run life
- High 27 CFM and 3400 FPM airflow gets the job done fast
- Quick-change plug-in heating element
- Optimized design for improved serviceability
- Redesigned ergonomic soft grip handle maximizes user comfort
- Sturdy die-cast aluminum housing will hold up in even the most demanding work environments
- Non-slip, reinforced stand offers stable 90-degree adjustability
- 6-ft power cord
- Designed and assembled in the USA



Quick-change plug-in heating element



[HG-201D-00-K](#)

[HG-301D-00-K](#)

[HG-501D-00-K](#)

D-Series Heat Guns and Kits							
Part Number	Voltage	Power Rating	Amperage Rating	Flow Rating	Maximum Tip Temperature	Includes	Price
<u>HG-201D</u>	120 VAC	600W	5.0A	27 CFM	400 deg F	non-slip reinforced stand	\$06b4o:
<u>HG-201D-00-K</u>						non-slip reinforced stand, (3) attachments (heat shrink, spreader, reducer), plastic carrying case	\$06b4s:
<u>HG-301D</u>		1440W	12.0A		800 deg F	non-slip reinforced stand	\$06b4p:
<u>HG-301D-00-K</u>						non-slip reinforced stand, (3) attachments (heat shrink, spreader, reducer), plastic carrying case	\$;06b4t:
<u>HG-501D</u>		1740W	14.5A		1200 deg F	non-slip reinforced stand	\$06b4q:
<u>HG-501D-00-K</u>						non-slip reinforced stand, (3) attachments (heat shrink, spreader, reducer), plastic carrying case	\$06b4u:

Note: Replacement tips not included in 5-year warranty



Heat Guns

Varitemp® Heat Guns

The Master Varitemp® heat gun is a heavy-duty industrial-quality heat gun. A universal motor, die-cast aluminum housing, reinforced mica-insulated ceramic heating element and externally replaceable carbon brushes make a rugged, reliable source of flame-less heat whether you're working with freezer coils, plastic laminates, circuit boards, PVC, fiberglass, or heat-shrinkable materials. This heat gun was designed to be versatile for use in hundreds of applications: bending plastics, curing adhesives, drying parts, heating parts, shrink-tubing and packaging, stripping paint, and much, much more

Features

- Upgraded long-life universal motor delivers industry-leading run life
- High 27 CFM and 3400 FPM airflow gets the job done fast
- New variable temperature dial provides easy temperature adjustment from 130°F to 1200°F
- Quick-change plug-in heating element
- Optimized design for improved serviceability
- Redesigned ergonomic soft grip handle maximizes user comfort
- Sturdy die-cast aluminum housing will hold up in even the most demanding work environments
- Non-slip, reinforced stand offers stable 90-degree adjustability
- 6-ft power cord
- Designed and assembled in the USA



Variable temperature dial

Quick-change plug-in heating element



90° Adjustable non-slip stand



VT-751D-00-K

Varitemp® Heat Guns and Kits							
Part Number	Voltage	Power Rating	Amperage Rating	Flow Rating	Maximum Tip Temperature	Includes	Price
<u>VT-751D</u>	120 VAC	1740W	14.5A	27 CFM	1200 deg F	non-slip reinforced stand	\$06b4v:
<u>VT-751D-00-K</u>						non-slip reinforced stand, (3) attachments (heat shrink, spreader, reducer), plastic carrying case	\$06b4x:

Note: Replacement tips not included in 5-year warranty



Heat Guns

Heat Shrink

The heat shrink attachment reflects heat around an object, and can therefore be used to apply heat to shrinkable tubing or to thaw pipes. It may also be used to prevent the surface behind the nozzle from being burned or damaged.

Spreader






The spreader attachment is used to disperse heat over a wide area. This tip type may be used for drying, removing paint, or thawing.

Reducer

The reducer attachment focuses heat on a specific area. It may be used to bend acrylic plastic sheets or direct heat into corners.



MA35245

D-Series and Varitemp® Master Heat Gun Accessories						
Part Number	Part Image	Attachment Type	Heat Shrink Nominal Diameter	Material	For Use With	Price
<u>A-160-HG</u>		heat shrink	up to 3/4in diameter	Chrome-Plated Steel	HG-201D, HG-301D, HG-501D & VT-751D heat guns	\$;6b4]:
<u>A-170-HG</u>			3/4 to 2in diameter			\$;6b4[:
<u>MA51543</u>		spreader	n/a			\$6b4#:
<u>MA51544</u>		reducer				\$;6b4!:
<u>MA35245</u>		heat shrink spreader reducer				up to 3/4in diameter

Note: Replacement tips not included in 5-year warranty