

Swivellink Mounting System Mounting Plates



Sensor Brackets

Choose sensor bracket holder based on size (Standard vs XS) and series (AFSB vs SLM).
Then choose the sensor bracket based on the size of sensor barrel.

Swivellink Mounting Plates Selection Guide					
Part Number	Price	Type	Fits to	Weight (oz [g])	Drawing
Sensor Bracket Holders (Standard)					
AFSB-SBH	\$;64fn:	Sensor bracket holder for standard series knuckles	Fits to Standard Series knuckle (ie AFSB-2)	2.51 [71.2]	PDF
AFSB-SBH-XS	\$;64fo:	Sensor bracket holder for XS series knuckles	Fits to XS Series knuckle (ie AFSB-2XS)	0.8 [22.7]	PDF
Sensor Brackets (Standard)					
AFSB-SB-8	\$;-64fi:	Sensor bracket 8mm	Fits to AFSB-SBH or AFSB-SBH-XS	1.63 [46.3]	PDF
AFSB-SB-12	\$;-64fj:	Sensor bracket 12mm		1.57 [44.5]	PDF
AFSB-SB-18	\$;64fk:	Sensor bracket 18mm		1.41 [39.9]	PDF
AFSB-SB-30	\$;-64fl:	Sensor bracket 30mm		2.14 [60.8]	PDF



[AFSB-SBH](#)



[AFSB-SB-12](#)



[SLM-SBH](#)



[SLM-SB-30](#)

Swivellink Mounting Plates Selection Guide					
Part Number	Price	Type	Fits to	Weight (oz [g])	Drawing
Sensor Bracket Holders (Metric)					
SLM-SBH	\$64g2:	Metric sensor bracket holder for standard series knuckles	Fits to Standard Series knuckle (ie SLM-2)	2.5 [70.8]	PDF
SLM-SBH-XS	\$64g3:	Metric sensor bracket holder for XS series knuckles	Fits to XS Series knuckle (ie. SLM-2XS)	0.8 [22.7]	PDF
Sensor Brackets (Metric)					
SLM-SB-8	\$;64f?:	Metric sensor bracket 8mm	Fits to SLM-SBH or SLM-SBH-XS	1.63 [46.3]	PDF
SLM-SB-12	\$;64f,::	Metric sensor bracket 12mm		1.57 [44.5]	PDF
SLM-SB-18	\$64g0:	Metric sensor bracket 18mm		1.41 [39.9]	PDF
SLM-SB-30	\$64g1:	Metric sensor bracket 30mm		2.14 [60.8]	PDF