

Accessories for OPT2012 - OPT2015

Photoelectric Sensors

Right-angle Mounting Brackets

Mounting bracket, right angle, steel and nickel plated. For use with [OPT2012](#)-[OPT2015](#) photoelectric sensors.

Accessories for OPT2012-OPT2015 Photoelectric Sensors				
Part Number	Price	Description	Drawing Link	Weight lb (g)
OPT2032	\$,7?,:.	Wenglor mounting bracket, right-angle, nickel-plated brass. For use with OPT2012 - OPT2015 photoelectric sensors.	PDF	0.36 (163.29)



[OPT2032](#)

Right-angle Swivel Mounting Systems

Mounting bracket, right-angle swivel, 360 degree vertical and horizontal adjustment, 12mm rod mount. For use with [OPT2012](#)-[OPT2015](#) photoelectric sensors. Available in all stainless steel or with an aluminum head with a stainless steel mounting plate.

Accessories for OPT2012-OPT2015 Photoelectric Sensors						
Part Number	Price	Description	Mounting Head	Mounting Plate	Drawing Link	Weight lb [g]
OPT2126	\$1nn6:	Wenglor mounting bracket, right-angle swivel, 360 degree vertical and horizontal adjustment, aluminum, 12mm rod mount. For use with OPT2012 - OPT2015 photoelectric sensors.	Aluminum	304 Stainless Steel	PDF	0.23 [104.32]
OPT2127	\$1nn7:	Wenglor mounting bracket, right-angle swivel, 360 degree vertical and horizontal adjustment, 304 stainless steel, 12mm rod mount. For use with OPT2012 - OPT2015 photoelectric sensors.	304 Stainless Steel	304 Stainless Steel	PDF	0.36 [163.29]



[OPT2126](#)

[OPT2127](#)



Note: 304 Stainless steel mounting rods sold separately: [OPT2109](#) (200mm length), [OPT2110](#) (300mm length), and [OPT2111](#) (500mm length).

Mounting Rods and Brackets

Mounting Rods

304 Stainless steel rods for mounting swivel brackets [OPT2112](#) - [OPT2127](#). Available in three lengths: 200mm, 300mm, and 500mm. 12mm diameter.

Mounting Rods for OPT2112-2127 Swivel Mounting Brackets				
Part Number	Price	Description	Drawing Link	Weight lb (g)
OPT2109	\$1nn9:	Wenglor mounting rod, 12mm diameter, 200mm length, 304 stainless steel.	PDF	0.41 [185.97]
OPT2110	\$1nna:	Wenglor mounting rod, 12mm diameter, 300mm length, 304 stainless steel.	PDF	0.60 [272.16]
OPT2111	\$1nnb:	Wenglor mounting rod, 12mm diameter, 500mm length, 304 stainless steel.	PDF	0.98 [444.52]



Right-angle Mounting Bracket

Mounting bracket, right-angle, nickel-plated brass. For use with 12mm mounting rods [OPT2109](#), [OPT2110](#) & [OPT2111](#).

Right-angle Mounting Brackets for 12mm Sensors				
Part Number	Price	Description	Drawing Link	Weight lb [g]
OPT2108	\$-1nly:	Wenglor mounting bracket, right-angle, nickel-plated brass. For use with 12mm mounting rods OPT2109, OPT2110 & OPT2111.	PDF	0.07 [31.8]

