

DIN Rail Mount EMC Shield Cable Clips SCF-EMV / MSCF-EMV Series

Overview

The SCF-EMV / MSCF-EMV series EMC shield cable clips easily snap on to 35mm DIN rail. The spring action provides uninterrupted contact pressure with the shield enabling a conductive path to discharge EMI (electromagnetic interference).

Features

- The spring action provides uninterrupted contact pressure with the shield
- Excellent discharge of high-frequency noise current
- Easy installation (no tools required)
- Zinc plated spring steel
- 35mm DIN rail mount

DIN Rail Mount EMC Shield Cable Clips SCF-EMV / MSCF-EMV Series				
Part Number	Price	Description	Shield Diameter	Drawing Link
571052	\$621k:	Murrplastik SCF-EMV series EMC shield cable clip, accepts 0.06-0.12in diameter cable, 35mm DIN rail mount, zinc plated spring steel. Package of 5.	0.06–0.12in	PDF
571054	\$-621l:	Murrplastik SCF-EMV series EMC shield cable clip, accepts 0.12-0.24in diameter cable, 35mm DIN rail mount, zinc plated spring steel. Package of 5.	0.12–0.24in	PDF
571056	\$621n:	Murrplastik SCF-EMV series EMC shield cable clip, accepts 0.24-0.31in diameter cable, 35mm DIN rail mount, zinc plated spring steel. Package of 5.	0.24–0.31in	PDF
571058	\$-621f:	Murrplastik SCF-EMV series EMC shield cable clip, accepts 0.31-0.43in diameter cable, 35mm DIN rail mount, zinc plated spring steel. Package of 5.	0.31–0.43in	PDF
571060	\$621g:	Murrplastik SCF-EMV series EMC shield cable clip, accepts 0.43-0.63in diameter cable, 35mm DIN rail mount, zinc plated spring steel. Package of 5.	0.43–0.63in	PDF
571064	\$621h:	Murrplastik SCF-EMV series EMC shield cable clip, accepts 0.67-1.18in diameter cable, 35mm DIN rail mount, zinc plated spring steel. Package of 5.	0.67–1.18in	PDF
571066	\$-621i:	Murrplastik SCF-EMV series EMC shield cable clip, accepts 1.18-1.46in diameter cable, 35mm DIN rail mount, zinc plated spring steel. Package of 5.	1.18–1.46in	PDF
571070	\$-621j:	Murrplastik MSCF-EMV series EMC shield cable clip, accepts 0.12-0.47in diameter cable, 35mm DIN rail mount, zinc plated spring steel. Package of 5.	0.12–0.47in	PDF
571072	\$621q:	Murrplastik MSCF-EMV series EMC shield cable clip, accepts 0.28-0.71in diameter cable, 35mm DIN rail mount, zinc plated spring steel. Package of 5.	0.28–0.71in	PDF



571060



571070



**SCF-EMV / MSCF-EMV installation
shown with shielded cable**

DIN Rail Mount EMC Shield Cable Clips With Strain Relief SCFZ-EMV / MSCFZ-EMV Series

Overview

The SCFZ-EMV / MSCFZ-EMV series EMC shield cable clips with strain relief easily snap on to 35mm DIN rail. The spring action provides uninterrupted contact pressure with the shield enabling a conductive path to discharge EMI (electromagnetic interference). The strain relief tab protects the cable when using with any standard cable tie.

Features

- The spring action provides uninterrupted contact pressure with the shield.
- Excellent discharge of high-frequency noise current
- High stability
- Easy installation (no tools required)
- Zinc plated spring steel
- 35mm DIN rail mount

DIN Rail Mount EMC Shield Cable Clips With Strain Relief SCFZ-EMV / MSCFZ-EMV Series				
Part Number	Price	Description	Shield Diameter	Drawing Link
571074	\$621s:	Murrplastik SCFZ-EMV series EMC shield cable clip, accepts 0.06-0.12in diameter cable, 35mm DIN rail mount, with strain relief, zinc plated spring steel. Package of 5.	0.06–0.12in	PDF
571075	\$,621t:	Murrplastik SCFZ-EMV series EMC shield cable clip, accepts 0.12-0.24in diameter cable, 35mm DIN rail mount, with strain relief, zinc plated spring steel. Package of 5.	0.12–0.24in	PDF
571076	\$621u:	Murrplastik SCFZ-EMV series EMC shield cable clip, accepts 0.24-0.31in diameter cable, 35mm DIN rail mount, with strain relief, zinc plated spring steel. Package of 5.	0.24–0.31in	PDF
571077	\$621v:	Murrplastik SCFZ-EMV series EMC shield cable clip, accepts 0.31-0.43in diameter cable, 35mm DIN rail mount, with strain relief, zinc plated spring steel. Package of 5.	0.31–0.43in	PDF
571078	\$621y:	Murrplastik SCFZ-EMV series EMC shield cable clip, accepts 0.43-0.63in diameter cable, 35mm DIN rail mount, with strain relief, zinc plated spring steel. Package of 5.	0.43–0.63in	PDF
571079	\$621z:	Murrplastik SCFZ-EMV series EMC shield cable clip, accepts 0.67-0.87in diameter cable, 35mm DIN rail mount, with strain relief, zinc plated spring steel. Package of 5.	0.67–0.87in	PDF
571071	\$.621j:	Murrplastik MSCFZ-EMV series EMC shield cable clip, accepts 0.12-0.47in diameter cable, 35mm DIN rail mount, with strain relief, zinc plated spring steel. Package of 5.	0.12–0.47in	PDF
571073	\$.621i:	Murrplastik MSCFZ-EMV series EMC shield cable clip, accepts 0.28-0.71in diameter cable, 35mm DIN rail mount, with strain relief, zinc plated spring steel. Package of 5.	0.28–0.71in	PDF



[571077](#)



[571071](#)



SCFZ-EMV / MSCFZ-EMV installation shown with cable tie securing cable to strain relief tab