

# Save up to 50% on pneumatics

AutomationDirect now offers  
pneumatic cylinders



## NITRA™ Pneumatic Stainless Steel Round Body Air Cylinders

The NITRA Pneumatics A-Series non-repairable stainless steel round body cylinders includes bore sizes from 7/16" to 2" and stroke lengths from 1/2" to 18" to meet a broad range of applications. These high quality cylinders are constructed with stainless steel bodies and double rolled-in high strength aluminum end caps with full flow ports.

- Interchangeable with other common brands of round body cylinders
- Available bore sizes: 7/16", 9/16", 3/4", 7/8", 1-1/16", 1-1/4", 1-1/2", 2"
- Excellent selection of stroke lengths
- Single-acting (spring return) and double-acting models
- Nose, pivot and double-end mounting options
- Type 304 stainless steel body with high-strength aluminum alloy end caps
- Factory lubricated for dependable, maintenance-free operation
- 250 psi operating pressure
- Models available with magnetic piston for position indication
- All models are available for same-day shipment
- Made in the USA



### CHECK OUT OUR PRICES

Pneumatic Cylinders	AutomationDirect NITRA	VS.	MSC	McMaster-Carr	Grainger
<b>Stainless Steel Air Cylinder</b> 2 inch bore, 4 inch stroke, double acting, pivot/double end mount	<b>\$53.25</b> A32040DD		<b>\$88.32</b> 36697563	<b>\$70.41</b> 6498K478	<b>\$75.20</b> 6D881
<b>Stainless Steel Air Cylinder</b> 3/4 inch bore, 1 inch stroke, single acting spring return, nose mount	<b>\$11.25</b> A12010SN		<b>\$17.05</b> 36696458	<b>\$14.35</b> 6498K141	<b>\$16.27</b> 6W070
<b>Stainless Steel Air Cylinder</b> 1-1/16 inch bore, 6 inch stroke, double acting, pivot/double end mount	<b>\$24.50</b> A17060DP		<b>\$42.84</b> 36696847	<b>\$30.31</b> 6498K658	<b>\$34.25</b> 6W130

All prices are U.S. published prices. Many other part numbers are available from all vendors. AutomationDirect prices are October 2009 prices. MSC prices are from www.msclirect.com 09/03/2009. McMaster-Carr prices are from www.mcmaster.com 09/03/2009. Grainger prices are from www.grainger.com 09/03/2009. Prices subject to change without notice.

### Also Available:

#### TUBING AND FITTINGS



[www.automationdirect.com](http://www.automationdirect.com)

For complete information or to order our free catalog, visit:  
[www.automationdirect.com/pneumatic-parts](http://www.automationdirect.com/pneumatic-parts)

**1-800-633-0405**

**Order Today,  
Ships Today!\***

\* See our Web site for details and restrictions.  
© Copyright 2009 AutomationDirect, Cumming, GA USA. All rights reserved.

**AUTOMATIONDIRECT**.COM  
the #1 value in automation