

Accessories, continued

NOTE: These parts available for sale to North American locations only

L7C/L7P/iX7NH System Motor Encoder Cables

Part Number	Price	Flex Rated	Length	Gauge	Drawing	Compatible Motors
APCS-EN03ES-AD	\$,58z:	N	3m [9.8 ft]	24AWG	PDF	APMC motors with 17-bit incremental encoders (AYK/AYK2 motors)
APCS-EN05ES-AD	\$,58]0:		5m [16.4 ft]		PDF	
APCS-EN10ES-AD	\$,58]6:		10m [32.8 ft]		PDF	
APCS-EN20ES-AD	\$,58]7:		20m [65.6 ft]		PDF	
APCS-EF03ES-AD	\$,58]8:	Y	3m [9.8 ft]		PDF	
APCS-EF05ES-AD	\$,58]9:		5m [16.4 ft]		PDF	
APCS-EF10ES-AD	\$,058]a:		10m [32.8 ft]		PDF	
APCS-EF20ES-AD	\$,058]b:		20m [65.6 ft]		PDF	
APCS-EN03ES1-AD	\$-5i64:	N	3m [9.8 ft]	24AWG	PDF	FBL/FCL series motors with 19-bit encoders
APCS-EN05ES1-AD	\$-5i65:		5m [16.4 ft]		PDF	
APCS-EN10ES1-AD	\$-05i66:		10m [32.8 ft]		PDF	
APCS-EN20ES1-AD	\$-05i67:		20m [65.6 ft]		PDF	
APCS-EF03ES1-AD	\$-05i68:	Y	3m [9.8 ft]		PDF	APM-FE/APM-FF series motors
APCS-EF05ES1-AD	\$,-05i5:		5m [16.4 ft]		PDF	
APCS-EF10ES1-AD	\$-05i60:		10m [32.8 ft]		PDF	
APCS-EF20ES1-AD	\$-05i61:		20m [65.6 ft]		PDF	
APCS-EN03DS1-AD	\$-5i62:	N	3m [9.8 ft]		PDF	
APCS-EN05DS1-AD	\$-05i63:		5m [16.4 ft]		PDF	
APCS-EN10DS1-AD	\$-05i69:		10m [32.8 ft]		PDF	
APCS-EN20DS1-AD	\$-05i6a:		20m [65.6 ft]		PDF	
APCS-EF03DS1-AD	\$-05i6b:	Y	3m [9.8 ft]		PDF	
APCS-EF05DS1-AD	\$-05i6c:		5m [16.4 ft]		PDF	
APCS-EF10DS1-AD	\$-05i6d:		10m [32.8 ft]		PDF	
APCS-EF20DS1-AD	\$-05i6e:		20m [65.6 ft]		PDF	

**APCS-EN series encoder cable****APCS-ENxxxES1 series encoder cable****APC-EF00BS-AD****L7P/iX7NH System Encoder Accessories**

Part Number	Price	Description	Compatible Drives
APC-EF00BS-AD	\$-5i5s:	17-pin motor encoder connector.	APM-FE and APM-FF series motors
APCS-BATT36-AD	\$5yn3:	Encoder battery. One (1) AA ER6V lithium battery with extended leads and an encoder cable connector.	All LS Electric motors with 19-bit encoders

**APCS-BATT36-AD**